



www.ti.com SLPS333 – NOVEMBER 2012

Dual 30-V N-Channel NexFET™ Power MOSFETs

FEATURES

- Common Source Connection
- Ultra Low Drain to Drain On-Resistance
- Space Saving SON 3.3 x 3.3mm Plastic Package
- Optimized for 5V Gate Drive
- Low Thermal Resistance
- Avalanche Rated
- Pb Free Terminal Plating
- RoHS Compliant
- Halogen Free


APPLICATIONS

 Adaptor/USB Input Protection for Notebook PCs and Tablets


DESCRIPTION

The CSD87312Q3E is a 30V common-source, dual N-channel device designed for adaptor/USB input protection. This SON 3.3 x 3.3mm device has low drain to drain on-resistance that minimizes losses and offers low component count for space constrained multi-cell battery charging applications.

Top View



Circuit Image



PRODUCT SUMMARY

T _A = 25°	С	TYPICAL VA	UNIT	
V_{DS}	Drain to Source Voltage		V	
Q_g	Gate Charge Total (4.5V)	6.3		nC
Q_{gd}	Gate Charge Gate to Drain	0.7	nC	
0	Drain to Drain On Resistance	$V_{GS} = 4.5V$	31	mΩ
R _{DD(on)}	(Q1+Q2)	V _{GS} = 8V 27		mΩ
V _{GS(th)}	Threshold Voltage	•	٧	


ORDERING INFORMATION

Device	vice Package Media		Qty	Ship	
CSD87312Q3E	SON 3.3 x 3.3mm Plastic Package	13-Inch Reel	2500	Tape and Reel	

ABSOLUTE MAXIMUM RATINGS

$T_A = 2$	5°C	VALUE	UNIT							
V_{DS}	Drain to Source Voltage	30	V							
V_{GS}	Gate to Source Voltage	+10/-8	V							
I _D	Continuous Drain Current, T _C = 25°C ⁽¹⁾	27	Α							
I_{DM}	Pulsed Drain Current (2)	45	Α							
P_D	Power Dissipation	2.5	W							
T_J , T_{STG}	Operating Junction and Storage Temperature Range	-55 to 150	°C							
E _{AS}	Avalanche Energy, single pulse I_D = 24A, L = 0.1mH, R_G = 25 Ω	29	mJ							

- (1) Typical R = 63° C/W on 1in² (2 oz.) on 0.060" thick FR4PCB
- (2) Pulse duration ≤300µs, duty cycle ≤2%



A

Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

SLPS333-NOVEMBER 2012 www.ti.com



These devices have limited built-in ESD protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the MOS gates.

ELECTRICAL CHARACTERISTICS

(T_A = 25°C unless otherwise stated)

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Static CI	naracteristics					
BV _{DSS}	Drain to Source Voltage	$V_{GS} = 0V, I_D = 250\mu A$	30			V
I _{DSS}	Drain to Source Leakage Current	$V_{GS} = 0V, V_{DS} = 24V$			1	μΑ
I _{GSS}	Gate to Source Leakage Current	$V_{DS} = 0V, V_{GS} = +10/-8V$			100	nA
V _{GS(th)}	Gate to Source Threshold Voltage	$V_{DS} = V_{GS}, I_D = 250\mu A$	0.8	1.0	1.3	V
D	Drain to Drain On Resistance (Q1 +	$V_{GS} = 4.5V, I_D = 7A$		31	38	mΩ
R _{DD(on)}	Q2)	$V_{GS} = 8V$, $I_D = 7A$		27	33	mΩ
9 _{fs}	Transconductance	$V_{DS} = 15V, I_{D} = 7A$		39		S
Dynamic	: Characteristics ⁽¹⁾					
C _{iss}	Input Capacitance			960	1250	pF
C _{oss}	Output Capacitance	$V_{GS} = 0V, V_{DS} = 15V, f = 1MHz$		190	247	pF
C _{rss}	Reverse Transfer Capacitance			12	16	pF
R_G	Series Gate Resistance			5	10	Ω
Qg	Gate Charge Total (4.5V)			6.3	8.2	nC
Q_{gd}	Gate Charge Gate to Drain	\/ 45\/ 70		0.7		nC
Q _{gs}	Gate Charge Gate to Source	$V_{DS} = 15V, I_D = 7A$		1.9		nC
Q _{g(th)}	Gate Charge at Vth			1.0		nC
Q _{oss}	Output Charge	V _{DS} = 15V, V _{GS} = 0V		4.0		nC
t _{d(on)}	Turn On Delay Time			7.8		ns
t _r	Rise Time	V 45V V 45V L 7A B 20		16		ns
t _{d(off)}	Turn Off Delay Time	$V_{DS} = 15V, V_{GS} = 4.5V, I_{DS} = 7A, R_G = 2\Omega$		17		ns
t _f	Fall Time			2.9		ns
Diode C	haracteristics ⁽¹⁾				,	
V _{SD}	Diode Forward Voltage	I _{SD} = 7A, V _{GS} = 0V		0.8	1	V
Q _{rr}	Reverse Recovery Charge	V 45V L 7A 4:/4t 200A/		5.3		nC
t _{rr}	Reverse Recovery Time	V_{DS} = 15V, I_F = 7A, di/dt = 300A/ μ s		12.2		ns
			•			

⁽¹⁾ All Dynamic and Diode Characteristics were measured with respect to one of the two drains, with the other left floating.

THERMAL CHARACTERISTICS


(T_A = 25°C unless otherwise stated)

	PARAMETER	MIN	TYP	MAX	UNIT
$R_{\theta JC}$	Thermal Resistance Junction to Case ⁽¹⁾			4.2	°C/W
$R_{\theta JA}$	Thermal Resistance Junction to Ambient ⁽¹⁾⁽²⁾			63	°C/W

 ⁽¹⁾ R_{θ,JC} is determined with the device mounted on a 1-inch² (6.45-cm²), 2-oz. (0.071-mm thick) Cu pad on a 1.5-inch x 1.5-inch (3.81-cm x 3.81-cm), 0.06-inch (1.52-mm) thick FR4 PCB. R_{θ,JC} is specified by design, whereas R_{θ,JA} is determined by the user's board design.
 (2) Device mounted on FR4 material with 1-inch² (6.45-cm²), 2-oz. (0.071-mm thick) Cu.


RUMENTS





Instruments

Max $R_{\theta JA} = 63^{\circ}C/W$ when mounted on 1 inch2 (6.45 cm2) of 2oz. (0.071-mm thick) Cu.



Max $R_{\theta JA} = 165^{\circ}C/W$ when mounted on a minimum pad area of 2-oz. (0.071-mm thick) Cu.

TYPICAL MOSFET CHARACTERISTICS

 $(T_A = 25^{\circ}C \text{ unless otherwise stated})$




Figure 1. Transient Thermal Impedance




Figure 2. Saturation Characteristics




Figure 3. Transfer Characteristics

TEXAS INSTRUMENTS

TYPICAL MOSFET CHARACTERISTICS (continued)

 $(T_A = 25^{\circ}C \text{ unless otherwise stated})$




Figure 4. Gate Charge




Figure 5. Capacitance




Figure 6. Threshold Voltage vs. Temperature




Figure 7. On-State Resistance vs. Gate-to-Source Voltage




Figure 8. Normalized On-State Resistance vs. Temperature




Figure 9. Typical Diode Forward Voltage



www.ti.com SLPS333 – NOVEMBER 2012

TYPICAL MOSFET CHARACTERISTICS (continued)

 $(T_A = 25^{\circ}C \text{ unless otherwise stated})$




Figure 10. Maximum Safe Operating Area




Figure 11. Single Pulse Unclamped Inductive Switching





Figure 12. Maximum Drain Current vs. Temperature



MECHANICAL DATA

Q3E Package Dimensions




DIM	MILLIMETERS					
DIM	MIN	MAX				
А	0.850	1.050				
b	0.280	0.400				
С	0.150	0.250				
c1	0.150	0.250				
d	0.940	1.040				
d1	0.160	0.260				
d2	0.150	0.250				
d3	0.250	0.350				
D1	3.200	3.400				
D2	2.650	2.750				
E	3.200	3.400				
E1	3.200	3.400				
E2	1.750	1.850				
е	0.68	50 TYP				
L	0.400	0.500				
θ	0°	-				
К	0.3	00 Тур				

Notes:


- 1. Pin 1-4: Drain 1
- 2. Pin 5: Gate
- 3. Pin 6-8: Drain 2
- 4. Pin 9: Source

www.ti.com SLPS333 – NOVEMBER 2012

Recommended PCB Pattern




Recommended Stencil Opening



For recommended circuit layout for PCB designs, see application note SLPA005 – Reducing Ringing Through PCB Layout Techniques.



Q3E Tape and Reel Information



Notes:

- 1. 10 sprocket hole pitch cumulative tolerance ±0.2
- 2. Camber not to exceed 1mm IN 100mm, noncumulative over 250mm
- 3. Material:black static dissipative polystyrene
- 4. All dimensions are in mm (unless otherwise specified)
- 5. Thickness: 0.30 ±0.05mm
- 6. MSL1 260°C (IR and Convection) PbF Reflow Compatible



PACKAGE OPTION ADDENDUM

6-Feb-2020

PACKAGING INFORMATION

Orderable Device	Status	Package Type	Package Drawing	Pins	Package Qty	Eco Plan	Lead/Ball Finish	MSL Peak Temp	Op Temp (°C)	Device Marking (4/5)	Samples
CSD87312Q3E	ACTIVE	VSON-CLIP	DPB	8	2500	Pb-Free (RoHS Exempt)	NIPDAU	Level-1-260C-UNLIM	-55 to 150	87312E	Samples

(1) The marketing status values are defined as follows:

ACTIVE: Product device recommended for new designs.

LIFEBUY: TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

NRND: Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

PREVIEW: Device has been announced but is not in production. Samples may or may not be available.

OBSOLETE: TI has discontinued the production of the device.

(2) RoHS: TI defines "RoHS" to mean semiconductor products that are compliant with the current EU RoHS requirements for all 10 RoHS substances, including the requirement that RoHS substance do not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, "RoHS" products are suitable for use in specified lead-free processes. TI may reference these types of products as "Pb-Free".

RoHS Exempt: TI defines "RoHS Exempt" to mean products that contain lead but are compliant with EU RoHS pursuant to a specific EU RoHS exemption.

Green: TI defines "Green" to mean the content of Chlorine (CI) and Bromine (Br) based flame retardants meet JS709B low halogen requirements of <=1000ppm threshold. Antimony trioxide based flame retardants must also meet the <=1000ppm threshold requirement.

- (3) MSL, Peak Temp. The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.
- (4) There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.
- (5) Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.
- (6) Lead/Ball Finish Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

Important Information and Disclaimer: The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

PACKAGE MATERIALS INFORMATION

www.ti.com 13-Dec-2018


TAPE AND REEL INFORMATION





	Dimension designed to accommodate the component width
	Dimension designed to accommodate the component length
K0	Dimension designed to accommodate the component thickness
W	Overall width of the carrier tape
P1	Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



*All dimensions are nominal

Device	Package Type	Package Drawing			Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
CSD87312Q3E	VSON- CLIP	DPB	8	2500	330.0	12.4	3.6	3.6	1.2	8.0	12.0	Q2

www.ti.com 13-Dec-2018



*All dimensions are nominal

Device	Device Package Type		Pins	SPQ	Length (mm)	Width (mm)	Height (mm)
CSD87312Q3E	VSON-CLIP	DPB	8	2500	367.0	367.0	35.0

IMPORTANT NOTICE AND DISCLAIMER

TI PROVIDES TECHNICAL AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for skilled developers designing with TI products. You are solely responsible for (1) selecting the appropriate TI products for your application, (2) designing, validating and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. TI grants you permission to use these resources only for development of an application that uses the TI products described in the resource. Other reproduction and display of these resources is prohibited. No license is granted to any other TI intellectual property right or to any third party intellectual property right. TI disclaims responsibility for, and you will fully indemnify TI and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these resources.

Tl's products are provided subject to Tl's Terms of Sale (www.ti.com/legal/termsofsale.html) or other applicable terms available either on ti.com or provided in conjunction with such Tl products. Tl's provision of these resources does not expand or otherwise alter Tl's applicable warranties or warranty disclaimers for Tl products.

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2020, Texas Instruments Incorporated