


## 晶创和立科技

G


## MINIATURE CADMIUM SULPHIDE PHOTOCONDUCTIVE CELL



## SPECIFICATION AND PERFORMANCE

Model	Vmax (VDC)	Pmax (mW)	Ambient temp(℃)	Spectral peak (nm)	Light Resistance at 10Lux (KΩ)	Dark Resistance (ΜΩ)	at 100-	Response Time (ms)	
								Rise Time	Decay time
GL7528	150	100	-30~+70	540	8-20	2	0.7	20	30

## **Measuring Conditions**



SHENZHEN JINGCHUANGHELI TECHNOLOGY CO., LTD. Tel:+86-755-23210829 Fax:+86-755-23210825

http://www.szjchl.com