

MINIATURE CADMIUM SULPHIDE PHOTOCONDUCTIVE CELL






FEATURES

- Miniature open frame package
- **Epoxy** coated
- Moisture resistant
- Spectral response similar to the human eye
- Applications include dusk-dawn lighting control

LIGHT DEPENDENT RESISTOR



Dimensions in millimetres

SPECIFICATION AND PERFORMANCE

Model	Vmax (VDC)	Pmax (mW)	Ambient temp(°C)	neak	Light Resistance at 10Lux (KΩ)	Dark Resistance (MΩ)	Gamm a value at 100- 10Lux	Response time (ms) I	
								Rise Time	Decay time
GL5520F	150	100	-30~+70	540	16-50	1	0.85	30	30

Measuring Conditions

1. Light resistance:

Measured at 10 Lux with standard light A (2854K color temperature) and 2hr illumination at 400-600 lux prior to testing.

2. Dark Resistance:

Measured 10 senconds after closed 10 lux.

3. Gamma Characteristic:

Between 10 lux ande 100 lux and given by $\gamma = Ig(R10/R100)$

R10、R100 Cell resistance at 10 lux and 100


The error of γ is \pm 0.1.

4. Pmax:

Max. power dissipation at ambient temperature of 25 °C.

5. Vmax:

Max. voltage in darkness that may be applied to the cell continuously.



SHENZHEN JINGCHUANGHELI TECHNOLOGY CO., LTI Http://www.sz.jchl.com E-mail:heli@szjchl.com

Tel:+86-755-23210829 Fax:+86-755-23210825