






RoHS



NOTE:

1. Rating: 50V 100mA DC
2. Insulation Resistance: $\geq 100 \text{ M}\Omega$
3. Withstand voltage: AC 500V 1Minute
4. Operating Force Range: 500gf Max
5. Mechanical Life: 3,000 Cycles

Ⓕ	Dust film		1	Polyimide tape	
Ⓖ	Terminal		10	Phosphor bronze	Gold plating
Ⓓ	Contact spring		5	Phosphor bronze	Gold plating
Ⓒ	Handle		5	PA46	White
Ⓑ	Cover		1	PPS	Black
Ⓐ	Base		1	PPS	Black
NO.	Name	Number	Qty	Material	Remarks

YUANDI® Yuandi Electronics Co, Ltd
元迪

design	date	name	DIP SWITCH
Review	date	model	TP-05
Approved	date		

Drawing number: Proportion 1:1 unit mm gage number A4

modify Review Approved Tolerance not specified