



100V PNP HIGH VOLTAGE TRANSISTOR IN SOT23

Features


- $BV_{CEO} > -100V$
- I_C = -1A High Continuous Collector Current
- I_{CM} = -2A Peak Pulse Current
- Low Saturation Voltage
- Excellent h_{FE} Characteristics up to $I_C = -1A$
- Complementary NPN Type: FMMT493
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- **PPAP Capable (Note 4)**

Mechanical Data

- Case: SOT23
- Case Material: Molded Plastic, "Green" Molding Compound UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish-Matte Tin Plated Leads, Solderable per MIL-STD-202, Method 208 @3
- Weight 0.008 grams (Approximate)

Applications

- High-Side Driver
- Load Disconnect Switch
- Motor Drive



Top View Pin-Out

Ordering Information (Notes 4 & 5)

Part Number	Compliance	Marking	Reel Size (inches)	Tape Width (mm)	Quantity per Reel
FMMT593TA	AEC-Q101	593	7	8	3000
FMMT593QTA	Automotive	593	7	8	3000
FMMT593TC	AEC-Q101	593	13	8	10,000
FMMT593QTC	Automotive	593	13	8	10,000

1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant Notes:


2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

4. Automotive products are AEC-Q101 qualified and are PPAP capable. Refer to https://www.diodes.com/quality/.

5. For packaging details, go to our website at http://www.diodes.com

Marking Information



593 = Product Type Marking Code



Absolute Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Collector-Base Voltage	V _{CBO}	-120	V
Collector-Emitter Voltage	V _{CEO}	-100	V
Emitter-Base Voltage	V _{EBO}	-7	V
Continuous Collector Current	Ic	-1	A
Peak Pulse Current	I _{CM}	-2	А
Continuous Base Current	IB	-200	mA

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic	Symbol	Value	Unit	
Power Dissipation	(Note 6)	PD	500	mW
Thermal Resistance, Junction to Ambient	(Note 6)	R _{OJA}	250	°C/W
Thermal Resistance, Junction to Lead	(Note 7)	R _{ƏJL}	197	°C/W
Operating and Storage Temperature Range		T _{J,} T _{STG}	-55 to +150	°C

Notes: 6. For a device surface mounted on 15mm x 15mm FR4 PCB with high coverage of single sided 1 oz copper, in still air conditions; the device is measured when operating in a steady-state condition.

7. Thermal resistance from junction to solder-point (at the end of the collector lead).



Thermal Characteristics and Derating Information






Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

	• • •		_			
Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Collector-Base Breakdown Voltage	BV _{CBO}	-120	—	—	V	I _C = -100μA
Collector-Emitter Breakdown Voltage (Note 8)	BV _{CEO}	-100	—		V	$I_{\rm C} = -1 {\rm mA}$
Emitter-Base Breakdown Voltage	BV _{EBO}	-7	-	—	V	I _E = -100μA
Collector Cutoff Current	I _{СВО}	—	—	-100	nA	V _{CB} = -100V
Emitter Cutoff Current	I _{EBO}	—	—	-100	nA	$V_{EB} = -5.6V$
Collector-Emitter Cut-Off Current	ICES	-	-	-100	nA	V _{CES} = -100V
Static Forward Current Transfer Ratio (Note 8)	hfe	100 100 100 50	_	 300 		$\begin{split} I_{C} &= -1 \text{mA}, \ V_{CE} = -5 \text{V} \\ I_{C} &= -250 \text{mA}, \ V_{CE} = -5 \text{V} \\ I_{C} &= -500 \text{mA}, \ V_{CE} = -5 \text{V} \\ I_{C} &= -1 \text{A}, \ V_{CE} = -5 \text{V} \end{split}$
Collector-Emitter Saturation Voltage (Note 8)	V _{CE(sat)}	_	—	-200 -300	mV	I _C = - 250mA, I _B = -25mA I _C = - 500mA, I _B = -50mA
Base-Emitter Saturation Voltage (Note 8)	V _{BE(sat)}	—	—	-1.1	V	I _C = -500mA, I _B = -50mA
Base-Emitter Turn-On Voltage (Note 8)	V _{BE(on)}	-	—	-1.0	V	I _C = -1mA, V _{CE} = -5V
Transition Frequency	f _T	50	—	—	MHz	$V_{CE} = -10V, I_{C} = -50mA,$ f = 100MHz
Output Capacitance	C _{obo}	—	_	5	pF	V _{CB} = -10V, f = 1MHz

Notes: 8. Measured under pulsed conditions. Pulse width \leq 300µs. Duty cycle \leq 2%.




Typical Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)





Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.




SOT23 (Type DN)					
Dim	Min	Max	, Тур		
Α	0.89	1.12	1.00		
A1	0.01	0.10	0.05		
b	0.30	0.51	0.45		
С	0.08	0.20	0.10		
D	2.80	3.04	3.00		
Е	2.10	2.64	2.42		
E1	1.20	1.40	1.37		
е	0.95 REF				
e1	1.90 REF				
L	0.25	0.60	0.30		
L1	0.45	0.62	0.54		
All Dimensions in mm					

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23 (Type DN)



Dimensions	Value (in mm)
С	2.0
Х	0.8
X1	1.35
Y	0.9
Y1	2.9

SOT23 (Type DN)



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated

www.diodes.com