

21V, 2A, 1.2MHz, PWM Mode EA8212A Synchronous Buck Converter Datasheet Datasheet

General Description

The EA8212A is a pure PWM mode 2A buck regulator, designed to operate from 4.5V to 21V input voltage range. Built-in low R_{DS(ON)} high/low side Power-MOSFETS not only reduce external components and has up to 95% efficiency, ideal for 2A output current applications. The EA8212A has complete protection functions, including cycle-by-cycle current limit, short circuit protection, OVP and OTP protection. The internal compensation design not only allows users to more simplified application, and can reduce the cost of external components. The EA8212A is available in the SOT-23-6 package and easy to use.


Features

- Built-in Low R_{DS(ON)} Power-MOSFETS
- Efficiency Up to 95%
- PWM Mode Operating at Light Load and Heavy Load
- 4.5V to 21V Input Voltage Range
- Output Adjustable Down to 0.6V
- 2A Continuous Load Current
- Fixed 1.2MHz Switching Frequency
- Internal Compensation
- Cycle-by-Cycle Current Limit
- Auto Recovery Hiccup Mode Short Circuit Protection
- Shutdown Current < 1uA
- Output Over Voltage Protection
- Auto Recovery OTP Protection
- Available in SOT-23-6 Package

Applications

- Distributed Power Systems
- **Netcom Products**
- LCD TVs and Flat TV
- **Notebooks**

Pin Configurations













Datasheet

Pin Description

Pin Name	Function Description	Pin No.
воот	The power input of the internal high side N-MOSFET gate driver. Connect a 100nF ceramic capacitor from BOOT pin to SWITCH pin.	1
GND	Ground pin.	2
FBK	Feedback input. Connect FBK pin and GND pin with voltage dividing resistors to set the output voltage.	3
RUN	The device turns on/turns off control input. The EA8212A on/off state can be controlled by RUN pin voltage level. Don't leave the RUN pin in the floating state, connect RUN pin to ground with a $1M\Omega$ resistor for weak pull-down.	4
PWR	The EA8212A power input pin. Recommended to use two 10uF MLCC capacitors between PWR pin and GND pin.	5
SWITCH	Internal MOSFET switching output. Connect SWITCH pin with a low pass filter circuit to obtain a stable DC output voltage.	6

Function Block Diagram




Figure 1. EA8212A internal function block diagram



21V, 2A, 1.2MHz, PWM Mode Synchronous Buck Converter

Absolute Maximum Ratings

Parameter	Value
Input Voltage (V _{PWR})	-0.3V to +23V
RUN Pin Input Voltage (V _{RUN})	-0.3V to +23V
BOOT Pin Voltage (V _{BOOT})	V_{SWITCH} -0.3V to V_{SWITCH} +5V
SWITCH Pin Voltage (V _{SWITCH})	-1V to +23V
FBK Pin Voltage (V _{FBK})	-0.3V to +6V
Ambient Temperature operating Range (T _A)	-40°C to +85°C
Maximum Junction Temperature (T _{Jmax})	+150°C
Lead Temperature (Soldering, 10 sec)	+260°C
Storage Temperature Range (T _S)	-65°C to +150°C

Note (1):Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device.

Exposure to "Absolute Maximum Ratings" conditions for extended periods may affect device reliability and lifetime.

Package Thermal Characteristics

Parameter	Value
SOT-23-6 Thermal Resistance (θ _{JC})	125°C/W
SOT-23-6 Thermal Resistance (θ _{JA})	250°C/W
SOT-23-6 Power Dissipation at T _A =25°C (P _{Dmax})	0.5W

Note (1): P_{Dmax} is calculated according to the formula: $P_{DMAX}=(T_{JMAX}-T_A)/\theta_{JA}$.

Recommended Operating Conditions

Parameter	Value
Input Voltage (V _{PWR})	+4.5V to +21V
RUN Pin Input Voltage (V _{RUN})	-0.3V to +21V
Output Voltage (V _{OUT})	+0.6V to +12V
Junction Temperature Range (T _J)	-40°C to +125°C



Datasheet

Electrical Characteristics

 V_{PWR} =12V, T_A =25°C, unless otherwise noted

Parameter	Symbol	Test Conditions	Min	Тур	Max	Unit
Input Voltage	V_{PWR}		4.5		21	V
Shutdown Supply Current	I _{SD}	$V_{RUN} = 0V$		0.1	1	uA
Quiescent Current	IQ	$V_{RUN} = 2V$, $V_{FBK} = 105\% V_{REF}$, $I_{LOAD} = 0A$		400	600	uA
Output Load Current	I_{LOAD}				2	А
Reference Voltage	V_{REF}	4. 5V ≤ V _{PWR} ≤ 21V	0.588	0.6	0.612	V
Switching Frequency	F _{SW}			1.2		MHz
High Side MOSFET On-Resistance	R _{DS(ON)-HM}		. 2	95		mΩ
Low Side MOSFET On-Resistance	R _{DS(ON)-LM}	(80		mΩ
High Side MOSFET Current Limit	I _{LIM-HM}		3.5	4		Α
High Side MOSFET Leakage Current	I _{LEAK-HM}	V _{RUN} = 0V, V _{SWITCH} = 0V		1	10	uA
RUN Pin Input Low Voltage	V_{RUN-L}	4			0.4	V
RUN Pin Input High Voltage	V _{RUN-H}	0	2			V
Maximum Duty Cycle	D _{MAX}	$V_{FBK} = 0.5V$		92		%
High Side MOSFET Minimum On Time	TONMIN			60		ns
Thermal Shutdown Threshold	T _{OTP}			160		°C
Thermal Shutdown Hysteresis	T_{HYST}			30		°C

Note (1): MOSFET on-resistance specifications are guaranteed by correlation to wafer level measurements.

^{(2):} Thermal shutdown specifications are guaranteed by correlation to the design and characteristics analysis.



21V, 2A, 1.2MHz, PWM Mode Synchronous Buck Converter

Application Circuit Diagram




Figure 2. Typical application circuit diagram

Ordering Information

Part Number	Package Type	Packing Information
EA8212AT6R	SOT-23-6	Tape & Reel / 3000

Note (1):"T6": Package type code.


(2):"R": Tape & Reel.



Datasheet


Typical Operating Characteristics

 V_{PWR} =12V, V_{OUT} =3.3V, L1=4.7uH, C1=10uF, C2=22uF, T_A =25°C, unless otherwise noted





21V, 2A, 1.2MHz, PWM Mode Synchronous Buck Converter





Datasheet

Application Information

Enable Control

The EA8212A use RUN pin to control the regulator turns on / turns off. When the RUN pin input voltage is higher than 2V, the EA8212A enters the operating mode. Drive the RUN pin input voltage lower than 0.4V to ensure the EA8212A into shutdown mode. Don't leave the RUN pin in the floating state, connect RUN pin to ground with a $1M\Omega$ resistor for weak pull-down, as shown in Figure3. When the device works in the shutdown mode, the shutdown supply current is less than 1uA. The EA8212A also provides automatic startup function as shown in Figure 4. Connect RUN pin and PWR pin with a $150K\Omega$ resistor, when the PWR supply input voltage increasing and higher than RUN pin threshold voltage, the EA8212A will enter operating mode automatically.




Figure 3. Enable control by RUN pin voltage




Figure 4. Automatic startup application circuit

Output Voltage Setting

The EA8212A output voltage can be set via a resistor divider (R1, R2). The output voltage is calculated by following equation:

$$V_{\text{OUT}} = 0.6 \times \frac{R1}{R2} + 0.6 \text{ V}$$

The following table lists common output voltage and the corresponding R1, R2 resistance value for reference.

Output Voltage	R1 Resistance	R2 Resistance	Tolerance
5V	56ΚΩ	7.5ΚΩ	1%
3.3V	68ΚΩ	15ΚΩ	1%
1.8V	30ΚΩ	15ΚΩ	1%

Input / Output Capacitors Selection

The input capacitors are used to suppress the noise amplitude of the input voltage and provide a stable and clean DC input to the device. Because the ceramic capacitor has low ESR characteristic, so it is suitable for input capacitor use. It is recommended to use X5R or X7R MLCC capacitors in order to have better temperature performance and smaller capacitance tolerance. In order to suppress the output voltage ripple, the MLCC capacitor is also the best choice. The suggested part numbers of input / output capacitors are as follows:



21V, 2A, 1.2MHz, PWM Mode Synchronous Buck Converter

Vendor	Part Number	Capacitance	Edc	Parameter	Size
TDK	C2012X5R1C106K	10uF	16V	X5R	0805
TDK	C3216X5R1E106K	10uF	25V	X5R	1206
TDK	C2012X5R0J226K	22uF	6.3V	X5R	0805
TDK	C3216X5R1A226M	22uF	10V	X5R	1206

Output Inductor Selection

The output inductor selection mainly depends on the amount of ripple current through the inductor ΔI_{L} . Large ΔI_{L} will cause larger output voltage ripple and loss, but the user can use a smaller inductor to save cost and space. On the contrary, the larger inductance can get smaller ΔI_{L} and thus the smaller output voltage ripple and loss. But it will increase the space and the cost. The inductor value can be calculated as:

$$L = \frac{V_{PWR} - V_{OUT}}{\Delta I_L \times F_{SW}} \times \frac{V_{OUT}}{V_{PWR}}$$


For most applications, 4.7uH to 10uH inductors are suitable for EA8212A. The suggested part numbers of output inductors are as follows:

Vendor	Part Number	Inductance	DCR (Max.)	Saturation Current	Dimensions (mm) (WxLxH)
SUMIDA	CDRH8D38-4R7	4.7uH	29mΩ	4A	8x8x3.8
SUMIDA	CDRH8D43R-6R8	6.8uH	29.8mΩ	4.2A	8.3x8.5x4.5

PCB Layout Recommendations

For EA8212A PCB layout considerations, please refer to the following suggestions in order to get good performance.

- ► High current path traces (shown as below) need to be widened.
- Place the input capacitors as close as possible to the PWR pin to reduce noise interference.
- \blacktriangleright Keep the feedback path (from V_{OUT} to FBK) away from the noise node (ex. SWITCH).
- SWITCH is a high current noise node. Complete the layout by using short and wide traces.




^{*} Bold lines indicate high current paths




Datasheet

Package Information


SOT-23-6 Package








Side View



Recommended Layout Pattern



Front View

Symbol	Dime Min	Dimension Min Max		Dimension Typ
А	0.25	0.52	K	1.40
В	2.59	3.01	L	1.40
С	0.85	1.05	М	0.95
C1	1.70	2.10	N	0.65
D	1.40	1.80		
Е	2.70	3.10		
F	0.30	0.62		
G	0.08	0.25		
H	0.89	1.35		
H1)	0.89	1.20		

0.15

H2

0.00

Unit: mm