





SUPER BARRIER RECTIFIER

Product Summary

V _{RRM} (V)	I _O (A)	V _F Max (V) @ +25°C	I _R Max (mA) @ +25°C
60	2	0.51	0.15

Features and Benefits

- Optimized for Ultra-Low Forward Voltage Drop
- +175°C Operation Junction Temperature
- Lead-Free Finish; RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- PPAP Capable (Note 4)

Description and Applications

The SBR2U60S1FQ is a single rectifier packaged in SOD123F. Offering ultra-low V_F , low power loss, and high efficiency, this device is ideal for use in general rectification and applications as a:

- DC-DC Conversion
- AC-DC Rectification
- Reverse Polarity Protection
- SMPS

Mechanical Data

- Case: SOD123F
- Case Material: Molded Plastic, "Green" Molding Compound.
 UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Matte Tin Finish Annealed over Copper Leadframe.
 Solderable per MIL-STD-202, Method 208 (§3)
- · Polarity: Cathode Band
- Weight: 0.015 grams (Approximate)

SOD123F



Top View

Ordering Information (Note 5)

t-		
Part Number	Case	Packaging
SBR2U60S1FQ-7	SOD123F	3000/Tape & Reel


Notes:

- 1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
- 2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. Automotive products are AEC-Q101 qualified and are PPAP capable. Please refer to https://www.diodes.com/quality/.
- 5. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



H6 = Product Type Marking Code YM = Date Code Marking Y = Year (ex: F = 2018) M = Month (ex: 9 = September) Bar Denotes Cathode Pin



Date Code Key

Year	2013	2014	2015	2016	2017	2018	2019	2020
Code	Α	В	С	D	E	F	G	Н

Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	N	D



Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

Characteristic	Symbol	Value	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RRM} V _{RWM} V _{RM}	60	V
Average Rectified Output Current	Ιο	2	Α
Non-Repetitive Peak Forward Surge Current 8.3ms Single Half Sine-Wave Superimposed on Rated Load	I _{FSM}	35	А
Power Dissipation	P _{tot}	1.3	W

Characteristic	Symbol	Ratings	Unit
Human Body Mode ESD Protection	ESD HBM	4000	V
Machine Model ESD Protection	ESD MM	400	V
Charged Device Model	ESD CDM	1	kV

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Typical Thermal Resistance Junction to Ambient (Note 6) Typical Thermal Resistance Junction to Case (Note 6)	R _{OJA} R _{OJC}	115 40	°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +175	°C

Notes:

- 6. Device mounted on FR-4 substrate, 0.4" \times 0.5", 2oz, single-sided, PC boards with 0.2" \times 0.25" copper pad.
- 7. T_J = 175°C for operation when reverse dissipation does not lead to reverse leakage runaway. See Figure 4.

Electrical Characteristics ($@T_A = +25^{\circ}C$, unless otherwise specified.)


Characteristic	Symbol	Min	Тур	Max	Unit	Test Condition
Reverse Breakdown Voltage (Note 8)	$V_{(BR)R}$	60	_	_	V	$I_R = 1.0 \text{mA}$
		_	0.25	_		I _F = 0.1A, T _J = +25°C
		_	0.32	_		$I_F = 0.5A, T_J = +25^{\circ}C$
Forward Voltage Drop (Note 8)	VF	_	0.37	0.46	V	$I_F = 1A, T_J = +25^{\circ}C$
		_	0.44	0.51		$I_F = 2A, T_J = +25^{\circ}C$
		_	0.42	_		$I_F = 2A$, $T_J = +125$ °C
		_	15	_	μA	$V_R = 10V, T_J = +25$ °C
Leakage Current (Note 8)	I_R	_	50	150	μA	$V_R = 60V, T_J = +25$ °C
		_	11	25	mA	$V_R = 60V, T_J = +125$ °C
		_	125	_		$V_R = 4V, f = 1MHz$
Total Capacitance	Ст	_	75	_	pF	$V_R = 10V$, $f = 1MHz$
		_	35	_		$V_R = 60V$, $f = 1MHz$

Notes:


8. Short duration pulse test used to minimize self-heating effect.







V_F, INSTANTANEOUS FORWARD VOLTAGE (V) Figure 1. Typical Forward Characteristics







Figure 3 Forward Power Dissipation



V_R, INSTANTANEOUS REVERSE VOLTAGE (V) Figure 2. Typical Reverse Characteristics




Figure 4 DC Reverse Power Dissipation




Figure 6. Typical Junction Capacitance







Figure 7: Single pulse Max. Avalanche Energy and Current






Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOD123F




SOD123F						
Dim	Min	Max	Тур			
Α	0.81	1.15				
b	0.80	1.05				
C	0.05	0.30	_			
۵	1.70	1.90	1.80			
Е	2.60	2.80	2.70			
He	3.30	3.70	3.50			
L2	0.35	0.85				
All [Dimen	sions	in mm			

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOD123F



Dimensions	Value (in mm)
С	2.86
G	1.52
Х	1.34
X1	4.20
Υ	1.80



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated

www.diodes.com