ModSTACK™ HD

6MS30017E43W38169



Preliminary data


General information


IGBT Stack for typical voltages of up to 690 V_{RMS} Rated output current 1800 A_{RMS}

- High power converterWind powerMotor drives

- · PrimePACKTM3 module with integrated NTC
- · Extended operational temperature · Low V_{cesat}

Topology	B6I
Application	Inverter
Load type	Resistive, inductive
Semiconductor (Inverter Section)	9x FF1000R17IE4
DC Link	10.8 mF
Heatsink	Water cooled
Implemented sensors	Current, voltage, temperature
Driver signals IGBT	Optical HFBR-1521; HFBR-2521
Sales - name	6MS30017E43W38169
SP - No.	SP001036760





prepared by: OW	date of publication: 2012-08-24
approved by: AR	revision: 2.0

ModSTACK™ HD

6MS30017E43W38169



Preliminary data

Absolute maximum rated values

Collector-emitter voltage	IGBT; T _{vj} = 25°C	V _{CES}	1700	V
Repetitive peak reverse voltage	Diode; T _{vj} = 25°C	V_{RRM}	1700	V
DC link voltage		V _{DC}	1250	V
Insulation management	according to installation height of 2000 m	V _{line}	690	V _{RMS}
Insulation test voltage	according to EN 50178, f = 50 Hz, t = 1 s	V _{ISOL}	2.5	kV _{RMS}
Repetitive peak collector current inverter section (IGBT)	t _p = 1 ms	I _{CRM2}	4280	А
Repetitive peak forward current inverter section (Diode)	t _p = 1 ms	I _{FRM2}	4280	А
I²t-value inverter section (Diode)	V _R = 0 V, t _p = 10 ms, T _{vj} = 125 °C	l²t	378	kA²s
Continuous current inverter section		I _{AC2}	1800	A _{RMS}
Junction temperature	under switching conditions	T _{vjop}	150	°C
Switching frequency unit 3		f _{sw3}	3	kHz

Further maximum ratings are specified in the following dedicated sections

Characteristic values

DC Link			min.	typ.	max.	
Rated voltage		V _{DC}		1100	1200	V
Over voltage shutdown	within 150 μs			1250		V
Capacitor	1 s, 27 p, rated tol. ±10 %	C _{DC}		10.8		mF
		type		Foil		
Maximum ripple current	per device, T _{amb} = 55 °C	Iripple			49	ARMS
Balance or discharge resistor	per DC link unit	R₀		15.7		kΩ

Notes
Operation above 1100 V subject to reduced operating time according to EN 61071

Inverter Section			min.	typ.	max.	
Rated continuous current	$ \begin{array}{l} V_{DC} = 1100 \text{ V}, V_{AC} = 690 \text{ V}_{RMS}, cos(_{\phi}) = 0.85, \\ f_{AC \text{ sine}} = 50 \text{ Hz}, f_{sw} = 3000 \text{ Hz}, T_{inlet} = 40^{\circ}\text{C}, \\ T_{j} \leq 150 ^{\circ}\text{C} \end{array} $	I _{AC}			1800	A _{RMS}
Continuous current at low frequency	V_{DC} = 1100 V, V_{AC} = 690 V_{RMS} , $f_{AC sine}$ = 0 Hz, f_{sw} = 3000 Hz, T_{inlet} = 40 °C, T_{j} ≤ 150 °C	I _{AC low}			790	A _{RMS}
Rated continuous current for 150% overload capability	$I_{AC\ 150\%}$ = 1830 A_{RMS} , $t_{on\ over}$ = 60 s, $T_j \le 150\ ^{\circ}C$	I _{AC over1}			1220	A _{RMS}
Rated continuous current for 150% overload capability	$I_{AC\ 150\%}$ = 2000 A _{RMS} , $t_{on\ over}$ = 3 s, T_j ≤ 150 °C	I _{AC over2}			1330	A _{RMS}
Over current shutdown	within 15 μs	I _{AC OC}			4280	A _{peak}
Power losses	$\begin{array}{l} I_{AC} = 1800 \; A, \; V_{DC} = 1100 \; V, \; V_{AC} = 690 \; V_{RMS}, \\ \cos(_{(p)} = 0.85, \; f_{AC \; sine} = 50 \; Hz, \; f_{sw} = 3000 \; Hz, \\ T_{inlet} = 40 \; ^{\circ}C, \; T_{j} \leq 150 \; ^{\circ}C \end{array}$	P _{loss}		29200		W

prepared by: OW	date of publication: 2012-08-24
approved by: AR	revision: 2.0

ModSTACK™ HD

6MS30017E43W38169



Preliminary data

Controller interface

Driver and interface board	ref. to separate Application Note			DR110		
Optical interface board	ref. to separate Application Note			OEA101	1	
			min.	typ.	max.	
Auxiliary voltage		V _{aux}	18	24	30	V
Auxiliary power requirement	V _{aux} = 24 V	Paux		40		W
Digital input level	resistor to GND 1.8 kΩ, capacitor to GND 4 nF,	V _{in low}	0		4	V
3 1	logic high = on, min. 15 mA	V _{in high}	11		15	V
Digital output level	open collector, logic low = no fault, max. 15 mA	V _{out low}	0		1.5	V
		Vout high		15		V
Analog current sensor output inverter section	load max 1 mA, @ 1800 A _{RMS}	V _{IU} ana2 V _{IV} ana2 V _{IW} ana2	4.1	4.2	4.3	V
Analog DC link voltage sensor output	load max 1 mA, @ 1100 V	V _{DC ana}	7.7	7.9	8.1	V
Analog temperature sensor output inverter section (NTC)	load max 1 mA, @ T_{NTC} = 77 °C, corresponds to T_j = 147 °C at rated conditions	V _{Theta NTC2}		8.8		V
Analog temperature sensor output inverter section (Simulated)	load max 1 mA, @T _{NTC} = 77 °C, corresponds to T _j = 147 °C at rated conditions	V _{Theta sim2}		9.2		V
Over temperature shutdown inverter section		V _{Error OT2}		9.4		V
Optical input power		P _{opt in}		12		μW
Optical output power		P _{opt out}			60	μW

System data				min.	typ.	max.	
EMC robustness	according to 61800-3 at named interfaces	power	V_{Burst}		2		kV
		control	V _{Burst}		1		kV
		aux (24V)	V _{surge}		1		kV
Storage temperature			T _{stor}	-40		80	°C
Operational ambient temperature	PCB, DC link capacitor, bus bar, excluding omedium	cooling	T _{op amb}	-25		55	°C
Cooling air velocity	PCB, DC link capacitor, bus bar, standard atmosphere		Vair	2			m/s
Humidity	no condensation		Rel. F	0		95	%
Vibration	according to IEC 60721					5	m/s²
Shock	according to IEC 60721					40	m/s²
Protection degree					IP00		
Pollution degree					2		
Dimensions	width x depth x height			1090	596	342	mm
Weight					172		kg

prepared by: OW	date of publication: 2012-08-24
approved by: AR	revision: 2.0

ModSTACK™ HD

6MS30017E43W38169



Preliminary data

Heatsink water cooled			min.	typ.	max.	
Water flow	according to coolant specification from Infineon	ΔV/Δt	45			dm³/min
Water pressure					8	bar
Water pressure drop	at 45 dm³/min water flow	Δp		200		mbar
Coolant inlet temperature		T _{inlet}	-40		55	°C
Thermal resistance heatsink to ambient	per switch	R _{th,ha}		0.038		K/W
Cooling channel material				Copper	•	

Composition of coolant: Water and 52 vol. % Antifrogen N

Overview of optional components	Unit 1	Inverter Section	Unit 3
Parallel interface board			
Optical interface board		×	
Voltage sensor		×	
Current sensor		×	
Temperature sensor		×	
Temperature simulation		×	
DC link capacitors		×	
Collector-emitter Active Clamping		×	

Notes
Setting of Active Clamping TVS-Diodes: V_Z = 1280 V

prepared by: OW	date of publication: 2012-08-24
approved by: AR	revision: 2.0

ModSTACK™ HD


6MS30017E43W38169




Preliminary data

 $f_{AC\;sine}$ - derating curve IGBT (motor), Diode (generator) V_{DC} = 1100 V, V_{AC} = 690 $V_{RMS},\,f_{sw}$ = 3 kHz, cos_{ϕ} = ± 0.85 T_{inlet} = 40°C and nom. cooling conditions


 f_{sw} - derating curve IGBT (motor), Diode (generator) V_{DC} = 1100 V, V_{AC} = 690 $V_{\text{RMS}},$ $f_{\text{AC sine}}$ = 50 Hz, \cos_ϕ = ± 0.85 T_{inlet} = 40°C and nom. cooling conditions






 T_{inlet} - derating curve IGBT (motor), Diode (generator) V_{DC} = 1100 V, V_{AC} = 690 $V_{RMS},\,f_{AC\,\,\text{sine}}$ = 3 kHz, $f_{AC\,\,\text{sine}}$ = 50 Hz cos_{ϕ} = ±0.85 and nom. cooling conditions

Analog temperature sensor output $V_{\text{Theta NTC}}$ Sensing NTC of IGBT module





prepared by: OW	date of publication: 2012-08-24
approved by: AR	revision: 2.0

ModSTACK™ HD


6MS30017E43W38169




Preliminary data


 $T_{vj,sim}$ vs. I_{AC} - Simulated junction temperature V_{DC} = 1100 V, V_{AC} = 690 $V_{RMS},\,f_{sw}$ = 3 kHz T_{inlet} = 40°C and nom. cooling conditions

Analog temperature sensor output $V_{\text{Theta sim}}$ $V_{\text{DC}} = 1100 \text{ V}$, $V_{\text{AC}} = 690 \text{ V}_{\text{RMS}}$, $f_{\text{sw}} = 3 \text{ kHz}$, $T_{\text{inlet}} = 40^{\circ}\text{C}$ and nom. cooling conditions





 $Z_{\text{th,ha}} \text{ - thermal impedance heatsink to ambient per switch} \\ \text{nom. cooling conditions}$



prepared by: OW	date of publication: 2012-08-24
approved by: AR	revision: 2.0


ModSTACK™ HD

6MS30017E43W38169



Preliminary data

Mechanical drawing



prepared by: OW	date of publication: 2012-08-24
approved by: AR	revision: 2.0

ModSTACK™ HD


6MS30017E43W38169



Preliminary data

Circuit diagram

approved by: AR



revision: 2.0

ModSTACK™ HD

6MS30017E43W38169



Preliminary data

Terms & Conditions of usage

The data contained in this product data sheet is exclusively intended for technically trained staff. You and your technical departments will have to evaluate the suitability of the product for the intended application and the completeness of the product data with respect to such application.

This product data sheet is describing the characteristics of this product for which a warranty is granted. Any such warranty is granted exclusively pursuant the terms and conditions of the supply agreement. There will be no guarantee of any kind for the product and its characteristics.

Should you require product information in excess of the data given in this product data sheet or which concerns the specific application of our product, please contact the sales office, which is responsible for you (see www.infineon.com, sales&contact). For those that are specifically interested we may provide application notes.

Due to technical requirements our product may contain dangerous substances. For information on the types in question please contact the sales office, which is responsible for you.

Should you intend to use the Product in aviation applications, in health or live endangering or life support applications, please notify. Please note, that for any such applications we urgently recommend

- to perform joint Risk and Quality Assessments;
- the conclusion of Quality Agreements;
- to establish joint measures of an ongoing product survey, and that we may make delivery depended on the realization of any such measures.

If and to the extent necessary, please forward equivalent notices to your customers.

Changes of this product data sheet are reserved.

Safety Instructions

Prior to installation and operation, all safety notices and warnings and all warning signs attached to the equipment have to be carefully read. Make sure that all warning signs remain in a legible condition and that missing or damaged signs are replaced. To installation and operation, all safety notices and warnings and all warning signs attached to the equipment have to be carefully read. Make sure that all warning signs remain in a legible condition and that missing or damaged signs are replaced.

prepared by: OW	date of publication: 2012-08-24
approved by: AR	revision: 2.0