
#### **FEATURES**

- 3.3V, 5V, 12V, and adjustable output versions
- Adjustable version output voltage range
- Guaranteed 5A output load current
- Input voltage range up to 40V
- 300KHz fixed frequency internal oscillator
- Excellent line and load regulation
- Thermal shutdown and current limit protection



- Simple high-efficiency step-down regulator
- On-card switching regulators
- Positive to negative converter



ORDERING INFORMATION

| Device        | Package   |
|---------------|-----------|
| LM1501BGR-X.X | TO-263-5L |
| LM1501BGT-X.X | TO-220-5L |

X.X = Output Voltage = 3.3, 5.0, 12, ADJ

#### **DESCRIPTION**

The LM1501BG series of regulators are monolithic integrated circuits that provide all the active functions for a step-down switching regulator, capable of driving a 5A load with excellent line and load regulation. These devices are available in fixed output voltages of 3.3V, 5V, 12V and an adjustable output version. Requiring a minimum number of external components, these regulators are simple to use and they include internal frequency compensation and a fixed-frequency oscillator. The LM1501BG series operates at a switching frequency of 300kHz thus allowing smaller sized filter components than what would be needed with lower frequency switching regulators.

Other features include a guaranteed  $\pm 4\%$  tolerance on output voltage under specified input voltage and output load conditions, and  $\pm 15\%$  on the oscillator frequency. External shutdown is included, featuring typically 80uA standby current. Self-protection features include a two stage frequency reducing current limit for output switch and an over temperature shutdown for complete protection under fault conditions.

# **ABSOLUTE MAXIMUM RATINGS** (Note 1)


| CHARACTERISTIC                          | SYMBOL              | VALUE              | UNIT |
|---|---------------------|--------------------|------|
| Maximum Input Supply Voltage            | $V_{IN\_MAX}$       | 45                 | V    |
| ON/OFF Pin Input Voltage                | V <sub>ON/OFF</sub> | -0.3 ≤ V ≤ +25     | V    |
| Feedback Pin Voltage                    | $V_{FB}$            | -0.3 ≤ V ≤ +25     | V    |
| Output Voltage to Ground (Steady State) | V <sub>OUT</sub>    | -1                 | V    |
| Power Dissipation                       | P <sub>D</sub>      | Internally limited | W    |
| Storage Temperature Range               | T <sub>STG</sub>    | -65 to +150        | °C   |
| Operating Temperature Range             | T <sub>J</sub>      | 150                | °C   |

## **RECOMMENDED OPERATING CONDITIONS**


| CHARACTERISTIC       | SYMBOL          | MIN. | MAX. | UNIT       |
|----------------------|-----------------|------|------|------------|
| Supply Voltage       | V <sub>IN</sub> | -    | 40   | V          |
| Load Current         | ILOAD           | -    | 5    | Α          |
| Junction Temperature | TJ              | -40  | 125  | $^{\circ}$ |

## **ORDERING INFORMATION**

| VOUT  | PACKAGE   | ORDER NO.     | DESCRIPTION | STATUS     |
|-------|-----------|---------------|-------------|------------|
|       | TO-263-5L | LM1501BGR-ADJ | 5A, 300KHz  | Active     |
| ADJ   | TO-220-5L | LM1501BGT-ADJ | 5A, 300KHz  | Active     |
| 3.3V  | TO-263-5L | LM1501BGR-3.3 | 5A, 300KHz  | Contact Us |
|       | TO-220-5L | LM1501BGT-3.3 | 5A, 300KHz  | Contact Us |
| 5.0)/ | TO-263-5L | LM1501BGR-5.0 | 5A, 300KHz  | Contact Us |
| 5.0V  | TO-220-5L | LM1501BGT-5.0 | 5A, 300KHz  | Contact Us |
| 12V   | TO-263-5L | LM1501BGR-12  | 5A, 300KHz  | Contact Us |
|       | TO-220-5L | LM1501BGT-12  | 5A, 300KHz  | Contact Us |



## **PIN CONFIGURATION**




TO-263-5L TO-220-5L

## **PIN DESCRIPTION**


| PIN NO. | TO-263-5L / TO-220-5L PKG |                                 |  |  |
|---------|---------------------------|---------------------------------|--|--|
| FIN NO. | NAME                      | FUNCTION                        |  |  |
| 1       | VIN                       | Operating Input Voltage         |  |  |
| 2       | OUTPUT                    | Switching Output Voltage        |  |  |
| 3       | GND                       | Ground                          |  |  |
| 4       | FB                        | Output Voltage Feedback Control |  |  |
| 5       | ON/OFF                    | ON/OFF Shutdown                 |  |  |

# **TYPICAL APPLICATION**

- Fixed Output Voltage Version



- Adjustable Output Voltage Version



# **ELECTRICAL CHARACTERISTICS**


Specification with standard type face are for  $T_J$ =25°C, and those with **boldface type** apply over **full Operating Temperature Range**. Unless otherwise specified,  $V_{IN}$ =12V for the 3.3V, 5V, and Adjustable version and  $V_{IN}$ =24V for the 12V version.  $I_{LOAD}$ =500mA


| CHARACTERISTIC               | SYMBOL          | TEST CONDITION                                 |   | MIN.<br>(Note 3) | TYP.<br>(Note 2) | MAX.<br>(Note 3)    | UNIT     |
|------------------------------|-----------------|--|---|------------------|------------------|---------------------|----------|
| SYSTEM PARAMETERS (Note 4    | )               |  |   |                  | T                |                     |          |
|                              |                 | LM1501BG-ADJ                                   | V <sub>IN</sub> =12V, I <sub>LOAD</sub> =5A                         |                  | 80               |                     |          |
|                              |                 | LM1501BG-3.3                                   | V <sub>IN</sub> =12V, I <sub>LOAD</sub> =5A                         |                  | 70               |                     | %        |
| Efficiency                   | η               | LM1501BG-5.0                                   | V <sub>IN</sub> =12V, I <sub>LOAD</sub> =5A                         |                  | 75               |                     |          |
|                              |                 | LM1501BG-12                                    | V <sub>IN</sub> =18V, I <sub>LOAD</sub> =5A                         |                  | 85               |                     |          |
|                              |                 | LM4504DO 2 2                                   | 5.5V ≤ V <sub>IN</sub> ≤ 40V  | 3.168            | 2.2              | 3.432               | <u> </u> |
|                              |                 | LM1501BG-3.3                                   | 0.2A ≤ I <sub>LOAD</sub> ≤ 5A                                       | 3.135            | 3.3              | 3.465               |          |
| Outrat Valle as              |                 | LM4504DO 5 0                                   | 8V ≤ V <sub>IN</sub> ≤ 40V  | 4.800            | 5.0              | 5.200               | V        |
| Output Voltage               | Vout            | LM1501BG-5.0                                   | 0.2A ≤ I <sub>LOAD</sub> ≤ 5A                                       | 4.750            | 5.0              | 5.250               |          |
|                              |                 | 111150100 10                                   | 15V ≤ V <sub>IN</sub> ≤ 40V   | 11.520           | 40               | 12.480              |          |
|                              |                 | LM1501BG-12                                    | 0.2A ≤ I <sub>LOAD</sub> ≤ 5A                                       | 11.400           | 12               | 12.600              |          |
| Feedback Voltage             |                 |  | 5.2V ≤ V <sub>IN</sub> ≤ 40V  | 1.193            | 1.23             | 1.267               | -<br>V   |
|                              | V <sub>FB</sub> | LM1501BG-ADJ                                   | 0.2A ≤ I <sub>LOAD</sub> ≤ 5A<br>V <sub>OUT</sub> programmed for 3V | 1.180            |                  | 1.280               |          |
| DEVICE PARAMETERS            | •               | •  |   |                  |                  |                     |          |
|                              |                 |  |   |                  | 15               | 50                  |          |
| Feedback Bias Current        | I <sub>FB</sub> | Adjustable Version Only, V <sub>FB</sub> =1.3V |   |                  |                  | 100                 | nA       |
| Ossillatas Fassus assu       | _               | (Nata 5)                                       |   | 255              | 300              | 345                 |          |
| Oscillator Frequency         | Fo              | (Note 5)                                       |   | 235              |                  | 365                 | kH       |
| Saturation Voltage           | Vsat            | I <sub>OUT</sub> =5A (Note 6, 7)               |   |                  | 1.65             | 1.85<br><b>2.00</b> | ٧        |
| Max Duty Cycle (ON)          |                 | (Note 7)                                       |   |                  | 100              | 2.00                |          |
| Max Duty Cycle (ON)          | DC              | I <sub>LOAD</sub> ≥ 4A                         |   |                  | 50               |                     | %        |
| Min Duty Cycle (OFF)         | •               | (Note 8)                                       |   |                  | 0                |                     |          |
| Current Limit                | I <sub>CL</sub> | Peak Current (Note 6,                          | 7)  |                  | 6.9              |                     | Α        |
| Γhermal Shutdown Temperature | T <sub>SD</sub> | (Note 10)                                      |   |                  | 185              |                     | °C       |
|                              |                 | Output=0V (Note 6, 8)                          | Output=0V (Note 6, 8)   |                  |                  | 50                  | μΑ       |
| Output Leakage Current       | lι              | Output=-1V (Note 9)                            |   |                  | 10               | 30                  | m/       |
| Quiescent Current            | lα              | (Note 8)                                       |   |                  | 5                | 10                  | m/       |
|                              |                 | ON/OFF pin = 5V(OFF) (Note 9)                  |   |                  | 80               | 200                 |          |
| Shutdown Current             | Ishutdown       |  |   |                  |                  | 250                 | μA       |


| ON/OFF CONTROL                           |                 |   |     |      |     |    |
|--|-----------------|---|-----|------|-----|----|
|  |                 |   |     | 1.3  |     |    |
| ON/OFF Pin Logic Input Threshold voltage | V <sub>IH</sub> | Low (Regulator ON)                        |     |      | 0.6 | ٧  |
| Threshold voltage                        | V <sub>IL</sub> | High (Regulator OFF)                      | 2.0 |      |     |    |
| ON/OFF Pin Logic Input                   | lн              | V <sub>LOGIC</sub> = 2.5V (regulator OFF) |     | 5    | 15  |    |
| current                                  | IL              | V <sub>LOGIC</sub> = 0.5V (regulator ON)  |     | 0.02 | 5   | uA |


- Note 1. Absolute Maximum Rating indicate limits beyond which damage to the device may occur. Operating Ratings indicate condition for which the device is intended to be functional, but do not guarantee specific performance limits. For guaranteed specifications and test conditions, see the Electrical Characteristics.
- **Note 2:** Typical numbers are at  $25^{\circ}$ ° and represent the most likely norm.
- Note 3: All limits guaranteed at room temperature (standard type face) and at temperature extremes (bold type face).
- **Note 4:** External components such as the schottky diode, inductor, input and output capacitors, and voltage programming resistors can affect switching regulator system performance. When the LM1501BG is used as shown in the typical circuit, system performance will be as shown in system parameters section of Electrical Characteristics.
- Note 5: The switching frequency is reduced when the second stage current limit is activated. The amount of reduction is determined by the severity of current over-load.
- Note 6: No diode, inductor or capacitor connected to output pin.
- Note 7: Feedback pin removed from output and connected to 0V to force the output transistor switch ON.
- Note 8: Feedback pin removed from output and connected to 12V for the 3.3V, 5V, and the ADJ version, and 15V for the 12V version, to force the output transistor switch OFF.
- Note 9: VIN = 40V.
- Note 10: Guaranteed by design, not tested.


# TYPICAL OPERATING CHARACTERISTIC






















#### **APPLICATION INFORMATION**

As in any switching regulator, layout is very important. Rapidly switching currents associated with wiring inductance generate voltage transients which can cause problems. For minimal inductance and ground loops, the length of the wires should be kept as short as possible. Single-point grounding or ground plane construction should be used for best results. Keep the feedback wiring away from the inductor flux

#### - Fixed Output Voltage Version



#### - Adjustable Output Voltage Version



\* 
$$V_{OUT} = V_{FB}(1 + \frac{R1}{R2})$$
, Where  $V_{FB} = 1.23V$ 

# 5A, 300KHz, Step-Down Switching Regulator

**LM1501BG** 

# **REVISION NOTICE**

The description in this datasheet can be revised without any notice to describe its electrical characteristics properly.