

DATASHEET

SMD • A 95-21UYC/S530-A3/TR7



Features

- Package in 12mm tape on 7" diameter reel.
- Compatible with automatic placement equipment.
- EIA Std. package.
- Mono-color type.
- Pb-free.
- RoHS compliant
- Compliance with EU REACH.
- Compliance Halogen Free .(Br <900 ppm ,Cl <900 ppm , Br+Cl < 1500 ppm)

Description

- The 95-21 SMD LED is much smaller than leaded components . Thus enable smaller board size. Higher packing density. Reduced storage space and finally smaller equipment to be obtained.
- Besides, light weight makes them ideal for miniature applications.
- Furthermore by automation assembly machines the accuracy is anticipated.

Applications

- Small indicator for indoor applications.
- Flat backlight for LCD, switches and symbols.
- Indicator and backlight in office equipment.
- Indicator and backlight for battery driven equipment.
- Indicator and backlight for audio and video equipment.
- Backlighting in dashboards and switches.
- Telecommunication : indicator and backlighting in telephone and fax.

Device Selection Guide

Chip Materials	Emitted Color	Resin Color
AlGaInP	Brilliant Yellow	Water Clear

Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit		
Reverse Voltage	V _R	5	V		
Forward Current	I _F	20	mA		
Peak Forward Current (Duty 1/10 @1KHz)	I _{FP}	60	mA		
Power Dissipation	Pd	60	mW		
Operating Temperature	T _{opr}	-40 ~ +85	C		
Storage Temperature	Tstg	-40 ~ +90	Ĵ		
Electrostatic Discharge	ESD _{HBM}	2000	V		
Soldering Temperature	T _{sol}	Reflow Soldering : 260 $^\circ\!\!\mathbb{C}$ for 10 sec. Hand Soldering : 350 $^\circ\!\!\mathbb{C}$ for 3 sec.			


Electro-Optical Characteristics (Ta=25°C)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Luminous Intensity	lv	463	714		mcd	I _F =20mA
Viewing Angle	20 _{1/2}		25		deg	I _F =20mA
Peak Wavelength	λр		591		nm	I _F =20mA
Dominant Wavelength	λd		589		nm	I _F =20mA
Spectrum Radiation Bandwidth	$\Delta\lambda$		15		nm	I _F =20mA
Forward Voltage	V_{F}		2.0	2.4	V	I _F =20mA
Reverse Current	I _R			10	μA	V _R =5V

Notes:


- 1. Tolerance of Luminous Intensity: ±11%.
- 2. Tolerance of Forward Voltage : ±0.05V.
- 3. Tolerance Color Rendering Index : ± 2

Typical Electro-Optical Characteristics Curves





Package Outline Dimensions




Note: The tolerances unless mentioned are ± 0.1 , unit=mm.




Package Outline Dimensions

Label Explanation




- CPN: Customer's Product Number
- P/N: Product Number
- LOT No: Lot Number
- QTY: Packing Quantity
- CAT: Luminous Intensity Rank
- HUE: Dom. Wavelength Rank
- REF: Forward Voltage Rank

Reel & Carrier Tape Dimensions



Note: The tolerances unless mentioned are ±0.1, unit=mm


Loaded quantity 1000 PCS per reel





Note: The tolerances unless mentioned are ± 0.1 , unit=mm.


Moisture Resistant Packaging











Aluminum moisture-proof bag

Desiccant



Precautions For Use

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big

current change (Burn out will happen).

- 2. Storage
- 2.1 Do not open moisture proof bag before the products are ready to use.
- 2.2 Before opening the package: The LEDs should be kept at 30° C or less and 90%RH or less.
- 2.3 After opening the package: The LED's floor life is 72 hours under 30° C or less and 60% RH or less.


If unused LEDs remain, it should be stored in moisture proof packages.

2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the

storage time, baking treatment should be performed using the following conditions.

Baking treatment : $60\pm5^{\circ}$ C for 24 hours.

- 3. Soldering Condition
- 3.1 Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

4.Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350° C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.