

## Filterless 25W Class F Mono Audio Amplifier

### **General Description**

The LPA2110A is a 25W, class F mono audio amplifier integrated Class AB/D optional mode. It is capable of delivering 25watts of continuous average power to a  $4\Omega$  BTL load with less than 10% distortion (THD) from a 14.5V DC power supply. It offers low THD+N, allowing it to achieve high-quality Power Supply sound reproduction. The LPA2110A device is fully protected against faults with short-circuit protection and thermal protection as well as over-voltage and DC protection. Faults are reported back to the processor to prevent devices form being damaged during overload conditions.

### **Order Information**



## **Applications**

- Mini-Micro Component, Speaker Bar, Docks
- ♦ After-Market Automotive
- ♦ Consumer Audio Applications, CRT TV
- ♦ Portable Bluetooth Speaker
- ♦ Square Speaker


### **Features**

- ♦ Wide voltage range: 4V~15.5V
- ◆ 550KHz fixed frequency switching for amplifier
- 25W Output at 10% THD with a 4Ω Load and 14.5V
   VDD for amplifier
  - 15W Output at 1% THD with a  $4\Omega$  Load and 12V VDD for amplifier
- Integrated Self-Protection Circuits Including Over-Voltage, Under-Voltage, Over-Temperature, DC-Detect, and Short Circuit
- ◆ High Efficient Class-D Operation: >86%
- Filterless, Low Quiescent Current and Low EMI
- Pb-Free Package


### **Marking Information**

Device	Marking	Package	Shipping			
	LPS					
LPA2110ASPF	LPA2110A	ESOP-8	4K/REEL			
	YWX					
Y: Y is year code. W: W is week code. X: X is series number.						

### **Typical Application Circuit**



## Pin Configuration(TOP View)



## **Functional Pin Description**

Pin Num.	Pin Name	Description					
	CTDI	Shutdown and Class AB, Class D control. Shutdown:0-0.6V; Class AB:0.7-1V; Class					
1	CTRL	D:1.5V-VDD.					
2	NC	No connection.					
3	IN+	Positive input of amplifier.					
4	IN-	Negative input of amplifier.					
5	OUT+	Positive output of signal.					
6	VDDP Sem	Voltage supply pin.					
7	GND	Ground.					
8	OUT-	Negative output of signal.					
9	Thermal PAD	Power Ground.					

# **Absolute Maximum Ratings** Note 1

<b></b>	Supply Voltage to GND
<b></b>	Other Pin to GND
<b></b>	Maximum Junction Temperature 155°C
<b></b>	Operating Ambient Temperature Range (Ta)
<b></b>	Maximum Soldering Temperature (at leads, 10 sec) 260°C

**Note 1.** Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

### **Thermal Information**

- ♦ Maximum Power Dissipation (ESOP-8, PD,TA=25°C) ------ 1.9W
- ♦ Thermal Resistance (ESOP-8, JA) ------ 65°C/W

## **ESD Susceptibility**

- ♦ HBM(Human Body Mode) ------ 2KV
- MM(Machine Mode) ------ 200V



### **Electrical Characteristics**


(T<sub>A</sub> = 25°C, VDD = 12V, R<sub>L</sub> = 4  $\Omega$ , unless otherwise noted)

Parameter	Symbol	Test Conditions	Min	Тур	Max	Units	
Supply power	VDD			4		15.5	V
		TUD N. 4007 ( 417) D. 40	VDD=15V		29		
		THD+N=10%, f=1KHz,RL=4Ω	VDD=12V		19		
			VDD=15V		16		
Output power	Po	THD+N=10%, f=1KHz,RL=8Ω	VDD=12V		10		W
Output power	FO	TUD.N. 407 £ 4174- DL 40	VDD=15V		24		VV
		THD+N=1%, f=1KHz,RL=4Ω	VDD=12V		15		
		TUD (N_40/ f_4KU-7 DI _00	VDD=15V		13		
		THD+N=1%, f=1KHz,RL=8Ω	VDD=12V		8.5		
Power supply ripple	PSRR	INPUT ac-grounded with	f=100HZ		-70		dB
rejection	FORK	CIN=0.47uF, VDD=12V	f=1KHz		-73		G
Signal-to-noise ratio	SNR	VDD=12V, $P_{OUT}$ =12W, $R_{L}$ =4 $\Omega$	f=1KHz		95		dB
Output integrated noise	Vn	22 Hz to 20kHz, A-weighted filter, THD=1%,RL=4 Ω			130		μ <b>V</b>
Eifficency	H U W	$R_L=4\Omega, P_O=10W$	f=1KHz	- B2	86		%
Quiescent current	ΙQ	VDD=12V	No load		25		mA
Shutdown current	I <sub>SD</sub>	VDD=12V,V <sub>SD</sub> =0			12		uA
Shutdown voltage	Vctrl_sd	VDD=12V		0		0.6	
Class AB voltage	V <sub>CTRL_AB</sub>	VDD=12V		0.7		1	V
Class D voltage	V <sub>CTRL_D</sub>	VDD=12V		1.5			
Offset output voltage	Vos	VDD=12V, V <sub>SD</sub> =0V		6		mV	
fosc Oscillator frequency	fsw			550		KHz	
start-up time	Ton	SD from low to high			180		ms
Thermal shutdown	OTP	Threshold			155		%
Thermal shutdown Hysteresis	ОТРН	Hysteresis			135		$^{\circ}$

LPA2110A-00

Jan.2019

## **Test setup for graphs**




- 1. Ci was shorted for any common-mode input voltage measurement. All other measurements were taken with Ci = 1µF (unless otherwise noted).
- 2. Cs1 = 0.1  $\mu$ F is placed very close to the device. The optional Cs2 = 10  $\mu$ F is used for datasheet graphs.
- 3. The 30 kHz low-pass filter is required even if the analyzer has an internal low-pass filter. An RC low-pass filter (1 k $\Omega$ , 4700pF) is used on each output for the data sheet graphs.

## **Typical Operating Characteristic For Amplifier**

#### PO VS THD

#### **Audio Precision**




Sweep	Trace	Color	Line Style	Thick	Data	Axis	Comment
1	1	Cyan	Solid	3	Analyzer.THD+N Ratio A	Left	VDD=6V,RL=4ohm
2	1	Green	Solid	3	Analyzer.THD+N Ratio A	Left	VDD=7.4V,RL=4ohm
3	1	Yellow	Solid	3	Analyzer.THD+N Ratio A	Left	VDD=8.4V,RL=4ohm
4	1	Red	Solid	3	Analyzer.THD+N Ratio A	Left	VDD=9V,RL=4ohm
5	1	Magenta	Solid	3	Analyzer.THD+N Ratio A	Left	VDD=12V,RL=4ohm
6	1	Blue	Solid	3	Analyzer.THD+N Ratio A	Left	VDD=15V,RL=4ohm

PO VS THD@4ohm.ats2

LPA2110A-00

Jan.2019

#### Audio Precision




Sweep	Trace	Color	Line Style	Thick	Data	Axis	Comment
1	1	Cyan	Solid	3	Analyzer.THD+N Ratio A	Left	VDD=6V,RL=8ohm
2	1	Green	Solid	3	Analyzer.THD+N Ratio A	Left	VDD=7.4V,RL=8ohm
3	1	Yellow	Solid	3	Analyzer.THD+N Ratio A	Left	VDD=8.4V,RL=8ohm
4	1	Red	Solid	3	Analyzer.THD+N Ratio A	Left	VDD=9V,RL=8ohm
5	1	Magenta	Solid	3	Analyzer.THD+N Ratio A	Left	VDD=12V,RL=8ohm
6	1	Blue	Solid	3	Analyzer.THD+N Ratio A	Left	VDD=15V,RL=8ohm

PO VS THD@8ohm.ats2

### Frequency response | Semi

#### **Audio Precision**



Sweep	Trace	Color	Line Style	Thick	Data	Axis	Comment
5 6	1	Blue Cyan	Solid Solid	3 3	•		VDD=9V,RL=4ohm,Class D,THD=1% VDD=9V,RL=4ohm,Class D,THD=10%

LPA2110A-00

Jan.2019

19 I

Email: marketing@lowpowersemi.com

www.lowpowersemi.com

Page 5 of 10

## **Applications Information**

#### Maximum Gain

The LPA2110A has two internal amplifier stages. The first stage's gain is externally configurable, while the second stage's is internally fixed. The closed-loop gain of the first stage is set by selecting the ratio of Rf to Ri while the second stage's gain is fixed at 2x. The output of amplifier 1 serves as the input to amplifier 2, thus the two amplifiers produce signals identical in magnitude, but different in phase by 180°. Consequently, the differential gain for the IC is

 $A_V = 20 \log [2 Rf/(Ri + 6)]$ 

Class AB: Rf= 100 k Ω±10%

Class D: Rf= 250 k Ω±10%

#### Shutdown operation

In order to reduce power consumption while not in use, the LPA2110A contains shutdown circuitry to turn off the amplifier's bias circuitry. This shutdown feature turns the amplifier off when logic low is applied to the SD pin.

#### Power supply decoupling

Power supply leads. For higher frequency transients, spikes, or digital hash on the line, a good low equivalent-series-resistance (ESR) ceramic capacitor, typically 1.0μF, works best, placing it as close as possible to the device VDD terminal. For filtering lower- frequency noise signals, a large capacitor of 20μF (ceramic) and a capacitor of 220uF(electrolytic) are recommended, placing them near the audio power amplifier.

#### **Short Circuit Protection (SCP)**

The LPA2110A has short circuit protection circuitry on the outputs to prevent damage to the device when output-to-output or output-to-GND short occurs. When a short circuit is detected on the outputs, the outputs are disabled immediately. If the short was removed, the device activates again.

#### Input Capacitor (Ci)

Ci for signal input. Large input capacitors are both expensive and space hungry for portable designs. Clearly, a certain sized capacitor is needed to couple in low frequencies without severe attenuation. But in many cases the speakers used in portable systems, whether internal or external, have little ability to reproduce signals below 100Hz to 150Hz. In the typical application, an input capacitor Ci is required to allow the amplifier to bias the input signal to the proper dc level for optimum operation. Thus, using a large input capacitor may not increase actual system performance. In this case, input capacitor (Ci) and input resistance (Ri) of the amplifier form a high-pass filter with the corner frequency determined by equation below,

$$f_C = \frac{1}{2\pi RiCi}$$

### **Over Temperature Protection**

Thermal protection on the LPA2110A prevents the device from damage when the internal die temperature exceeds 155°C. There is a ± 15°C tolerance on this trip point from device to device.

Preliminary Datasheet LPA2110A


Once the die temperature exceeds the thermal set point, the device outputs are disabled. This is not a latched fault. The thermal fault is cleared once the temperature of the die is reduced by 20°C. This large hysteresis will prevent motor boating sound well and the device begins normal operation at this point without external system intervention.

#### How to reduce EMI

A simple solution is to put an additional capacitor at power supply terminal for power line. The traces from amplifier to speakers should design as short as we can. The LPA2110A has been tested with a simple ferrite bead filter for a variety of applications. The LPA2110A EVM passes FCC class-B specifications under these conditions using twisted speaker wires. The size and type of ferrite bead can be selected to meet application requirements. Also, the filter capacitor can be increased if necessary with some impact on efficiency. There may be a few circuit instances where it is necessary to add a LC complete reconstruction filter. These circumstances might occur if there are nearby circuits which are sensitive to noise. In these cases a classic second order Butterworth filter similar to

those shown in the figures below can be used.

Some systems have little power supply decoupling from the AC line but are also subject to line conducted interference (LCI) regulations. These include systems powered by "wall warts" and "power bricks." In these cases, LC reconstruction filters can be the lowest cost means to pass LCI tests. Common mode chokes using low frequency ferrite material can also be effective at preventing line conducted interference.



LPA2110A-00 Jan.2019 Email: mar




### **PCB Layout notices**


- 1, In the path of the power supply, plus a 1uF and a 10uF to ground high-frequency filter capacitor. These caps can be connected to the thermal pad directly for an excellent ground connection. Consider adding a small, good quality low ESR ceramic capacitor may achieve better sound effects.
- 2, Large (470  $\mu$ F or greater) bulk power supply decoupling capacitors should be placed near the LPA2110A on the VDD supplies. Local, high-frequency bypass capacitors should be placed as close to the VDD pins as possible.
- 3, The power line, ground line and filter capacitor and bypass capacitors as close to the chip's pins, remember not to put the capacitor on the back of the board, through tiny holes through the jumper even over. Keep the current loop from each of the outputs through the ferrite bead and the small filter cap and back to GND as small and tight as possible. The size of this current loop determines its effectiveness as an antenna.
- 4, Power, ground, and a large current line must try to be wide enough, if you want to add vias, the number of through-holes must be at least 6. The thermal pad must be soldered to the PCB for proper thermal performance and optimal reliability.
- 5, GND and VDD should be put independently, high-power signals to avoid interference.
- 6, If you want to pursue as large as the effect of power, a large selection of speakers or sound chamber with low resistance (such as  $3.6\Omega$ ) speakers, or added to improve the supply voltage.
- 7, Including the line between large current cell and chip, the inductor should be as close and short as possible to chip for a high performance. Adding a coil to this pin would be helpful for EMI certification. If there is a high standards needed in LPA2110A application, we could add a coil and capacitor between chip and speaker constituting a LC filter which coil would be 100MHz,  $600\Omega$  and its DCI beyond 4A placing as close as possible to chip, the capacitor should be 1nF connecting the GND.
- 8, The position under the amplifier chip on the board must be added vents and large areas of exposed copper and tin to enhance heat dissipation.
- 9, In case of fixed gain and meeting demand, it should make CIN small as possible as we can because it constitute a high through filter with Rin which cutoff frequency is 1/2\*3.414\*Cin\*Rin. A high capacitance cap could make POP worse.



### **PCB LAYOUT TOP VIEW:**



### **BOTTOM VIEW:**




LPA2110A-00

Jan.2019



# **Packaging Information**

### ESOP-8



SYMBOLS	DIMENSI	ON (MM)	DIMENSION (INCH)		
STIVIBOLS	MIN	MAX	MIN	MAX	
А	1.30	1.70	0.051	0.067	
A1	0.00	0.15	0.000	0.006	
A2	1.25	1.52	0.049	0.060	
b	0.33	0.51	0.013	0.020	
С	5.80	6.20	0.228	0.244	
D	4.80	5.00	0.189	0.197	
D1	3.15	3.45	0.124	0.136	
E	3.80	4.00	0.150	0.157	
E1	2.26	2.56	0.089	0.101	
е	1.27	BSC	0.050 BSC		
Н	0.19	0.25	0.0075	0.0098	
L	0.41	1.27	0.016	0.050	
θ	0°	8°	0°	8°	

LPA2110A-00

Jan.2019