



Specifications :


- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤30mΩ
- After environmental testing: ≤40mΩ

X2011 W V X-XX A HF-XX XX XX
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩

- ① Series No.
- ② Category: W-WAFER
- ③ Welding Board Angle: V-Straight 180°
- ④ Welding Way: Blank-DIP
- ⑤ Row No.-Pin No.: XX-02P~16P
- ⑥ Plug the Pin & Special No.: A-Without Baffle ;
- ⑦ HF-Halogen Free
- ⑧ Material: N0 -PA66 UL 94V-0; LCP 94V-0
- ⑨ Plating Category: SN-Bright Tin Plating;
SW-Matte Tin Plating
- ⑩ Color : Blank-Natural Color



Poles	Dimensions (mm)			Poles	Dimensions (mm)		
	A	B	C		A	B	C
02	2.00	6.00	4.75	10	18.00	22.00	20.75
03	4.00	8.00	6.75	11	20.00	24.00	22.75
04	6.00	10.00	8.75	12	22.00	26.00	24.75
05	8.00	12.00	10.75	13	24.00	28.00	26.75
06	10.00	14.00	12.75	14	26.00	30.00	28.75
07	12.00	16.00	14.75	15	28.00	32.00	30.75
08	14.00	18.00	16.75	16	30.00	34.00	32.75
09	16.00	20.00	18.75				



Recommended P.C.B Layout
 General Tolerance±0.05

X2011WV-XXA-LPSW	LCP 94V-0	Brass	Matte Tin-Plated	X2011H
X2011WV-XXAHF-N0SN	PA 66 UL 94V-0 Halogen Free		Tin-Plated	
X2011WV-XXA-N0SN	PA 66 UL 94V-0			
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
 香港星坤工業精密有限公司

DSND	DATE	SCALE: N/A	MODEL TYPE: X2011WV-XXAXX-XXXX
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm	2.00mm Crimp Style Connector
APPD	DATE	SIZE: A4	DWG NO.:
			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

REVISIONS
 Authorized Signature(s)

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

XKB INDUSTRIAL PRECISION CO., LIMITED