


Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤20mΩ
- After environmental testing: ≤30mΩ



T2530PS-2	Phosphor Bronze	AWG#22-26	1.55mm(Max)	Stamping Before Plating: 30u" Ni;70u"Sn	2530H
PART NO	Material	Wire Range	Insulation O.D.	Finish	Used In SWB Housing

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN兴飞连接器有限公司		SHEET	1/1	
				X.	±0.30	X°	±5°	CONNECTORS XFCN CONNECTORS CO., LTD.		DATE	2010. 4. 12	
				.X	±0.20	.X°	±2°	PRODUCT NAME	2.54mm Crimp Style Connectors		UNITS	mm
				.XX	±0.08	.XX°	±1°	PART. NO.	T2530PS-2		SCALE	1:1
				.XXX	±0.03	.XXX°	±0.5°	VIEW			DWG NO.	009
AO	MODIFICATION	DRAW	DATE									