

650V Super-Junction Power MOSFET

DESCRIPTION

650V Super-junction Power MOSFET

Super-junction power MOSFET is a revolutionary technology for high voltage power MOSFETs, designed according to the SJ principle and pioneered. The Multi-EPI SJ MOSFET provide an extremely fast and robust body diode. Also provide an extremely low switching, communication and conduction losses device with highest robustness make especially resonant switching applications more reliable, more efficient, lighter and cooler, designed by Wuxi Unigroup Microelectronics Company.


FEATURES

- Ultra-fast body diode
- Very low FOM $R_{DS(on)} \times Q_a$
- Easy to use/drive
- 100% avalanche tested
- RoHS compliant

APPLICATIONS

- Switch Mode Power Supply (SMPS)
- Uninterruptible Power Supply (UPS)
- Power Factor Correction (PFC)
- LLC Half-bridge
- Charger







Device Marking and Package Information

Device	Package	Marking
TPA65R300MFD	TO-220F	65R300MFD

Key Performance Parameters				
Parameter	Value	Unit		
V _{DS} @ T _{j,max}	650	V		
R _{DS(on),max}	0.30	Ω		
I _D	15	A		
$Q_{g,typ}$	29	nC		
I _{DM}	45	А		
t _{rr}	152	ns		
Q _{rr}	0.84	μC		
I _{rrm}	11	А		



Absolute Maximum Ratings $T_C = 25$ °C, unless otherwise noted				
Parameter		Symbol	Value	Unit
Drain-Source Voltage (V _{GS} = 0V)		V _{DSS}	650	V
Continuous Drain Current	T _C = 25°C	l _D	15	Α
Continuous Diam Current	TC = 100°C	'D	9	
Pulsed Drain Current	(note1)	I _{DM}	45	А
Gate-Source Voltage		V_{GSS}	±30	V
Single Pulse Avalanche Energy	(note2)	E _{AS}	290	mJ
Repetitive Avalanche Energy	(note2)	E _{AR}	0.44	mJ
Avalanche Current		I _{AR}	2.4	А
MOSFET dv/dt ruggedness, V _{DS} = 0480V		dv/dt	50	V/ns
Power Dissipation		P_{D}	32	W
Continuous Body Diode Current		I _S	15	A
Pulsed Diode Forward Current (note1)		I _{SM}	45	
Reverse diode dv/dt (note3)		dv/dt	15	V/ns
Maximum diode commutation speed (note3)		di _f /dt	500	A/us
Operating Junction and Storage Temperature Range		T _J , T _{stg}	-55~+150	°C

Thermal Resistance			
Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case	R_{thJC}	3.9	°C/W
Thermal Resistance, Junction-to-Ambient	R _{thJA}	80	-0///



		rwise noted	Value			
Parameter	Symbol	Test Conditions			Max.	Unit
Static				1		
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS} = 0V, I_D = 250\mu A$	650			V
7 O. I. V. II D		V _{DS} = 650V, V _{GS} = 0V, T _J = 25°C		1.75		
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 650V, V _{GS} = 0V, T _J = 150°C			1750	μΑ
Gate-Source Leakage	I _{GSS}	V_{GS} = $\pm 30V$			±100	nA
Gate-Source Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_{D} = 250 \mu A$	3		5	V
Drain-Source On-Resistance	R _{DS(on)}	V _{GS} = 10V, I _D = 7.5A		0.26	0.30	Ω
Gate resistance	R_{G}	f = 1.0MHz open drain		12.5		Ω
Dynamic						
Input Capacitance	C _{iss}	V 0V		1205		
Output Capacitance	C _{oss}	$V_{GS} = 0V,$ $V_{DS} = 100V,$		45		pF
Reverse Transfer Capacitance	C _{rss}	f = 1.0MHz		3		
Total Gate Charge	Qg			29		
Gate-Source Charge	Q_{gs}	$V_{DD} = 520V, I_{D} = 15A,$ $V_{GS} = 10V$		8		nC
Gate-Drain Charge	Q_{gd}			11		
Turn-on Delay Time	t _{d(on)}			24		
Turn-on Rise Time	t _r	V _{DD} = 400V, I _D = 15A,		31		
Turn-off Delay Time	$t_{d(off)}$	$R_G = 25\Omega$		121		ns
Turn-off Fall Time	t _f			40		
Drain-Source Body Diode Characte	ristics					
Body Diode Voltage	V _{SD}	$T_J = 25$ °C, $I_{SD} = 7.5$ A, $V_{GS} = 0$ V		1.0	1.5	V
Reverse Recovery Time	t _{rr}			152		ns
Reverse Recovery Charge	Q _{rr}	$V_R = 400V, I_F = I_S,$ $di_F/dt = 100A/\mu s$		0.84		μC
Peak Reverse Recovery Current	I _{rrm}	.,		11		Α

Notes

- 1. Repetitive Rating: Pulse width limited by maximum junction temperature
- 2. I_{AS} = 2.4A, V_{DD} = 50V, R_G = 25 Ω , Starting T_J = 25 $^{\circ}$ C
- 3. Identical low side and high side switch with identical $R_{\mbox{\scriptsize G}}$



Typical Characteristics $T_J = 25$ °C, unless otherwise noted





Figure 3. On-Resistance vs. Drain Current






Figure 2. Transfer Characteristics




Figure 4. Capacitance




Figure 6. Body Diode Forward Voltage

102

(Y)

101

T_J = 125°C

T_J = 25°C

100

0.0

0.5

1.0

1.5

V_{SD}, Source-to-Drain Voltage (V)

Typical Characteristics $T_J = 25$ °C, unless otherwise noted




Figure 9. Transient Thermal Impedance




Figure 8. Breakdown voltage vs. Junction Temperature




Figure 10. Safe operation area for






Figure A: Gate Charge Test Circuit and Waveform




Figure B: Resistive Switching Test Circuit and Waveform







Figure C: Unclamped Inductive Switching Test Circuit and Waveform





TO-220F





Unit:mm				
Symbol	Min.	Nom	Max.	
Е	9.96	10.16	10.36	
Α	4.50	4.70	4.90	
A1	2.34	2.54	2.74	
A2	0.30	0.45	0.60	
A4	2.56	2.76	2.96	
С	0.40	0.50	0.65	
c1	1.20	1.30	1.35	
D	15.57	15.87	16.17	
H1	6.70REF			

Unit:mm				
Symbol	Min.	Nom	Max.	
е		2.54BSC		
L	12.68	12.98	13.28	
L1	2.93	3.03	3.13	
ФР	3.03	3.18	3.38	
ФР3	3.15	3.45	3.65	
F3	3.15	3.30	3.45	
G3	1.25	1.35	1.55	
b1	1.18	1.28	1.43	
b2	0.70	0.80	0.95	



Disclaimer

All product specifications and data are subject to change without notice.

For documents and material available from this datasheet, Wuxi Unigroup does not warrant or assume any legal liability or responsibility for the accuracy, completeness of any product or technology disclosed hereunder.

No license, express or implied, by estoppels or otherwise, to any intellectual property rights is granted by this document or by any conduct of Wuxi Unigroup.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling Wuxi Unigroup products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Wuxi Unigroup for any damages arising or resulting from such use or sale.

Wuxi Unigroup disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Wuxi Unigroup's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

Wuxi Unigroup Microelectronics CO., LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

In the event that any or all Wuxi Unigroup products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

Information (including circuit diagrams and circuit parameters) herein is for example only. It is not guaranteed for volume production. Wuxi Unigroup believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.