
## KEMET Part Number: R73TI1100SE00J



R73, Film, Film/Foil Polypropylene, Automotive Grade, 1000 pF, 5%, 1600 VDC, 85°C, Lead Spacing = 15mm



| Dimensions |                  |  |
|------------|------------------|--|
| L          | 18mm +0.3/-0.5mm |  |
| Н          | 11mm +0.1/-0.5mm |  |
| Т          | 5mm +0.2/-0.5mm  |  |
| S          | 15mm +/-0.4mm    |  |
| LL         | 4mm +2mm         |  |
| F          | 0.8mm +/-0.05mm  |  |

| Packaging Specifications |           |
|--------------------------|-----------|
| Packaging:               | Bulk, Bag |
| Packaging Quantity:      | 2000      |

| General Information |   |
|---------------------|---|
| Series:             | R73   |
| Dielectric:         | Film/Foil Polypropylene                             |
| Style:              | Radial  |
| Features:           | Automotive Grade, Pulse                             |
| RoHS:               | Yes   |
| Lead:               | Cut   |
| Qualifications:     | AEC-Q200  |
| AEC-Q200:           | Yes   |
| Miscellaneous:      | Above 85C DC And AC Voltage<br>Derating Is 1.25%/C. |

| Specifications         |   |  |
|------------------------|---|--|
| Capacitance:           | 1000 pF                                 |  |
| Capacitance Tolerance: | 5%                                      |  |
| Voltage AC:            | 450 VAC                                 |  |
| Voltage DC:            | 1600 VDC                                |  |
| Temperature Range:     | -55/+105°C                              |  |
| Rated Temperature:     | 85°C                                    |  |
| Dissipation Factor:    | 0.03% 1kHz, 0.04% 10kHz, 0.1%<br>100kHz |  |
| Insulation Resistance: | 100 GOhms                               |  |
| Max dV/dt:             | 34000 V/us                              |  |
| Inductance:            | 10 nH                                   |  |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

