

**Schottky rectifier**

**Features**

- Low profile package
- Ideal for automated placement
- Ultra high-speed switching
- Low power losses, high efficiency
- Low forward voltage drop
- High surge capability
- High temperature soldering:  
260°C/10 seconds at terminals Component in accordance to RoHS 2002/95/1 and WEEE 2002/96/EC


**SOD-323 Surface Mount**



SOD-323

**Mechanical Data**

- **Case:** SOD323 molded plastic
- **Terminals:** Solder plated, solderable per JESD22-B102
- **Polarity:** Laser band denotes cathode end



**Circuit Diagram**

**Absolute Maximum Ratings (T<sub>A</sub> = 25°C unless otherwise noted)**

Symbol	Parameter	Value	Units
V <sub>RRM</sub>	Maximum repetitive peak reverse voltage	40	V
V <sub>RMS</sub>	Maximum RMS voltage	28	V
V <sub>DC</sub>	Maximum DC blocking voltage	40	V
I <sub>F(AV)</sub>	Maximum average forward rectified current	1.0	A
I <sub>FSM</sub>	Peak forward surge current 8.3ms single half sine-wave superimposed on rated load	9	A
dv/dt	Voltage rate of change (rated V <sub>R</sub> )	10000	V/μs
R <sub>θJL</sub>	Thermal resistance from junction to lead	35	°C/W
T <sub>J</sub> , T <sub>STG</sub>	Operating junction and storage temperature range	- 65 to +125	°C

**Electrical Characteristics (T<sub>A</sub> = 25°C unless otherwise noted)**

Items	Test conditions	Symbol	Type	UNIT
Instantaneous forward voltage	I <sub>F</sub> = 1.0A	V <sub>F</sub>	0.55	V
Reverse current	V <sub>R</sub> = V <sub>DC</sub>	I <sub>R</sub>	T <sub>j</sub> = 25°C	0.1
			T <sub>j</sub> = 100°C	10

**Typical Performance Characteristics (T<sub>A</sub> = 25°C unless otherwise Specified)**

Fig 1. Forward Current Derating Curve




Fig 2. Maximum Non-Repetitive Peak Forward Surge Current




Fig 3. Typical Instantaneous Forward






Fig 4. Typical Reverse Leakage Characteristics




**SOD-323 Package Outline Drawing**



SYM	DIMENSIONS			
	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	1.60	1.95	0.063	0.077
B	1.10	1.50	0.043	0.059
C	2.30	2.90	0.095	0.112
D	0.80	1.15	0.031	0.045
E	0.20	0.40	0.008	0.016
F	0.10	0.15	0.004	0.006
H	-	0.10	-	0.004

**Suggested Land Pattern**



SYM	DIMENSIONS	
	MILLIMETERS	INCHES
A	3.00	0.110
B	0.60	0.024
C	0.60	0.024