



深圳市业展电子有限公司

承认书

SPECIFICATION FOR APPROVAL

客户名称

Customer Name _____

客户料号

Customer P/N _____

产品名称

Product Name

Shunt Resistors - UBH Series

产品规格

Product Type

UBH-U-100-50F-W

申请承认日期

Apply Date

2019-09-05

版本

REV. _____

供货商属性 代理商

制造商 深圳市业展电子有限公司

Vendor Type Agency

Manufacturer

Note: 禁止使用 1 级环境管理物质.遵守 ACBEL"环境管理物质规范"中所要求之含量标准.

Restrict use of hazardous substances of level 1; Comply with "Specification for Hazardous Substances and Materials Management" of ACBEL

供货商印鉴 Vendor Stamp	APPROVED	CHECKED	PREPARED	承认印鉴 Stamp
			邓小辉	

Mainland China: 深圳市业展电子有限公司

Shenzhen Yezhan Electronics Co., Ltd.

Add: 深圳市龙华新区观澜街道办横坑河东村 440 号 7 栋 4 楼

Tel: 0755-26500756-8018/18926048203

Fax: 0755-29500756

E-mail: caixiaojuan@yezhan.com.cn

标准书名 Classification 承认书 Specification	Spec No.	YZ-QR-EN-007
品名：分流电阻器 UBH Series Product Name: Alloy Shunt Resistors	Version	1.5
	Page	4-1

1. 一般事项 General

1.1 适用范围 Scope

本承认书适用于深圳市业展电子有限公司 制造之[U型分流电阻器]。

This specification is available for Alloy Shunt Resistors manufactured by

Shenzhen Yezhan Electronics Co., Ltd.

1.2 品质 Quality

本电阻器的制造系经高质量管理程序，并具有高信赖性的质量保证，且符合 RoHS 和无卤要求。

The resistor is manufactured by highly quality-controlled process and guaranteed high reliability,

it meets RoHS & Halogen-Free requirement.

1.3 标准试验状态 Standard measuring conditions

温度 $20 \pm 2^\circ\text{C}$ 、湿度 $65 \pm 5\%$ 。

但在温度 $5 \sim 35^\circ\text{C}$ 、湿度 $45 \sim 85\%$ 之情况下，仍可给予判定。

Temperature $20 \pm 2^\circ\text{C}$, Humidity $65 \pm 5\%$.


Being no doubt about the judgment, measurements can be made within the following Temperature

$5 \sim 35^\circ\text{C}$, Humidity $45 \sim 85\%$.

1.4 形名 (例) Type designation (example)

依使用种类、线径、脚距、形状、公称电阻值、电阻值容许差而区别，其构造如下：

The type designation shall be in the following form and as specified.




标准书名 Classification 承认书 Specification	Spec No.	YZ-QR-EN-007
品名：分流电阻器 UBH Series Product Name: Alloy Shunt Resistors	Version	1.5
	Page	4-2


1.5 材质 Material

代号 Symbol	材料 Material	成分 Components	电阻率 Resistance rate
2	锰铜 Manganin wire	Cu 85%, Mn 12%, Ni 3%	44 $\mu\Omega \cdot \text{cm}$

1.6 功率曲线 Power Derating



1.7 温度系数曲线 TCR Derating



标准书名 Classification 承认书 Specification	Spec No.	YZ-QR-EN-007
品名：分流电阻器 UBH Series Product Name: Alloy Shunt Resistors	Version	1.5
	Page	4-3

1.8 外形 External

项 目	参 数
材 料	锰铜+无氧铜拼接带
图 解	
C (线宽)	17.2mm±1mm
W (跨距)	10.5mm±0.5mm
H (高度)	24mm±2mm
A (脚长)	3.0mm±0.2mm
D (厚度)	2mm±0.1mm
L	18mm±0.2mm
E	1.4mm±0.1mm
B	6mm±0.1mm
T	1.4mm±0.1mm
F	6mm±0.5mm
阻 值	0.5mΩ±1%
推荐使用温度	-65℃~170℃

标准书名 Classification 承认书 Specification	Spec No.	YZ-QR-EN-007
品 名 : 分流电阻器 UBH Series Product Name: Alloy Shunt Resistors	Version	1.5
	Page	4-4

2.0 工作特性 Performance Date

Items	Additional Requirements	Reference	Limits
Temperature Cycling	1000 Cycles(-55°C to +125°C)	JESD22 Method JA-104	±0.5%
High Temperature Exposure	1000hrs.@T=125°C.Unpowered.	MIL-STD-202 Method 108	±1%
Biased Humidity	1000hrs 85°C/85%RH。 Note: Specified conditions: 10% of operating power.	MIL-STD-202 Method 103	±0.5%
Operational Life	Condition D Steady State TA=125°C at rated power.	MIL-STD-202 Method 108	±1%
Solderability	245°C±5°C,5s+0.5s/-0	J-STD-002C	95% CoverageMin
Resistance to Soldering Heat	260°C±5°C, 10s±1s	MIL-STD-202 Method 210	±0.5%
Short Time Overload	5×Rated power for 5 s	MIL-STD-202 Method 301	±0.5%