

FUNCTION TABLE (each latch)

INP	UTS	OUTI	PUTS
D	С	a	ā
L	Н	L	н
н	Н	н	L
х	L	00	\overline{a}_0


H = high level, L = low level, X = irrelevant $O_0 = the level of Q before the high-to-low transition of G$

description

These latches are ideally suited for use as temporary storage for binary information between processing units and input/output or indicator units. Information present at a data (D) input is transferred to the Q output when the enable (C) is high and the Q output will follow the data input as long as the enable remains high. When the enable goes low, the information (that was present at the data input at the time the transition occurred) is retained at the Q output until the enable is permitted to go high.


The '75 and 'LS75 feature complementary Q and \overline{Q} outputs from a 4-bit latch, and are available in various 16-pin packages. For higher component density applications.

XD74LS75 0° C to 70° C.





logic symbols†

75, LS75





logic diagrams (each latch) (positive logic)






Pata: Req = 2 kΩ NOM Enable: Req = 1 kΩ NOM







recommended operating conditions

	Х	XD74LS75		
	MIN	NOM	MAX	UNIT
Supply voltage, V _{CC}	4.75	5	5,25	V
High-level output current, 10H			-400	μΑ
Low-level output current, IOL			16	mA
Width of enabling pulse, tw	20			ns
Setup time, t _{SU}	20			ns
Hold time, th	5			ns
Operating free-air temperature, TA	0		70	°C

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

	PARAMETER			NDITIONS [†]	MIN	TYP‡	MAX	UNIT
VIH	High-level input voltage				2			٧
VIL	Low-level input voltage						0.8	V
VIK	Input clamp voltage		V _{CC} = MIN,	I _I = -12 mA			-1.5	V
V _{OH}	High-level output voltage	put voltage		V _{1H} = 2 V, I _{OH} = -400 μA	2.4	3.4		٧
VOL	Low-level output voltage		V _{CC} = MIN, V _{IL} = 0.8 V,	V _{IH} = 2 V, I _{OL} = 16 mA		0.2	0.4	٧
11	Input current at maximum input voltage		V _{CC} = MAX,	V ₁ = 5.5 V			1	mA
1	District Control of the Control of t	D input	V _{CC} = MAX, V _I	V _I = 2.4 V			80	μΑ
ΉН	High-level input current	C input		V - 2.4 V			160	
1	Law law line to the control of the c	D input	V MAY	V ₁ = 0.4 V	,		-3.2	mA
11L	Low-level input current		VCC = MAX,	V			-6.4] ""^
	Chart aire it autout auron 8			SN54'	-20		-57	mA
los	Short-circuit output current§		V _{CC} = MAX	SN74'	-18		–57	I IIIA
1	Constitution of the consti		V _{CC} = MAX,	SN54'		32	46	mA
Icc	Supply current		See Note 3	SN74'		32	53	"A

[†]For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

NOTE 3: I_{CC} is tested with all inputs grounded and all outputs open.

switching characteristics, $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ}\text{C}$

PARAMETER	FROM (INPUT)	TO (OUTPUT)	TEST CONDITIONS	MIN	TYP	MAX	UNIT
[†] PLH					16	30	
tPHL.	D Q		14	25	ns		
tPLH¶		ā	0 15 - 5		24	40	ns
tPHL¶			7	15	""		
tPLH .	_	Q	R _L = 400 Ω , See Figure 1		16	30	ns
^t PHL	С	ā	See Figure 1		7	15] "
tPLH¶			1		16	30	ns
tPHL¶					7	15] ""

 $t_{PLH} \equiv \text{propagation delay time, low-to-high-level output}$

[‡]All typical values are at $V_{CC} = 5 \text{ V}$, $T_A = 25^{\circ}\text{C}$.

Not more than one output should be shorted at a time.

 $t_{PHL} \equiv propagation delay time, high-to-low-level output$

recommended operating conditions

	XD7	XD74LS75		
	MIN N	IOM MAX	1	
Supply voltage, V _{CC}	4.75	5 5.25	V	
High-level output current, IOH		-400	μА	
Low-level output current, IOL		8	mA	
Width of enabling pulse, tw	20		ns	
Setup time, t _{su}	20		ns	
Hold time, th	5		ns	
Operating free-air temperature, TA	0	70	°C	

electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

PARAMETER		TEST CONDITIONS [†]		XD74LS75			UNIT	
					MIN	TYP‡	MAX	
V∤H	High-level input voltage				2			V
VIL	Low-level input voltage						0.8	٧
VIK	Input clamp voltage	V _{CC} = MIN,	I _I =18 mA				-1.5	V
VOH High-level output vol	High level gutaut valtage	VCC = MIN,	V _{IH} = 2 V,		2.7	3.5		v
	High-level output voltage	VIL = VIL max,	I _{OH} = -400	μA	2.7	3.5		
V	Low-level output voltage	V _{CC} = MIN,	V _{IH} = 2 V,	toL = 4 mA		0.25	0.4	V
VOL		VIL = VIL max		IOL = 8 mA		0.35	0.5	•
	Input current at	V MAY	V ₁ = 7 V	D input			0.1	^
4	maximum input voltage	V _{CC} = MAX,	Cinput				0.4	mA
	History Company	V 110 V	V. = 2.7.V	D input			20	
Ιн	High-level input current	V _{CC} = MAX,	$V_1 = 2.7 V$	Cinput			80	μA
	1 1 1	W MAN	V = 0.4.V	D input			-0.4	_^
11L	Low-level input current	V _{CC} = MAX,	$CC = MAX$, $V_1 = 0.4 V$	Cinput			-1.6	mA
los	Short-circuit output current §	V _{CC} = MAX			-20		-100	mA
100	Supply current	Voc - MAY	See Note 2	LS75		6.3	12	mA
1CC	Supply current	VCC = MAX,	366 140 te 2	'LS77				L'''^_

[†] For conditions shown as MIN or MAX, use the appropriate value specified under recommended operating conditions.

switching characteristics, VCC = 5 V, TA = 25°C


040445750¶	FROM	то	TEST COMPLETIONS	TO LS7		'LS75		l
PARAMETER¶	(INPUT)	(OUTPUT)	TEST CONDITIONS	MIN	MIN TYP MA		UNIT	
^t PLH	D	Q				15	27	ns
tPHL		4			9	17	l '''	
tPLH	D	ā	CL = 15 pF,		12	20	ns	
tPHL	6	ď			7	15	""	
†PLH			$R_L = 2 k\Omega$,		15	27	ns	
tPH L	С	a	See Figure 1	See Figure 1	14	14	25	l '''
tPLH .		ā			16	30	ns	
^t PHL	С	u			7	15	'''	

[¶] tpLH = propagation delay time, low-to-high-level output tpLH = propagation delay time, high-to-low-level output

 $^{^{\}ddagger}$ All typical values are at V_{CC} = 5 V, T_A = 25 °C. § Not more than one output should be shorted at a time, and duration of the short-circuit should not exceed one second NOTE 2: I_{CC} is tested with all inputs grounded and all outputs open.

PARAMETER MEASUREMENT INFORMATION

switching characteristics†



VOLTAGE WAVEFORMS

[†]Complementary Q outputs are on the '75 and 'LS75 only.

- NOTES: A. The pulse generators have the following characteristics: $Z_{out} \approx 50 \Omega$; for pulse generator A, PRR ≤ 500 kHz; for pulse generator B, PRR ≤ 1 MHz. Positions of D and C input pulses are varied with respect to each other to verify setup times.
 - B. Ct includes probe and jig capacitance.
 - C. All diodes are 1N3064 or equivalent.
 - D. When measuring propagation delay times from the D input, the corresponding C input must be held high.
 - E. For '75 , $V_{ref} = 1.5 \text{ V}$; for 'LS75 , $V_{ref} = 1.3 \text{ V}$.

FIGURE 1



