

1. ELECTRICAL SPECIFICATIONS @25°C

1.1 OCL: 350 uH Min @ 100 KHz, 0.1V with 8mA DC Bias

350 mA Current Capability

1.2 Leakage Inductance: 0.5uH Max @ 100KHz, 0.2V

1.3 DCR: 1.4 Ω Max

1.4 Turns Ratio: 1CT:1CT

1.5 Polarity: 1-16, 6-11 In-Phase

1.6 Insertion Loss: -1.0 dB Max. @ 0.3-100 MHz

1.7 Return Loss: -18 dB Min. @ 1-30 MHz

-14 dB Min. @ 30-60MHz

-12 dB Min.@ 60-80 MHz


1.8 Cross Talk: -30 dB Min@ 1-100 MHz

1.9 Common Mode Rejection : -30 dB Min@ 1-100 MHz


1.10 Isolation HI-POT: 1500Vrms 2mA 60Second

1.11 Operating temperature 0°C to +70°C


1.12 Storage temperature -40°C to +85°C

DRAWN BY:	CHECKED BY:	APPROVED BY:	TITLE: 10/100 BASE-T
Spencer			FPE PART NO : H16101MC
	Dong guan Meixin Science and Technology Co., Ltd		REV:B
			PAGE: 1 / 2

2. SCHEMATICS



3. DIMENSIONS & MARKING



DRAWN BY:	CHECKED BY:	APPROVED BY:	TITLE: 10/100 BASE-T
Spencer			FPE PART NO : H16101MC
FPE ®	Dongguan Meixin Science and Technology Co., Ltd	REV: B	
		PAGE: 2 / 2	