

HMC602LP4 / 602LP4E

v03.0209




70 dB. LOGARITHMIC **DETECTOR / CONTROLLER, 1 - 8000 MHz**

Typical Applications

The HMC602LP4(E) is ideal for IF and RF applications in:

- Cellular/PCS/3G
- · WiMAX, WiBro, WLAN, Fixed Wireless & Radar
- Power Monitoring & Control Circuitry
- Receiver Signal Strength Indication (RSSI)
- Automatic Gain & Power Control

Functional Diagram



Features

Wide Dynamic Range: up to 70 dB

High Accuracy: ±1 dB with 60 dB Range Up To 6 GHz

Fast: 10ns Output Response Time

Supply Voltage: +5V Power-Down Mode

Excellent Stability over Temperature Buffered Temperature Sensor Output Compact 4x4mm Leadless SMT Package

General Description

The HMC602LP4(E) Logarithmic Detector/Controller converts RF signals at its input, to a proportional DC voltage at its output. The HMC602LP4(E) employs a successive compression topology which delivers extremely high dynamic range and conversion accuracy over a wide input frequency range. As the input power is increased, successive amplifiers move into saturation one by one creating an accurate approximation of the logarithm function. The output of a series of square law detectors is summed, converted into voltage domain and buffered to drive the LOGOUT output. For detection mode, the LOGOUT pin is shorted to the VSET input. and will provide a nominal logarithmic slope of -25mV/ dB and an intercept of 18 dBm (23 dBm for f > 5.8 GHz). The HMC602LP4(E) can also be used in the controller mode where an external voltage is applied to the VSET pin, to create an AGC or APC feedback loop.

Electrical Specifications, T_A = +25C, EN= 5V, Vcc1, Vcc2, Vcc3= +5V [1]

Parameter	Тур.	Тур.	Units							
Input Frequency	50	100	900	1900	2200	3600	5800	7000	8000	MHz
±3 dB Dynamic Range	69	70	71	71	71	68	66	61	56	dB
±3 dB Dynamic Range Center	-24.5	-25	-25.5	-25.5	-25.5	-24	-23	-20.5	-19	dBm
±1 dB Dynamic Range	61	61	62	62	63	62	63	56	49	dB
Output Intercept	18.2	18	18.7	19.8	20.2	23.1	24.4	23	21.6	dBm
Output Slope	-25.6	-25.5	-25.3	-25	-25	-24.6	-25.4	-27.5	-30	mV/dB
Temperature Sensitivity @ -10 dBm Input [2]	16	16	14	14	15	16	15	14	22	mdB/°C

- [1] Detector mode measurements; LOGOUT (Pin 15) is shorted to VSET (Pin 16).
- [2] Measured from T_A = -40C to T_A = +85C [3] C9 removed from production board

Parameter		Conditions	Min.	Тур.	Max.	Units
LOGOUT Interface						
Output Voltage Range			0		Vcc -1.0	V
Output Fall Time -10 dBm Input Pulsed; Measured from 10% to 90% [3]		Pulsed; Measured from 10% to 90% [3]		9.5		ns
Output Rise Time -10 dBm Input Pulsed; Measured from		Pulsed; Measured from 10% to 70% [3]		10		ns
VSET Interface			·			
Input Impedance				30		kΩ
Input Voltage Range				0.25 to 2.0		V
Low Frequency Gain		VSET to LOGOUT		56		dB





70 dB, LOGARITHMIC **DETECTOR / CONTROLLER, 1 - 8000 MHz**

Electrical Specifications, (continued)


Parameter	Conditions	Min.	Тур.	Max.	Units
Open Loop Corner Frequency			700		kHz
Power Down (EN) Interface					
Voltage Range for Normal Mode		0.8 x Vcc [4]		Vcc [4]	V
Voltage Range for Powerdown Mode		0		0.2 x Vcc [4]	V
Threshold Voltage			Vcc [4]/2		V
Power Supply (Vcc1, Vcc2, Vcc3)					
Operating Voltage Range		4.5		5.5	V
Supply Current in Normal Mode			113		mA
Supply Current in Power Down Mode			1		mA

[4] Vcc= Vcc1= Vcc2= Vcc3= +5V


Test Conditions

Parameter	Condition
Vcc1, Vcc2, Vcc3	+5V
Input Zo	50Ω
T _A	+25C
Fin	900 MHz

LOGOUT Voltage & Error vs. Input Power, Fin = 50 MHz




LOGOUT Voltage & Error vs. Input Power, Fin = 900 MHz




Unless otherwise noted: Vcc1, Vcc2, Vcc3 = +5V, T_A = +25C

LOGOUT Voltage & Error vs. Input Power, Fin = 100 MHz



LOGOUT Voltage & Error vs. Input Power, Fin = 1900 MHz



Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners. For price, delivery, and to place orders: Analog Devices, Inc., Phone: 781-329-4700 • Order online at www.analog.com


ANALOGDEVICES

v03.0209




70 dB, LOGARITHMIC DETECTOR / CONTROLLER, 1 - 8000 MHz

LOGOUT Voltage & Error vs. Input Power, Fin = 2200 MHz




LOGOUT Voltage & Error vs. Input Power, Fin = 3600 MHz




HMC602LP4 / 602LP4E


LOGOUT Voltage & Error vs. Input Power, Fin = 5800 MHz




LOGOUT Voltage & Error vs. Input Power, Fin = 7000 MHz



LOGOUT Voltage & Error vs. Input Power, Fin = 8000 MHz



LOGOUT vs. Frequency Over Input Power




Unless otherwise noted: Vcc1, Vcc2, Vcc3 = +5V, TA = +25C






70 dB, LOGARITHMIC DETECTOR / CONTROLLER, 1 - 8000 MHz


LOGOUT Slope vs. Frequency




LOGOUT Slope vs. Supply Voltage




LOGOUT Intercept vs. Frequency




LOGOUT Intercept vs. Supply Voltage



LOGOUT Error vs. Input Power, Normalized [2], Fin= 1900 MHz



LOGOUT Voltage vs. Input Power & Frequency



- [1] Unless otherwise noted: Vcc1, Vcc2, Vcc3 = +5V, $T_A = +25C$
- [2] This data is relative to the room temperature performance of the HMC602LP4(E)
- [3] Reference plane at J1 connector on Evaluation PCB

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.


HMC602LP4 / 602LP4E

v03.0209



70 dB, LOGARITHMIC **DETECTOR / CONTROLLER, 1 - 8000 MHz**

Input Return Loss vs Frequency [4]



Absolute Maximum Ratings

Vcc1, Vcc2, Vcc3	+5.5V
EN	+5.5V
VSET Input Voltage	+5.5V
LOGOUT Output Current	3 mA
RF Input Power	+15 dBm
Junction Temperature	125 °C
Continuous Pdiss (T = 85°C) (Derate 7.95 mW/°C above 85°C)	1.55 Watts
Thermal Resistance (R _{th}) (junction to lead)	42 °C/W
Storage Temperature	-65 to +150 °C
Operating Temperature	-40 to +85 °C




ELECTROSTATIC SENSITIVE DEVICE **OBSERVE HANDLING PRECAUTIONS**

[4] Reference plane at J1 connector on Evaluation PCB

Outline Drawing

BOTTOM VIEW



- PAD BURR HEIGHT SHALL BE 0.05mm MAXIMUM
- 5. PACKAGE WARP SHALL NOT EXCEED 0.05mm.
- 6. ALL GROUND LEADS AND GROUND PADDLE MUST BE SOLDERED TO PCB RF GROUND.
- 7. REFER TO HMC APPLICATION NOTE FOR SUGGESTED PCB LAND PATTERN.

Part Number Package Marking [3] Package Body Material Lead Finish MSL Rating H602 HMC602LP4 Low Stress Injection Molded Plastic Sn/Pb Solder MSL1 [1] XXXX H602 MSL1 [2] HMC602LP4E RoHS-compliant Low Stress Injection Molded Plastic 100% matte Sn XXXX

[1] Max peak reflow temperature of 235 °C

Package Information

- [2] Max peak reflow temperature of 260 °C
- [3] 4-Digit lot number XXXX

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.





70 dB, LOGARITHMIC DETECTOR / CONTROLLER, 1 - 8000 MHz

Pin Descriptions

Pin Number	Function	Description	Interface Schematic	
1, 6, 7, 13, 17, 18	N/C	These pins are not connected internally.		
2	TEMP	Temperature sensor output pin.	Vcc1, Vcc2, Vcc3 OtemP 250 Ohms Ohms	
3, 4	INP, INN	RF Input pins. Connect RF to INP, and AC couple INN to ground for single-ended operation.	1NP 0 700 0 1NNO	
5	EN	Enable pin, connect to Vcc1, Vcc2, Vcc3 for normal operation. Applying voltage <0.2 x (Vcc1, Vcc2, Vcc3) will initiate power saving mode.	Vcc1, 0 Vcc2, Vcc3	
8 - 12, 19, 20, 23, 24	Vcc1, Vcc2, Vcc3	Bias supply. Connect supply voltage to these pins with appropriate filtering.	Vcc1, Vcc2,0 Vcc3	
14	CLPF	Loop filter capacitor for output ripple filtering.	Vcc1, Vcc2, Vcc3 Vcc3 CLPF	
15	LOGOUT	Logarithmic output that converts the input power to a DC level in detector mode. Short this pin to VSET for detector mode.	OVcc2 15 Ohms 550 Ohms	
16	VSET	VSET input in controller mode. Short this pin to LOGOUT for detector mode.	200 Ohms VSET	






70 dB, LOGARITHMIC DETECTOR / CONTROLLER, 1 - 8000 MHz

Pin Descriptions (Continued)

Pin Number	Function	Description	Interface Schematic
21, 22	N/C	The user should not connect to these pins.	
Package Base	GND	Exposed paddle must be connected to RF and DC ground.	

Application & Evaluation PCB Schematic



Notes


- Note 1: The HMC602LP4 & HMC602LP4E evaluation boards are pre-assembled for single-ended input, and detector/RSSI mode.
- Note 2: For detector mode, connect high impedance volt meter to the LOGOUT port, and make no connection to VSET. LOGOUT is shorted to VSET by R9, as required for detector mode.
- Note 3: For controller mode, remove R9 and install 0 ohm resistor (R11), then make appropriate connection to LOGOUT and VSET. In controller mode, the LOGOUT output can be used to drive a variable gain amplifier, or a variable attenuator, either directly or through a buffer or microcontroller. VSET should be connected to an external supply, typically between +0.6 and +1.9V.





70 dB, LOGARITHMIC DETECTOR / CONTROLLER, 1 - 8000 MHz

Evaluation PCB



List of Materials for Evaluation PCB 121492 [1]

Item	Description
J1 - J3	PC Mount SMA Connector
J4	Molex Connector Header
J5 - J9	DC Pin
C1, C2, C3, C5, C7	100 pF Capacitor, 0402 Pkg.
C4, C6, C8	0.1μF Capacitor, 0402 Pkg.
C9	220 pF Capacitor, 0402 Pkg.
R1	68Ω Resistor, 0402 Pkg.
R2	1k Ω Resistor, 0402 Pkg.
R3	10k Ω Resistor, 0402 Pkg.
R4 - R6, R9, R12	0Ω Resistor, 0402 Pkg.
R13	180Ω Resistor, 0402 Pkg.
R14	27.4Ω Resistor, 0402 Pkg.
R15	15Ω Resistor, 0402 Pkg.
R16	49.9Ω Resistor, 0402 Pkg.
U1	HMC602LP4 / HMC602LP4E Logarithmic Detector / Controller
PCB [2]	121490 Evaluation PCB

^[1] Reference this number when ordering complete evaluation PCB

The circuit board used in the final application should use RF circuit design techniques. Signal lines should have 50 ohm impedance while the package ground leads and exposed paddle should be connected directly to the ground plane similar to that shown. A sufficient number of via holes should be used to connect the top and bottom ground planes. The evaluation circuit board shown is available from Hittite upon request.

^[2] Circuit Board Material: Rogers 4350