

BCR420UW6Q / BCR421UW6Q

LINEAR LED CONSTANT CURRENT REGULATOR IN SOT26

Description

These Linear LED drivers are designed to meet the stringent requirements of automotive applications.

The BCR420U and BCR421U monolithically integrate transistors, diodes and resistors to function as a Constant Current Regulator (CCR) for linear LED driving. The device regulates with a preset 10mA nominal that can be adjusted with an external resistor up to 350mA. It is designed for driving LEDs in strings and will reduce current at increasing temperatures to self-protect. Operating as a series linear CCR for LED string current control, it can be used in multiple applications, as long as the maximum supply voltage to the device is < 40V.

With the low-side control, the BCR421U has an Enable (EN) pin which can be pulse-width modulated (PWM) up to 25 kHz by a microcontroller for LED dimming.

With no need for additional external components, this CCR is fully integrated into an SOT26 minimizing PCB area and component count.

Applications

Constant Current Regulation (CCR) in:

- · Automotive Interior Lighting
- · Mood and Decorative Lighting

Features


- LED Constant Current Regulator using NPN Emitter-Follower with **Emitter Resistor to Current Limit**
- I_{OUT} 10mA ± 10% Constant Current (Preset)
- I_{OUT} up to 350mA Adjustable with an External Resistor
- Vout 40V Supply Voltage
- P_D up to 1W in SOT26 (SC74R)
- Low-Side Control Enabling PWM Input < 25kHz (BCR421U)
- Negative Temperature Coefficient (NTC) Reduces IOUT with Increasing Temperature
- Parallel Devices to Increase Regulated Current
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability
- PPAP Capable (Note 4)

Mechanical Data


- Case: SOT26 (SC74R)
- Case Material: Molded Plastic. "Green" Molding Compound. UL Flammability Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads. Solderable per MIL-STD-202, Method 208 @3
- Weight: 0.018 grams (Approximate)



Top View



Schematic



Top View Pin-Out

Pin Name	Pin Function			
OUT	Regulated Output Current			
EN	Enable for Biasing Transistor			
R _{EXT}	External Resistor for Adjusting Output Current			
GND	Power Ground			

Ordering Information (Note 5)


Product	Compliance	Marking	Reel Size (inches)	Tape Width (mm)	Quantity per Reel
BCR420UW6Q-7	Automotive	420	7	8	3,000
BCR421UW6Q-7	Automotive	421	7	8	3,000

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
- 2. See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 4. Automotive products are AEC-Q101 qualified and are PPAP capable. Refer to http://www.diodes.com/product_compliance_definitions.html.
- 5. For packaging details, go to our website at http://www.diodes.com/products/packages.html.



Marking Information



xxx = Part Marking (See Ordering Information)

YM = Date Code Marking Y = Year (ex: D = 2016) M = Month (ex: 9 = September)

Date Code Key

Year	2016		2017	2	2018	201	9	2020		2021	2	022
Code	D		Е		F	G		Н		ı		J
Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec

Absolute Maximum Ratings (Voltage relative to GND, @TA = +25°C, unless otherwise specified.)

Chara	cteristic	Symbol	Value	Unit	
Enghia Valtaga	BCR420U	V	40	V	
Enable Voltage	BCR421U	V _{EN}	18	V	
Output Current		I _{OUT}	500	mA	
Output Voltage		V _{OUT}	40	V	
Reverse Voltage Between all Terr	minals	V _R	0.5	V	

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)


Characteristic		Symbol	Value	Unit
Power Dissipation	(Note 6)	D-	1,190	mW
Power Dissipation	(Note 7)	P _D	912	IIIVV
Thermal Decistores, Junction to Ambient	(Note 6)	D	105	
Thermal Resistance, Junction to Ambient	(Note 7)	R _{θJA}	137	°C/W
Thermal Resistance, Junction to Lead	(Note 8)	R _{0JL}	50	
Recommended Operating Junction Temperature Ra	TJ	-55 to +150	°C	
Maximum Operating Junction and Storage Tempera	ature Range	T _J , T _{STG}	-65 to +150	C

ESD Ratings (Note 9)

Characteristics	Symbols	Value	Unit	JEDEC Class	
Electrostatic Discharge – Human Body	BCR420U	НВМ	500	V	1B
Model	BCR421U	ПБІИ	1,000	V	1C
Electrostatic Discharge Machine Madel	BCR420U	ММ	300	V	В
Electrostatic Discharge – Machine Model	BCR421U		400	V	С

Notes:

- 6. For a device mounted with the OUT leads on 50mm x 50mm 1oz copper that is on a single-sided 1.6mm FR-4 PCB; device is measured under still air conditions while operating in steady-state.
- 7. Same as Note 5, except mounted on 25mm x 25mm 1oz copper.
- 8. $R_{\theta JL}$ = Thermal resistance from junction to solder-point (at the end of the OUT leads).
- 9. Refer to JEDEC specification JESD22-A114 and JESD22-A115.






Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic		Symbol	Min	Тур	Max	Unit	Test Condition
Collector-Emitter Breakdown Voltage		BV _{CEO}	40	_	_	V	I _C = 1mA
Enable Current	BCR420U	I _{EN}	_	1.2	_	mA	V _{EN} = 24V
Enable Current	BCR421U		_	1.2	_		V _{EN} = 3.3V
DC Current Gain		h _{FE}	200	350	500	_	I _C = 50mA; V _{CE} = 1V
Internal Resistor		R _{INT}	85	95	105	Ω	I _{RINT} = 10mA
Bias Resistor	BCR420U	D.	_	20	_	kΩ	_
BCR42	BCR421U	R _B	_	1.5	1	K12	_
Output Current	BCR420U	Гоит	9	10	11	mA	V _{OUT} = 1.4V; V _{EN} = 24V
Output Current	BCR421U		9	10	11	mA	V _{OUT} = 1.4V; V _{EN} = 3.3V
Output Current at	BCR420U		_	150	_	mA	V _{OUT} > 2.0V; V _{EN} = 24V
$R_{EXT} = 5.1\Omega$	BCR421U	lout	_	150	_	mA	$V_{OUT} > 2.0V; V_{EN} = 3.3V$
Voltage Drop (V _{REXT})		V_{DROP}	0.85	0.95	1.05	V	I _{OUT} = 10mA
Minimum Output Voltage		V _{OUT(MIN)}	_	1.4	_	V	I _{OUT} > 18mA
Output Current Change	BCR420U	A.1. //	_	-0.2	_	0/ /90	V _{OUT} > 2.0V; V _{EN} = 24V
vs. Temperature	BCR421U	ΔΙ _{ΟυΤ} /Ι _{ΟυΤ}	_	-0.2	_	%/°C	$V_{OUT} > 2.0V; V_{EN} = 3.3V$
Output Current Change	BCR420U	A.1. //	_	1	_	%/V	V _{OUT} > 2.0V; V _{EN} = 24V
vs. Supply Voltage	BCR421U	Δl _{OUT} /l _{OUT}	_	1	_		$V_{OUT} > 2.0V; V_{EN} = 3.3V$




Typical Thermal Characteristics BCR420/1U (@T_A = +25°C, unless otherwise specified.)






Typical Electrical Characteristics BCR421U (Cont.) (@TA = +25°C, unless otherwise specified.)






Typical Electrical Characteristics BCR421U (Cont.) (@T_A = +25°C, unless otherwise specified.)






Typical Electrical Characteristics BCR420U (Cont.) (@TA = +25°C, unless otherwise specified.)





Typical Electrical Characteristics BCR420U (Cont.) (@T_A = +25°C, unless otherwise specified.)





Application Information




Figure 1 Typical Application Circuit for Linear Mode Current Sink LED Driver




Figure 2 Application Circuit for Increasing LED Current

The BCR420/1 is designed for driving low current LEDs with typical LED currents of 10mA to 350mA. They provide a cost-effective way for driving low current LEDs compared with more complex switching regulator solutions. Furthermore, they reduce the PCB board area of the solution as there is no need for external components like inductors, capacitors and switching diodes.

Figure 1 shows a typical application circuit diagram for driving an LED or string of LEDs. The device comes with an internal resistor (RINT) of typically 95Ω , which in the absence of an external resistor, sets an LED current of 10mA (typical) from a $V_{EN} = 3.3V$ and $V_{OUT} = 1.4V$ for BCR421; or $V_{EN} = 24V$ and $V_{OUT} = 1.4V$ for BCR420. LED current can be increased to a desired value by choosing an appropriate external resistor, R_{EXT}.

The R_{EXT} Vs I_{OUT} graphs should be used to select the appropriate resistor. Choosing a low tolerance REXT will improve the overall accuracy of the current sense formed by the parallel connection of RINT and R_{EXT.}

Two or more BCR420/1s can be connected in parallel to construct higher current LED strings as shown in Figure 2. Consideration of the expected linear mode power dissipation must be factored into the design, with respect to the BCR420/1's thermal resistance. The maximum voltage across the device can be calculated by taking the maximum supply voltage and subtracting the voltage across the LED string.

$$\begin{aligned} &V_{OUT} = V_S - V_{LED} \\ &P_D = (V_{OUT} \times I_{LED}) \ + \ (V_{EN} \times I_{EN}) \end{aligned}$$

As the output current of BCR420/1 increases, it is necessary to provide appropriate thermal relief to the device. The power dissipation supported by the device is dependent upon the PCB board material, the copper area and the ambient temperature. The maximum dissipation the device can handle is given by:

$$P_D = (T_{J(MAX)} - T_A) / R_{\theta JA}$$

Refer to the thermal characteristic graphs on Page 4 for selecting the appropriate PCB copper area.



Application Information (Cont.)

PWM dimming can be achieved by driving the EN pin. Dimming is achieved by turning the LEDs ON and OFF for a portion of a single cycle. The PWM signal can be provided by a micro-controller or analog circuitry; typical circuit is shown in Figure 3. Figure 4 is a typical response of LED current vs PWM duty cycle on the EN pin. PWM up to 25kHz with duty cycle of 0.5% (dimming range 200:1). This is above the audio band minimizing audible power supply noise.




Figure 3 Application Circuits for LED Driver with PWM Dimming Functionality



Figure 4 Typical LED Current Response vs. PWM Duty Cycle for 25kHz PWM Frequency (Dimming Range 200:1)



Application Information (Cont.)




Figure 5 Application Circuit for LED Driver with Reverse Polarity Protection

To remove the potential of incorrect connection of the power supply damaging the lamp's LEDs, many systems use some form of reverse polarity protection.

One solution for reverse input polarity protection is to simply use a diode with a low V_F in line with the driver/LED combination. The low V_F increases the available voltage to the LED stack and dissipates less power. A circuit example is presented in Figure 5 which protects the light engine although it will not function until the problem is diagnosed and corrected. An SDM10U45LP (0.1A/45V) is shown, providing exceptionally low V_F for its package size of 1mm x 0.6mm. Other reverse voltage ratings are available from Diodes Incorporated's website such as the SBR02U100LP (0.2A/100V) or SBR0220LP (0.2A/20V).

While automotive applications commonly use this method for reverse battery protection, an alternative approach shown in Figure 6, provides reverse polarity protection and corrects the reversed polarity, allowing the light engine to function.

The BAS40BRW incorporates four low V_F Schottky diodes in a single package, reducing the power dissipated and maximizes the voltage across the LED stack.

Figure 7 shows an example configuration for 350mA operation. In such higher current configurations adequate enable current is provided by increasing the enable voltage.




Figure 6 Application Circuit for LED Driver with Assured Operation Regardless Of Polarity





Figure 7 Example for 350mA Operation



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT26 (SC74R)




,	SOT26 (SC74R)							
Dim	Min	Min Max						
A1	0.013	0.10	0.05					
A2	1.00	1.30	1.10					
A3	0.70	0.80	0.75					
b	0.35	0.50	0.38					
С	0.10	0.20	0.15					
D	2.90	3.10	3.00					
е	-	-	0.95					
e1	-	-	1.90					
Е	2.70	3.00	2.80					
E1	1.50	1.70	1.60					
L	0.35	0.55	0.40					
а	-	-	8°					
a1	-	-	7°					
All	All Dimensions in mm							


Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT26 (SC74R)



Dimensions	Value (in mm)
С	2.40
C1	0.95
G	1.60
Х	0.55
Y	0.80
Y1	3.20





IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2016, Diodes Incorporated

www.diodes.com