KDS Series Intrusion Switches



Features/Benefits

- Slot mount into chassis to reduce installation cost
- Wire harness length & connector easily customized
- Available in N.O. or N.C. configuration
- RoHS compliant

Typical Applications

- Intrusion/Alarm switch in network desktop PC
- Intrusion/Alarm switch in telecommunication equipment
- Intrusion/Alarm switch in cellular base station

Specifications

CONTACT RATING: 0.4 VA max. @ 20 V AC or DC. MECHANICAL & ELECTRICAL LIFE: 10,000 actuations min. at full load.

CONTACT RESISTANCE: 200 m Ω max. initial @ 2-4 V DC, 100mA. INSULATION RESISTANCE: 10⁹ Ω min.

OPERATING TEMPERATURE: -40°C to +85°C

TRAVEL: KDS11: Pre-travel 0.180" TYP; Overtravel 0.223" KDS33: No pre-travel, full travel 0.403"

DIELECTRIC STRENGTH: 500 Vrms min. @ sea level.

PACKAGING: Bulk packaging.

How To Order

Complete part numbers for KDS Series Switches are shown below.


Materials


HOUSING: Nylon 6/6 (UL 94V-0) ACTUATOR: Nylon 6/6 (UL 94V-0) MOVABLE CONTACT: Copper alloy, gold plate over nickel plate. FIXED CONTACT: Brass, gold plate over nickel plate. WIRE: UL 1061-24 AWG.

NOTE: Specifications and materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center.

SWITCH FUNCTION POS. 1 POS. 2 PART NUMBER SCHEMATIC .400 (10, 16)KDS11 OFF MOM. SPST N.O. 2 KDS33 ON OFF SPST N.C. .359 (8,89)

KDS33





.600 (15,24)

 \odot



E–26

Dimensions are shown: mm Specifications and dimensions subject to change