

### **US1J thru US1M**

## SURFACE MOUNT ULTRA FAST RECTIFIER


REVERSE VOLTAGE - 600 to 1000 Volts FORWARD CURRENT - 1.0 Amperes

#### **FEATURES**

- · Glass passivated chip
- · Ultra fast switching for high efficiency
- · Low forward voltage drop and high current capability
- · Low reverse leakage current
- Qualified according AEC-Q101 Rev\_C

#### **MECHANICAL DATA**

- · Case: Molded plastic
- Case Material: "Green" Molding compound, UL flammability classification 94V- 0,"Halogen-free"
- · Polarity : Indicated by cathode band
- Weight: 0.002 ounces, 0.069 grams (Approximate)



#### **SMA** DIM MIN MAX 4.06 4.57 Α В 2.29 2.92 С 1.63 1.27 D 0.15 0.31 Ε 4.83 5.59 F 0.05 0.20 G 2.01 2.40 Н 0.76 1.52 All Dimensions in millimeter

#### MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

#### **ABSOLUTE RATINGS**

PARAMETER		SYMBOL	US1J	US1K	US1M	UNIT
Maximum repetitive peak reverse voltage		$V_{RRM}$	600	800	1000	V
Maximum RMS voltage		V <sub>RMS</sub>	420	560	700	V
Maximum DC Blocking voltage		$V_{DC}$	600	800	1000	V
Maximum Average rectified forward current	@T <sub>L</sub> =110 °C	l <sub>F</sub>	1.0			Α
Peak forward surge single half sine-wave	@tp=8.3ms	I <sub>FSM</sub>	30		Α	
Operating ant Storage temperature range		T <sub>J</sub> , T <sub>STG</sub>	-55 ~ +150			°C

#### STATIC ELECTRICAL CHARACTERISTICS

PARAMETER	TEST CONDITION		SYMBOL	MAX	UNIT	
Forward voltage (Note 1)	I <sub>F</sub> =1A	T <sub>J</sub> = 25°C	VF	1.7	V	
Reverse leakage current at Rated DC		I <sub>R</sub>	5.0 100	uA		
Typical junction capacitance(Note 2)		Ci	10	рF		

#### THERMAL PERFORMANCE

PARAMETER	SYMBOL	ТҮР	UNIT
	RthJ <sub>A</sub>	60	
Typical thermal resistance(Note 3)	RthJ∟	22	°C/W
	RthJ <sub>C</sub>	18	

### DYNAMIC ELECTRICAL CHARACTERISTICS

PARAMETER		SYMBOL	MAX		UNIT
Reverse recovery time	I <sub>F</sub> =0.5A,I <sub>rr</sub> =0.25A,I <sub>R</sub> =1.0A	T <sub>rr</sub>	75		nS
Note:			REV0, Oct-2019, KSF	A03	


#### (1) 300us pulse with, 2% duty cycle

- (2) Measured at 1.0MHz and reverse voltage of 4.0V DC.
- (3) Thermal resistance junction to Ambient, Lead and Case

Please be aware that an **Important Notice and Disclaimer** concerning availability, disclaimers, and use in critical applications of LSC products thereto appears at the end of this Data Sheet.

# RATING AND CHARACTERISTIC CURVES US1J thru US1M







#### IMPORTANT NOTICE AND DISCLAIMER

LSC reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design purchase or use.

ALL INFORMATION ARE PROVIDED AS-IS, EVEN IT HAS QUALIFIED BY THE AEC-Q101 WHICH SATISFY INDUSTRIAL APPLICATION REQUIREMENT, EXCEPT AS EXPRESSLY STATED IN THIS DATA SHEET IS APPLIED FOR AUTOMOTIVE GRADE, LSC MAKE NO WARRANTIES, REPRESENTATION OR GUARANTEE, WHETHER EXPRESS, IMPLIED OR STATUTORY, INCLUDING, WITHOUT LIMITATION, REGARDING ANY MERCHANTABILITY, SATISFACTORY QUALITY, OR FITNESS FOR A PARTICULAR PURPOSE WITH RESPECT TO THE LSC TECHNOLOGY.

LSC DOES NOT ASSUME ANY LIABILITY OR COMPENSATION FOR ANY APPLICATION ASSISTANCE OR CUSTOMER PRODUCT DESIGN, AND MAKE NO WARRANTY OR ACCEPT ANY LIABILITY WITH PRODUCTS, WHICH ARE PURCHASED OR USED FOR ANY UNINTENDED OR UNAUTHORIZED APPLICATION.

No license is granted by implication or otherwise under any intellectual property rights of LSC.

LSC products are not authorized for use as critical components in life support devices or systems without express written approval of LSC.