


40V Input, 500mA Output Current, Low Dropout, Low Quiescent Current LDO

General Description

The BL9152 series is a high accuracy, high input voltage low quiescent current, high speed, and low dropout Linear regulator with high ripple rejection. The device is manufactured with Bi-CMOS process.

The BL9152 offers over-current limit and over temperature protection to ensure the device working in well conditions.




The BL9152 regulators are available in standard SOT-89-3L packages. Standard products are Pb-free and Halogen-free.


Features

- Supply Voltage : 4.75V~40V
- Output Voltage : 1.8V,3.3V,3.6V,5.0V~10V
- Output Accuracy : <+/-2%
- Output Current : 100mA (Up to 500mA Typ.)
- PSRR : 45dB @ 100Hz
- Dropout Voltage : 300mV @ $I_{OUT}=100mA$
- Quiescent Current : $6\mu A@V_{IN}=7V(Typ.)$
- Recommend Capacitor : 10uF


Typical Application



Functional Block Diagram



Pin Configuration



Pin Description

| Pin Number | Pin Name | Function Description |
|------------|-----------|----------------------|
| 1 | V_{OUT} | Voltage Output |
| 2 | GND | Ground |
| 3 | V_{IN} | Voltage Input |

Absolute Maximum Ratings (Ta=25 °C)

| Parameter Name | Rating | Unit |
|--------------------------------------|------------------|------|
| Power Dissipation | Internal limited | mW |
| V _{IN} Range | -0.3~45 | V |
| V _{OUT} Range | -0.3~12 | V |
| Lead Temperature Range | 260 | °C |
| Storage Temperature Range | -55~150 | °C |
| Operating Junction Temperature Range | 125 | °C |
| ESD MM | 400 | V |
| ESD HBM | 4K | V |

Recommended Operating Conditions (Ta=25°C)

| Parameter Name | Rating | Unit |
|---|---------|------|
| Operating Supply voltage | 4.75~40 | V |
| Operating Temperature Range | -40~85 | °C |
| Thermal Resistance(On PCB),R _{θJA} | 43.5 | °C/W |
| Power Dissipation | 1000 | mW |


Electrical Characteristics (Ta=25°C, V_{IN}=12V, C_{IN}=C_{OUT}=10uF, unless otherwise noted)

| Parameter Name | Symbol | Test Conditions | Min | Typ | Max | Unit |
|-------------------------|---------------------|--|---------|------|-------|-------|
| Input Range | V _{IN} | I _{OUT} =10mA | 4.75 | | 40 | V |
| Output Voltage | V _{OUT} | V _{IN} =12V, I _{OUT} =10mA | 3.234 | 3.3 | 3.366 | V |
| | | | 3.528 | 3.6 | 3.672 | |
| | | | 4.9 | 5.0 | 5.1 | |
| Maximum Output Current | I _{OUT_PK} | V _{IN} =12V, R _L =1Ω | | 500 | | mA |
| Quiescent Current | I _Q | V _{IN} =3.6V, No load | | 5.8 | 7.8 | μA |
| | | V _{IN} =5.5V, No load | | 5.9 | 7.9 | |
| | | V _{IN} =7V, No load | | 6 | 8 | |
| | | V _{IN} =24V, No load | | 7.5 | 10 | |
| | | V _{IN} =40V, No load | | 10 | 15 | |
| Dropout Voltage | V _{DROP} | I _{OUT} =1mA | | 2 | 12 | mV |
| | | I _{OUT} =100mA | | 300 | 400 | |
| Line Regulation | LNR | V _I =7~24V, V _{OUT} =5V, I _{OUT} =1mA | | 0.02 | | % / V |
| | | V _{IN} =7~45V, V _{OUT} =5V, I _{OUT} =1mA | | 0.1 | | |
| Load Regulation | LDR | V _{IN} =12V, I _{OUT} =1~100mA | | 0.6 | | % |
| Output Noise | e _{NO} | I _{OUT} =10mA | -100 | | 100 | μV |
| Ripple Rejection | PSRR | V _{IN} =10V V _{PP} =0.5V I _{OUT} =1mA | f=100Hz | 50 | | dB |
| | | | f=1KHz | 40 | | |
| | | | f=10KHz | 30 | | |
| Thermal Protection | T _{SD} | V _{IN} =12V, I _{OUT} =1mA | | 155 | | °C |
| Thermal Protection Hys | T _{SD_HYS} | V _{IN} =12V, I _{OUT} =1mA | | 30 | | °C |
| Temperature Coefficient | ΔV _O /ΔT | V _{IN} =12V, I _{OUT} =1mA | | ±0.4 | | mV/°C |

Outline Dimensions

SOT-89-3L

Unit:mm



| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|-------|----------------------|-------|
| | Min | Max | Min | Max |
| Δ | 1.400 | 1.600 | 0.055 | 0.063 |
| b | 0.320 | 0.520 | 0.013 | 0.197 |
| b1 | 0.400 | 0.580 | 0.016 | 0.023 |
| c | 0.350 | 0.440 | 0.014 | 0.017 |
| D | 4.400 | 4.600 | 0.173 | 0.181 |
| D1 | 1.550 REF | | 0.061 REF | |
| E | 2.300 | 2.600 | 0.091 | 0.102 |
| E1 | 3.940 | 4.250 | 0.155 | 0.167 |
| e | 1.500 TYP | | 0.060TYP | |
| e1 | 3.000 TYP | | 0.118TYP | |
| L | 0.900 | 1.200 | 0.035 | 0.047 |