

2.6 Watt Mono Filter-Free Class-D Audio Power Amplifier

Features

 \Box Efficiency With an 8- Ω Speaker:

88% at 400 mW 80% at 100 mW

80% at 100

- Image: 3.8mA Quiescent Current
- $\square \quad 0.4 \mu A Shutdown Current$
- Deptimized PWM Output Stage Eliminates LC Output Filter
- □ Internally Generated 250-kHz Switching Frequency Eliminates Capacitor and Resistor
- □ Improved PSRR (-75 dB) and Wide Supply Voltage (2.5 V to 5.5 V) Eliminates Need for a Voltage Regulator
- □ Fully Differential Design Reduces RF Rectification and Eliminates Bypass Capacitor
- □ Improved CMRR Eliminates Two Input Coupling Capacitors
- □ MSOP8, SOP8, DFN8 package

General Description

The BL6306 is a 2.6W high efficiency filter-free class-D audio power amplifier that requires only three external components.

Features like 88% efficiency, -75dB PSRR, and improved RF-rectification immunity make the BL6306 ideal for cellular handsets. In cellular handsets, the earpiece, speaker phone, and melody ringer can each be driven by the BL6306.

Applications

- □ Mobile phone、PDA、MID
- □ MP3/4、PMP
- Portable electronic devices

Order Information

Part Number	Package	Shipping
BL6306MM	MSOP8	3000 pcs / Tape & Reel
BL6306SO	SOP8	2500 pcs / Tape & Reel
BL6306DN	DFN8	3000 pcs / Tape & Reel

<u> Pin Diagrams</u>

http://www.belling.com.cn




DFN8 PACKAGE			SOP8/MSOP8 PACKAGE
(TOP VIEW)			(TOP VIEW)
SDB	1) (8 Vo-	SDB 1 8 Vo- NC 2 7 GND IN+ 3 6 VDD IN- 4 5 Vo+
NC	2) (7 GND	
IN+	3) (6 VDD	
IN-	4) (5 Vo+	

Pin Description

Pin #	Name	Description	
1	SDB	Shutdown terminal (low active)	
2	NC	NC (No internal connection)	
3	IN+	Positive differential input	
4	IN-	Negative differential input	
5	VO+	Positive BTL output	
6	VDD	Power Supply	
7	PGND	Power Ground	
8	VO-	Negative BTL output	

Function Block Diagram



Notes: Total Voltage Gain = $Av1 \times Av2 = 2 \times \frac{150k}{R_1}$

Figure 1. Function Block Diagram



Application Circuit




Figure 2. BL6306 Application Schematic With Differential Input




Figure 3. BL6306 Application Schematic With Differential Input and Input Capacitors




Figure 4. BL6306 Application Schematic With Single-Ended Input



Absolute Maximum Ratings

Supply Voltage	-0.3V to 6V
Input Voltage	-0.3V to VDD+0.3V
Storage Temperature	-65℃ to +150℃
Operating Temperature Ran	ge -40° C to $+85^{\circ}$ C

NOTE: <u>Absolute Maximum Ratings indicate limits beyond which damage to the device may occur. Operating</u> <u>Rating indicate conditions for which the device is functional, but do not guarantee specific performance limits.</u>

Electrical Characteristics

The following specifications apply for the circuit shown in Figure 5.

 $T_A = 25$ °C, unless otherwise specified.

	Parameter	Conditions	Spec			TT . M
Symbol			Min.	Тур.	Max.	Units
I _{SD}	Shutdown Current	V _{IN} =0V, V _{SDB} =0V, No Load		0.4	2	uA
		V_{DD} = 2.5V, V_{IN} = 0V, No Load		2.2	3.2	
I_Q	Quiescent Current	V_{DD} = 3.6V, V_{IN} = 0V, No Load		2.6		mA
		V_{DD} = 5.5V, V_{IN} = 0V, No Load		3.8	8	
		$V_{IN} = 0V, A_V = 2V/V,$			25	17
V_{OS}	Output Offset Voltage	$V_{DD} = 2.5 V$ to 5.5 V		2	25	mV
PSRR	Power Supply Rejection Ratio	$V_{DD} = 2.5 V$ to 5.5 V		-75		dB
	Common Mode Rejection Ratio	$V_{DD} = 2.5 V$ to 5.5 V,				dB
CMRR		$V_{\rm IC} = V_{\rm DD}/2$ to 0.5V,		-68		
		$V_{\rm IC} = V_{\rm DD}/2$ to $V_{\rm DD}$ - 0.8V				
F _{SW}	Modulation frequency	$V_{DD} = 2.5 V$ to 5.5 V	200	250	300	kHz
	N7.1($V_{DD} = 2.5V$ to 5.5V	270k	300k	330k	V/V
A_V	Voltage gain		R _I	R _I	R _I	
R _{SDB}	Resistance from SDB to GND			300		kΩ
ZI	Input impedance		135	150	165	kΩ
T _{WU}	Wake-up time from shutdown	$V_{DD} = 3.6V$		32		mS
		$V_{DD} = 2.5 V$		700		
r _{DS(on)}	Drain-Source resistance (on-state)	$V_{DD} = 3.6V$		500		mΩ
		$V_{DD} = 5.5 V$		400		
V _{SDIH}	Shutdown Voltage Input High		1.3			V
V _{SDIL}	Shutdown Voltage Input Low				0.4	V



Operating Characteristics

D $V_{DD} = 5V$, $R_I = 150k\Omega$, $T_A = 25^{\circ}C$, unless otherwise specified.

Sumbal	Parameter		Spec			I.I.m.ita
Symbol		Conditions	Min.	Тур.	Max.	Units
	P _O Output Power	THD+N=10%, f=1KHz, $R_L = 4\Omega$		2.60		
р		THD+N=1%, f=1KHz, $R_L = 4\Omega$		2.10		W
P ₀		THD+N=10%, f=1KHz, $R_L = 8\Omega$		1.60		
		THD+N=1%, f=1KHz, $R_L = 8\Omega$		1.30		
TUDIN	Total Harmonic		0.21		0/	
THD+N	Distortion + Noise	Po=1.0Wrms, f=1kHz, $R_L = 8\Omega$		0.21		%
SNR	Signal-to-Noise ratio	$V_{DD}=5V$, Po=1.0Wrms, $R_L = 8\Omega$		91		dB

\Box V_{DD} = 3.6V, R_I = 150k Ω , T_A = 25 °C, unless otherwise specified.

Symbol	Parameter	Conditions		Spec			Units
Symbol	rarameter			Min.	Тур.	Max.	Units
		THD+N=10%, f=1KHz, $R_L = 4$	Ω		1.35		
р	Output Douvor	THD+N=1%, f=1KHz, $R_L = 4\Omega$	2		1.08		W
Po	Output Power	THD+N=10%, f=1KHz, $R_L = 8$	Ω		0.85		vv
		THD+N=1%, f=1KHz, $R_L = 8\Omega$			0.69		
THD+N	Total Harmonic Distortion + Noise	Po=0.5Wrms, f=1kHz, $R_L = 8\Omega$			0.21		%
K _{SVR}	Supply ripple rejection ratio	V_{DD} = 3.6V, input ac-grounded with C _I = 2uF f=217Hz, V(Ripple)=200mV _{PP}			-65		dB
V			No weighting		100		υV
V _n	Output voltage noise	with $C_I = 2uF$, f=20~20kHz	A weighting		75		uV _{RMS}
CMRR	Common Mode Rejection Ratio	$V_{DD} = 3.6V, V_{IC} = 1 V_{PP}, f = 217Hz$			-70		dB

\Box V_{DD} = 2.5V, R_I = 150k Ω , T_A = 25°C, unless otherwise specified.

Symphol	Parameter	Conditions	Spec			Units
Symbol			Min.	Тур.	Max.	Units
	Output Power	THD+N=10%, f=1KHz, $R_L = 4\Omega$		0.60		W
D		THD+N=1%, f=1KHz, $R_L = 4\Omega$		0.51		
Po		THD+N=10%, f=1KHz, $R_L = 8\Omega$		0.40		
		THD+N=1%, f=1KHz, $R_L = 8\Omega$		0.33		
THD+N	Total Harmonic	$P_{0}=0.2W_{max}$ for $f=1$ by $P_{0}=80$		0.21		%
	Distortion + Noise	Po=0.2Wrms, f=1kHz, $R_L = 8\Omega$		0.21		70



Test Circuit





Figure 5. BL6306 test set up circuit





- Notes: 1>. C_S should be placed as close as possible to VDD/GND pad of the device
 - 2>. Ci should be shorted for any Common-Mode input voltage measurement
 - 3>. A 33uH inductor should be used in series with R_L for efficiency measurement
 - 4>. The 30 kHz LPF (shown in figure 5) is required even if the analyzer has an internal LPF

Component Recommended

Due to the weak noise immunity of the single-ended input application, the differential input application should be used whenever possible. The typical component values are listed in the table:

R _I	CI	Cs
150 k	3.3 nF	2 uF

http://www.belling.com.cn



- (1) C_1 should have a tolerance of $\pm 10\%$ or better to reduce impedance mismatch.
- (2) Use 1% tolerance resistors or better to keep the performance optimized, and place the R_I close to the device to limit noise injection on the high-impedance nodes.

Input Resistors (R_I) & Capacitors (C_I)

The input resistors (R_I) set the total voltage gain of the amplifier according to Eq1

$$Gain = \frac{2 \times 150k\Omega}{R_I} \quad \left(\frac{V}{V}\right) \qquad Eq1$$

The input resistor matching directly affects the CMRR, PSRR, and the second harmonic distortion cancellation.

If a differential signal source is used, and the signal is biased from $0.5V \sim V_{DD}$ -0.8V (shown in Figure2), the input capacitor (C₁) is not required.

If the input signal is not biased within the recommended common-mode input range in differential input application (shown in Figure 3), or in a single-ended input application (shown in Figure 4), the input coupling capacitors are required.

If the input coupling capacitors are used, the R_1 and C_1 form a high-pass filter (HPF). The corner frequency (f_C) of the HPF can be calculated by *Eq2*

$$f_C = \frac{1}{2\pi \cdot R_I \cdot C_I} \quad (Hz) \qquad Eq2$$


Decoupling Capacitor (Cs)

A good low equivalent-series-resistance (ESR) ceramic capacitor (C_S), used as power supply decoupling capacitor (C_S), is required for high power supply rejection (PSRR), high efficiency and low total harmonic distortion (THD). C_S is 2µF, placed as close as possible to the device VDD pin.



Package Dimensions

SOP8






MSOP8


3.000±0.1


RO. 127






DFN8









OVMDOI	MILLIMETER			
SYMBOL	MIN	NOM	MAX	
А	0.70	0.75	0.80	
A1	-	0.02	0.05	
b	0.25	0.30	0.35	
с	0.18	0.20	0.25	
D	2.90	3.00	3.10	
D2		2.50RE	F	
e		0.65BS	С	
Nd		1.95BS	С	
Е	2.90	3.00	3.10	
E2	1.55REF			
L	0.30	0.40	0.50	
h	0.20	0.25	0.30	