

SUPER-SEMI



SUPER-MOSFET

Super Junction Metal Oxide Semiconductor Field Effect Transistor

800V Super Junction Power MOSFET SS*80R380S

Rev. 1.4 Aug. 2019

www.supersemi.com.cn



September, 2013

SJ-FET

SSF80R380S/SSP80R380S/SSW80R380S/SSA80R380S 800V N-Channel MOSFET

Description

SSMOS-FET is new generation of high voltage MOSFET family that is utilizing an advanced charge balance mechanism for outstanding low on-resistance and lower gate charge performance. This advanced technology has been tailored to minimize conduction loss, provide superior switching performance, and withstand extreme dv/dt rate and higher avalanche energy. SJ-FET is suitable for various AC/DC power conversion in switching mode operation for higher efficiency.

Features

- Multi-Epi process SJ-FET
- 850V @TJ = 150 ℃
- Typ. RDS(on) = 0.36Ω
- Ultra Low Gate Charge (typ. Qg = 17.5nC)
- 100% avalanche tested



Absolute Maximum Ratings

Symbol	Parameter		SSP_W_A80R380S	SSF80R380S	Unit
V_{DSS}	Drain-Source Voltage		800		V
I _D	Drain Current -Continuous (TC = 25°C) -Continuous (TC = 100°C)		13.6* 8.6*		Α
I _{DM}	Drain Current - Pulsed	(Note 1)	40*		Α
V_{GSS}	Gate-Source voltage		±30		V
E _{AS}	Single Pulsed Avalanche Energy (Note		284		mJ
I _{AR}	Repetitive Avalanche Current (Note 1)		2.4		Α
Ear	Repetitive Avalanche Energy (Note 1)		0.43		mJ
dv/dt	Peak Diode Recovery dv/dt (Note 3)		15		V/ns
dVds/dt	Drain Source voltage slope (Vds=640V)		50		V/ns
P_D	Power Dissipation (TC = 25°C)		104	32	W
T _J , T _{STG}	Operating and Storage Temperature Range		-55 to +150		°C
TL	Maximum Lead Temperature for Soldering Purpose, 1/8" from Case for 5 Seconds		300		°C

^{*} Drain current limited by maximum junction temperature. Maximum duty cycle D=0.75.

Thermal Characteristics

Symbol	Parameter	SSP_W_A80R380S	SSF80R380S	Unit
R _{BJC} Thermal Resistance, Junction-to-Case		1.2	3.9	°C/W
R _{ecs} Thermal Resistance, Case-to-Sink Typ.		0.5	-	°C/W
R _{BJA} Thermal Resistance, Junction-to-Ambient		62	80	°C/W



Electrical Characteristics TC = 25°C unless otherwise noted

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Off Characterist	tics					'
BVDSS	Drain-Source Breakdown Voltage	VGS = 0V, ID = 250µA, TJ = 25°C	800	-	-	V
		VGS = 0V, ID = 250μA, TJ = 150°C	-	850	-	V
ΔBVDSS / ΔTJ	Breakdown Voltage Temperature Coefficient	ID = 250µA, Referenced to 25°C	-	0.6	ı	V/°C
IDSS	Zero Gate Voltage Drain Current	VDS = 800V, VGS = 0V -TJ = 150°C	-	- 10	1 -	μA μA
IGSSF	Gate-Body Leakage Current, Forward	VGS = 30V, VDS = 0V	-	-	100	nA
IGSSR	Gate-Body Leakage Current, Reverse	VGS = -30V, VDS = 0V	-	-	-100	nA
On Characterist	tics					•
VGS(th)	Gate Threshold Voltage	VDS = VGS, ID = 250µA	2.5	3.5	4.5	V
RDS(on)	Static Drain-Source On-Resistance	VGS = 10V, ID = 7.5A	-	0.36	0.41	Ω
gFS	Forward Transconductance	VDS = 40V, ID = 15A	-	12	-	S
Dynamic Charac	cteristics					
Ciss	Input Capacitance	VDS = 25V, VGS = 0V,	-	800	-	pF
Coss	Output Capacitance	f = 1MHz	-	230	-	pF
Crss	Reverse Transfer Capacitance			15	-	pF
Switching Chara	acteristics					
td(on)	Turn-On Delay Time	VDD = 400V, ID = 7.5A, RG =	-	31	-	ns
tr	Turn-On Rise Time	25Ω(Note 4)	-	19	-	ns
td(off)	Turn-Off Delay Time		-	91	•	ns
tf	Turn-Off Fall Time		-	20	-	ns
Qg	Total Gate Charge	VDS = 450V, ID = 7.5A, VGS =	-	17.5	-	nC
Qgs	Gate-Source Charge	10V (Note 4)	-	4.1	-	nC
Qgd	Gate-Drain Charge		-	7.1	-	nC
Drain-Source D	iode Characteristics and Maximum Rating	S				
Is	Maximum Continuous Drain-Source Diode Forward Current			-	14	Α
Ism	Maximum Pulsed Drain-Source Diode	Maximum Pulsed Drain-Source Diode Forward Current		-	40	Α
VsD	Drain-Source Diode Forward Voltage	Vgs = 0V, Is = 15A		0.9	1.5	V
trr	Reverse Recovery Time	$V_R = 400V, VGS = 0V,$	-	660	ı	ns
Qrr	Reverse Recovery Charge	IF = 15A, dIF/dt =100A/μs	-	9.7	ı	μC
I _{rrm}	Peak reverse recovery Current		-	25	-	Α

NOTES:

- Repetitive Rating: Pulse width limited by maximum junction temperature 2. I_{AS} =2.4A, VDD=50V, Starting TJ=25 °C 3. I_{SO} =ID, di/dt ≤ 200A/us, V_{DD} ≤ BV_{DSS}, Starting TJ = 25 °C 4. Essentially Independent of Operating Temperature Typical Characteristics






Figure 1: On-Region Characteristics@25°C




Figure 2: On-Region Characteristics@125°C




Figure 3:Power Dissipation TO-220, TO-247




Figure 4: Power dissipation TO-220FullPAK






Figure 5: On-Resistance vs. Junction Temperature




Figure 6: On-Resistance vs. Drain Current, Tj=125°C




Figure 7: Body-Diode Characteristics




Figure 8: Gate-Charge Characteristics






Figure 9: Capacitance Characteristics





Figure 10: $C_{\rm oss}$ stored Energy



Tc=25°C, TO-220, TO-247




Figure 12: Maximum Forward Biased Safe Operating Area Tc=25°C, TO-220 FullPAK






Figure 13: Break Down vs. Junction Temperature




Figure 14: Typical transfer characteristics




Figure 15: Maximum Transient Thermal Impedance TO-220, TO-247




Figure 16: Maximum Transient Thermal Impedance TO-220 FullPAK








Figure 17: Avalanche energy




Test circuits


Switching times test circuit and waveform for inductive load





Unclamped inductive load test circuit and waveform










Test circuits


Test circuit and waveform for diode characteristics















COMMON DIMENSIONS

SYMBOL	MM			
SIMBOL	MIN	NOM	MAX	
E	10.00	10.16	10.32	
E1	9.94	10.04	10.14	
E2	9.36	9.46	9.56	
A	4.50	4.70	4.90	
A1	2.34	2.54	2.74	
A4	2.66	2.76	2.86	
A5		1.00REF		
с	0.45	0.50	0.60	
D	15.67	15.87	16.07	
Q		9. 40REF		
H1		6.70REF		
e		2.54BSC		
ФΡ		3. 18REF		
L	12.78	12.98	13.18	
L1	2.83	2. 93	3. 03	
L2	7.70	7.80	7. 90	
ФР1	1.40	1.50	1.60	
ФР2	0.95	1.00	1.05	
ФР3		3. 45REF		
θ 1	3°	5°	7°	
θ2	-	45°	-	
F1	1.00	1.50	2.00	
F2	13.80	13.90	14.00	
F3	3.20	3. 30	3. 40	
F4	5.30	5. 40	5. 50	
G	7.80	8.00	8.20	
G1	6.90	7.00	7.10	
G3	1.25	1.35	1.45	
b1	1.23	1.28	1.38	
b2	0.75	0.80	0.90	
K1	0.65	0.70	0.75	
R	0. 50REF			




Package Outline

TO-220








COMMON DIMENIONS


SYMBOL	MM			
SIMBUL	MIN	NDM	MAX	
A	4.40	4.57	4.70	
A1	1.27	1.30	1.37	
A2	2.35	2.40	2.50	
Ь	0.77	0.80	0.90	
b2	1.17	1.27	1.36	
С	0.48	0.50	0.56	
D	15.40	15.60	15.80	
D1	9.00	9.10	9.20	
DEP	0.05	0.10	0.20	
Ε	9.80	10.00	10.20	
E1	38 — 11	8.70		
E2	9.80	10.00	10.20	
ØP1	1.40	1.50	1.60	
e	2.54BSC			
e1	5.08BSC			
H1	6.40	6.50	6.60	
L	12.75	13.50	13.65	
L1	-	3.10	3.30	
L2		2.50REF		
ΦP	3.50	3.60	3.63	
q	2.73	2.80	2.87	
θ1	5	7	9,	
θ2	1"	3.	5	
θ3	1'	3"	5'	



Package Outline

TO-247






COMMON DIMENSIONS

	MM			
SYMBOL	MIN	NOM	MAX	
A	4.90	5.00	5.10	
A1	2.31	2.41	2.51	
A2	1.90	2.00	2.10	
ь	1.16	1.21	1.26	
b2	1.96	2.01	2.06	
b4	2.96	3.01	3.06	
с	0.59	0.61	0.66	
D	20.90	21.00	21.10	
D1	16.25	16.55	16.85	
D2	1.05	1.20	1.35	
E	15.70	15.80	15.90	
E1	13.10	13.30	13.50	
E2	4.90	5.00	5.10	
E3	2.40	2.50	2.60	
e		5.44BSC		
h	0.05	0.10	0.15	
L	19.80	19.92	20.10	
L1	-	-	4.30	
ΦР	3.50	3.60	3.70	
ФР1			7.30	
ФР2	2.40	2.50	2.60	
Q	5.60	5.80	6.00	
S	6.15BSC			
R		0.50REF		
T	9.80 -		10.20	
T1	1.65REF			
T2	8.00REF			
T3	12.80REF			
U	6.00		6.40	
θ1	6°	7°	8°	
θ2	4°	5°	6°	
63	1°		1.5°	
94	14°	15°	16°	



Package Outline

TO-3P



റവ	MON	DIMENSIONS
	WICH	DIMERNSIONS

MM			
MIN	NOM	MAX	
4.60	4.80	5.00	
1.40	1.50	1.60	
1.33	1.38	1.43	
0.80	1.00	1.20	
2.80	3.00	3.20	
1.80	2.00	2.20	
0.50	0.60	0.70	
	19.90	20.05	
13.70	13.90	14.10	
	12.90REF	1	
15.40	15.60	15.80	
13.40	13.60	13.80	
9.40	9.60	9.80	
	5.45 TYP		
4.60	4.80	5.00	
40.30	40.50	40.70	
23.20	23.40	23.60	
0.05	0.10	0.15	
		•	
	1.00 REF		
6.90	7.00	7.10	
	3.20 REF		
3.50 REF			
1.40	1.50	1.60	
0.50 REF			
5.00 REF			
12.56	12.76	12.96	
7.8	8	8.2	
	7°	9°	
1° 3° 5°			
60° REF			
	4.60 1.40 1.33 0.80 2.80 1.80 0.50 19.75 13.70 15.40 13.40 9.40 4.60 40.30 23.20 0.05 6.90 1.40	MIN NOM 4.60 4.80 1.40 1.50 1.33 1.38 0.80 1.00 2.80 3.00 1.80 2.00 0.50 0.60 19.75 19.90 13.70 13.90 12.90REF 15.40 15.60 13.40 9.60 9.40 9.60 4.80 40.30 40.50 23.20 23.40 0.05 0.10 7.40 TYP 9.00 TYP 11.00 REF 6.90 7.00 3.20 REF 3.50 REF 1.40 1.56 12.76 7.8 8 5° 7° 1° 3°	



DISCLAIMER

SUPER SEMICONDUCTOR reserves the right to make changes WITHOUT further notice to any products herein to improve reliability, function, or design.

For documents and material available from this datasheet, SUPER SEMICONDUCTOR does not warrant or assume any legal liability or responsibility for the accuracy, completeness of any product or technology disclosed hereunder.

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, SUPER SEMICONDUCTOR hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

The products shown herein are not designed for use as critical components in medical, life-saving, or life-sustaining applications, whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness. Customers using or selling SUPER SEMICONDUCTOR products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify SUPER SEMICONDUCTOR for any damages arising or resulting from such use or sale.

INFORMATION

For further information on technology, delivery terms and conditions and prices, please contact SUPER SEMICONDUCTOR office or website (www.supersemi.com.cn).