

# ATC 100 B Series Porcelain Superchip® Multilayer Capacitors

- Case B Size (.110" x .110")
- High Q
- Low ESR/ESL
- Low Noise
- Extended WVDC up to 1500 VDC
- Capacitance Range 0.1 pF to 1000 pF
- Ultra-Stable Performance
- High Self-Resonance
- Established Reliability (QPL)

ATC, the industry leader, offers new improved ESR/ESL performance for the 100 B Series RF/Microwave Capacitors. This Series is now available with extended operating temperatures up to 175°C. High Density porcelain construction provides a rugged, hermetic package.

Typical functional applications: Bypass, Coupling, Tuning, Feedback, Impedance Matching and DC Blocking.

Typical circuit applications: UHF/Microwave RF Power Amplifiers, Mixers, Oscillators, Low Noise Amplifiers, Filter Networks, Timing Circuits and Delay Lines.

## ENVIRONMENTAL TESTS

ATC 100 B Series Capacitors are designed and manufactured to meet and exceed the requirements of EIA-198, MIL-PRF-55681 and MIL-PRF-123.

**THERMAL SHOCK:** MIL-STD-202, Method 107, Condition A.

**MOISTURE RESISTANCE:** MIL-STD-202, Method 106.

### LOW VOLTAGE HUMIDITY:


MIL-STD-202, Method 103, Condition A, with 1.5 Volts DC applied while subjected to an environment of 85°C with 85% relative humidity for 240 hours min.

### LIFE TEST:

MIL-STD-202, Method 108, for 2000 hours, at 125°C.

Voltage Applied:

200% of WVDC for capacitors rated at 500 volts DC or less.  
120% of WVDC for capacitors rated at 1250 volts DC or less.  
100% of WVDC for capacitors rated above 1250 volts DC.



## ELECTRICAL AND MECHANICAL SPECIFICATIONS

**QUALITY FACTOR (Q):** greater than 10,000 at 1 MHz.

### TEMPERATURE COEFFICIENT OF CAPACITANCE (TCC):

+90 ±20 PPM/°C (-55°C to +125°C)  
+90 ±30 PPM/°C (+125°C to +175°C)

### INSULATION RESISTANCE (IR):

0.1 pF to 470 pF:  
10<sup>6</sup> Megohms min. @ +25°C at rated WVDC.  
10<sup>5</sup> Megohms min. @ +125°C at rated WVDC.

510 pF to 1000 pF:  
10<sup>5</sup> Megohms min. @ +25°C at rated WVDC.  
10<sup>4</sup> Megohms min. @ +125°C at rated WVDC.

IR above +125°C is derated by one order of magnitude.

**WORKING VOLTAGE (WVDC):** See Capacitance Values Table, page 2.

### DIELECTRIC WITHSTANDING VOLTAGE (DWV):

250% of WVDC for capacitors rated at 500 volts DC or less for 5 seconds.  
150% of WVDC for capacitors rated at 1250 volts DC or less for 5 seconds.  
120% of WVDC for capacitors rated above 1250 Volts DC for 5 seconds.  
Test voltage is applied for 5 secs.

**RETRACE:** Less than ±(0.02% or 0.02 pF), whichever is greater.

**AGING EFFECTS:** None

**PIEZOELECTRIC EFFECTS:** None

(No capacitance variation with voltage or pressure).

**CAPACITANCE DRIFT:** ±(0.02% or 0.02 pF), whichever is greater.

### OPERATING TEMPERATURE RANGE:

Standard WVDC:

0.1 to 330 pF: from -55°C to +175°C  
360 to 1000 pF: from -55°C to +125°C

Extended WVDC:

0.1 to 1000 pF: from -55°C to +125°C  
(No derating of working voltage).

### TERMINATION STYLES:

Available in various surface mount and leaded styles.  
See Mechanical Configurations, page 3.

**TERMINAL STRENGTH:** Terminations for chips and pellets withstand a pull of 5 lbs. min., 15 lbs. typical, for 5 seconds in direction perpendicular to the termination surface of the capacitor. Test per MIL-STD-202, method 211.



**AMERICAN**  
ATC North America  
sales@atceramics.com

**TECHNICAL**  
ATC Europe  
saleseur@atceramics.com

**CERAMICS**  
ATC Asia  
sales@atceramics-asia.com

**THE ENGINEERS' CHOICE®**  
ISO 9001 REGISTERED COMPANY  
ATC # 001-807 Rev. T, 2/20

**THE ENGINEERS' CHOICE®**

**www.atceramics.com**


# ATC 100 B Capacitance Values

CAP. CODE	CAP. (pF)	TOL.	RATED WVDC		CAP. CODE	CAP. (pF)	TOL.	RATED WVDC		CAP. CODE	CAP. (pF)	TOL.	RATED WVDC		CAP. CODE	CAP. (pF)	TOL.	RATED WVDC																			
			STD.	EXT.				STD.	EXT.				STD.	EXT.				STD.	EXT.																		
0R1	0.1	B	500	1500	2R4	2.4	B, C, D	500	1500	200	20	F, G, J, K, M	500	1500	151	150	F, G, J, K, M	300	EXT.																		
0R2	0.2				2R7	2.7				220	22				161	160			1000																		
0R3	0.3	3R0			3.0	240				24	181				180	VOLT.																					
0R4	0.4	3R3			3.3	270				27	201				200																						
0R5	0.5	3R6			3.6	300				30	221				220	200		EXT.																			
0R6	0.6	3R9			3.9	330				33	241				240																						
0R7	0.7	4R3			4.3	360				36	271				270			VOLT.																			
0R8	0.8	4R7			4.7	390				39	301				300																						
0R9	0.9	5R1			5.1	430				43	331				330	100		EXT.																			
1R0	1.0	5R6			5.6	470				47	361				360																						
1R1	1.1	6R2	6.2	510	51	391	390																														
1R2	1.2	B, C, D	500	1500	6R8	6.8	B, C, J, K, M	500	1500	560	56	F, G, J, K, M	500	1500	431	430	F, G, J, K, M	200	EXT.																		
1R3	1.3				7R5	7.5				620	62				471	470																					
1R4	1.4				8R2	8.2				680	68				511	510																					
1R5	1.5				9R1	9.1				750	75				561	560																					
1R6	1.6	B, C, D			500	1500				100	10				F, G, J, K, M	500		1500	820	82	F, G, J, K, M	500	1500	621	620	F, G, J, K, M	100	EXT.									
1R7	1.7									110	11								910	91				681	680												
1R8	1.8									120	12								101	100				751	750												
1R9	1.9									130	13								111	110				821	820												
2R0	2.0	B, C, D								500	1500								150	15				F, G, J, K, M	500		1500	121	120	F, G, J, K, M	500	1500	911	910	F, G, J, K, M	50	EXT.
2R1	2.1																		160	16								131	130				102	1000			
2R2	2.2		180	18																																	

VRMS = 0.707 X WVDC

• SPECIAL VALUES, TOLERANCES, HIGHER WVDC AND MATCHING AVAILABLE. • ENCAPSULATION OPTION AVAILABLE. PLEASE CONSULT FACTORY. NOTE: EXTENDED WVDC DOES NOT APPLY TO CDR PRODUCTS.

## ATC PART NUMBER CODE



The above part number refers to a 100 B Series (case size B) 91 pF capacitor, J tolerance (±5%), 500 WVDC, with W termination (Tin/Lead, Solder Plated over Nickel Barrier), laser marking and Tape and Reel packaging.

ATC accepts orders for our parts using designations **with** or **without** the "ATC" prefix. Both methods of defining the part number are equivalent, i.e., part numbers referenced with the "ATC" prefix are interchangeable to parts referenced without the "ATC" prefix. Customers are free to use either in specifying or procuring parts from American Technical Ceramics.

For additional information and catalogs contact your ATC representative or call direct at (631) 622-4700.

Consult factory for additional performance data.

**A M E R I C A N T E C H N I C A L C E R A M I C S**

ATC North America  
sales@atceramics.com

ATC Europe  
sales@atceramics.com

ATC Asia  
sales@atceramics-asia.com

# ATC 100 B Capacitors: Mechanical Configurations

ATC SERIES & CASE SIZE	ATC TERM. CODE	MIL-PRF-55681	CASE SIZE & TYPE	OUTLINE W/T IS A TERMINATION SURFACE	BODY DIMENSIONS INCHES (mm)			LEAD AND TERMINATION DIMENSIONS AND MATERIALS			
					LENGTH (L)	WIDTH (W)	THICKNESS (T)	OVERLAP (Y)	MATERIALS		
100B	W	CDR14BG	B Solder Plate		.110 + .020 - .010 (2.79 + 0.51 -0.25)	.110 ± 0.015 (2.79 ± 0.38)	.102 (2.59) max..	.015 (0.38) ± 0.010 (0.25)	Tin /Lead, Solder Plated over Nickel Barrier Termination		
100B	P	CDR14BG	B Pellet		.110 + .035 - .010 (2.79 + 0.89 -0.25)	.110 ± 0.015 (2.79 ± 0.38)			Heavy Tin/Lead Coated, over Nickel Barrier Termination		
100B	T	N/A	B Solderable Nickel Barrier		.110 + .035 - .010 (2.79 + 0.51 -0.25)	.110 ± 0.015 (2.79 ± 0.38)			<b>RoHS Compliant</b> Tin Plated over Nickel Barrier Termination		
100B	CA	CDR13BG	B Gold Chip		.110 + .020 - .010 (2.79 + 0.51 -0.25)	.110 ± 0.015 (2.79 ± 0.38)			<b>RoHS Compliant</b> Gold Plated over Nickel Barrier Termination		
100B	MS	CDR21BG	B Microstrip		.135 ± 0.015 (3.43 ± 0.38)	.110 ± 0.015 (2.79 ± 0.38)	.120 (3.05) max.	N/A	Length (L <sub>L</sub> )	Width (W <sub>L</sub> )	Thickness (T <sub>L</sub> )
100B	AR	CDR22BG	B Axial Ribbon						.250 (6.35) min.	.093 ± .005 (2.36 ± 0.13)	.004 ± .001 (.102 ± .025)
100B	RR	CDR24BG	B Radial Ribbon						.145 ± 0.020 (3.68 ± 0.51)	.102 (2.59) max.	N/A
100B	RW	CDR23BG	B Radial Wire		100B	AW	CDR25BG	B Axial Wire			

Additional lead styles available: Narrow Microstrip (NM), Narrow Axial Ribbon (NA) and Vertical Narrow Microstrip (H). Other lead lengths are available; consult factory. All leads are high purity silver attached with high temperature solder and are **RoHS** compliant. For a complete military catalog, request American Technical Ceramics document ATC 001-818.

**A M E R I C A N T E C H N I C A L C E R A M I C S**

ATC North America  
sales@atceramics.com

ATC Europe  
sales@atceramics.com

ATC Asia  
sales@atceramics-asia.com

# ATC 100 B Non-Magnetic Capacitors: Mechanical Configurations

ATC SERIES & CASE SIZE	ATC TERM. CODE	MIL-PRF-55681	CASE SIZE & TYPE	OUTLINES W/T IS A TERMINATION SURFACE	BODY DIMENSIONS INCHES (mm)			LEAD AND TERMINATION DIMENSIONS AND MATERIALS			
					LENGTH (L)	WIDTH (W)	THICKNESS (T)	OVERLAP (Y)	MATERIALS		
100B	WN	Meets Requirements	B Non-Mag Solder Plate		.110 + .025 - .010 (2.79 + 0.64 - 0.25)	.110 ± .015 (2.79 ± 0.38)	.102 (2.59) max..	.102 (2.59) ±.010 (0.25)	Tin/Lead, Solder Plated over Non-Magnetic Barrier Termination		
100B	PN	Meets Requirements	B Non-Mag Pellet		.110 + .035 - .010 (2.79 + 0.89 - 0.25)	.110 ± .015 (2.79 ± 0.38)			Heavy Tin/Lead, Coated over Non-Magnetic Barrier Termination		
100B	TN	Meets Requirements	B Non-Mag Solderable Barrier		.110 + .025 - .010 (2.79 + 0.64 - 0.25)	.110 ± .015 (2.79 ± 0.38)			<b>RoHS Compliant</b> Tin Plated over Non-Magnetic Barrier Termination		
100B	MN	Meets Requirements	B Non-Mag Microstrip		.135 ± .015 (3.43 ± 0.38)	.110 ± .015 (2.79 ± 0.38)	.120 (3.05) max.	N/A	Length (L <sub>L</sub> )	Width (W <sub>L</sub> )	Thickness (T <sub>L</sub> )
100B	AN	Meets Requirements	B Non-Mag Axial Ribbon						.250 (6.35) (6.35) min.	.093 ± .005 (2.36 ± 0.13)	.004 ± .001 (.102 ± .025)
100B	FN	Meets Requirements	B Non-Mag Radial Ribbon						.145 ± .020 (3.68 ± 0.51)	.102 (2.59) max.	N/A
100B	RN	Meets Requirements	B Non-Mag Axial Wire								
100B	BN	Meets Requirements	B Non-Mag RadialWire								

Additional lead styles available: Narrow Microstrip (DN), Narrow Axial Ribbon (GN) and Vertical Narrow Microstrip (HN). Other lead lengths are available; consult factory. All leads are high purity silver attached with high temperature solder and are RoHS compliant.

## Suggested Mounting Pad Dimensions

Horizontal Electrode Orientation

Vertical Electrode Orientation

Case B Vertical Mount

Cap Value	Pad Size	A Min.	B Min.	C Min.	D Min.
0.1 pF	Normal	.065	.050	.075	.175
	High Density	.045	.030	.075	.135
0.2 pF	Normal	.090	.050	.075	.175
	High Density	.070	.030	.075	.135
0.3 to 510 pF	Normal	.110	.050	.075	.175
	High Density	.090	.030	.075	.135
> 510 pF	Normal	.120	.050	.075	.175
	High Density	.100	.030	.075	.135

Horizontal Mount

All values	Pad Size	A Min.	B Min.	C Min.	D Min.
All values	Normal	.130	.050	.075	.175
	High Density	.110	.030	.075	.135

A M E R I C A N T E C H N I C A L C E R A M I C S


ATC North America  
sales@atceramics.com

ATC Europe  
sales@atceramics.com


ATC Asia  
sales@atceramics-asia.com

# ATC 100 B Performance Data


**ESR VS. CAPACITANCE  
ATC SERIES 100, CASE B**




**Q VS. CAPACITANCE  
ATC SERIES 100, CASE B**




**ESR VS. CAPACITANCE  
ATC SERIES 100, CASE B**




**Q VS. CAPACITANCE  
ATC SERIES 100, CASE B**



**SERIES RESONANCE VS. CAPACITANCE  
ATC SERIES 100, CASE B**




**CAPACITANCE CHANGE VS. TEMPERATURE  
ATC SERIES 100, CASE B**




# ATC 100 B Performance Data


**CURRENT RATING VS. CAPACITANCE  
ATC SERIES 100, CASE B**



**CURRENT RATING VS. CAPACITANCE  
ATC SERIES 100, CASE B**



**CURRENT RATING VS. CAPACITANCE  
ATC SERIES 100, CASE B, EXTENDED VOLTAGE**



Sales of ATC products are subject to the terms and conditions contained in American Technical Ceramics Corp. Terms and Conditions of Sale (ATC document #001-992 Rev. B; 12/05). Copies of these terms and conditions will be provided upon request. They may also be viewed on ATC's website at [www.atceramics.com/productfinder/default.asp](http://www.atceramics.com/productfinder/default.asp). Click on the link for Terms and Conditions of Sale.

ATC has made every effort to have this information as accurate as possible. However, no responsibility is assumed by ATC for its use, nor for any infringements of rights of third parties which may result from its use. ATC reserves the right to revise the content or modify its product without prior notice.

© 1996 American Technical Ceramics Corp. All Rights Reserved

ATC # 001-807 Rev. T, 2/20



**AMERICAN**  
ATC North America  
sales@atceramics.com

**TECHNICAL**  
ATC Europe  
sales@atceramics.com

**CERAMICS**  
ATC Asia  
sales@atceramics-asia.com

**THE ENGINEERS' CHOICE®**  
ISO 9001 REGISTERED  
COMPANY

**THE ENGINEERS' CHOICE®**

**www.atceramics.com**