


GPSR1050-Series

GPSR系列產品符合“實用新型-貼片式功率電感器”專利，專利號：ZL 2009 2 0129705.8



實物圖:




推薦焊盤:



尺寸: (Unit:mm)



命名方式:



特性參數:

Part Number 型號	Inductance 電感量 (μH) @100KHz, 1V	DC Resistance 直流電阻 (mΩ)		Heat Rating Current 溫升電流(A)	Saturation Current 飽和電流(A)
		典型值 Typical	最大值 Max		
GPSR1050-5R2M	5.2	16	21	5.5	10
GPSR1050-150M	15	39	52	3.6	6
GPSR1050-220M	22	73	92	4	6
GPSR1050-330M	33	107	120	3	5
GPSR1050-470M	47	160	210	3	4
GPSR1050-680M	68	240	300	3	4
GPSR1050-101M	100	320	400	2	3

典型電流重疊與溫升特性曲線

