

TECHNICAL DATA SHEET

Description: 2.4-2.4835GHz Ceramic SMT

antenna, 4x4.25mm keep out area

PART NUMBER: W3008



Features:

2400-2483.5MHz

Size: 3.2 x 1.6 x 1.1mm

• Efficiency: 66 %

Gain: 1.1 dBi

Polarization: Linear

Power Handling: 5W

RoHS Compliant

Moisture Sensitivity Level MSL3

Applications:

- · Bluetooth, BLE, Zigbee, WiFi
- · 2.4GHz ISM band radios

All dimensions are in mm / inches

Issue: 1823

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden.

For more information:

Pulse Worldwide Headquarters 15255 Innovation Drive #100 San Diego, CA 92128 USA Tel:1-858-674-8100 Pulse/Larsen Antennas 18110 SE 34th St Bldg 2 Suite 250 Vancouver, WA 98683 USA Tel: 1-360-944-7551 Europe Headquarters Pulse GmbH & Do, KG Zeppelinstrasse 15 Herrenberg, Germany Tel: 49 7032 7806 0 Pulse (Suzhou) Wireless Products Co, Inc. 99 Huo Ju Road(#29 Bldg,4th Phase Suzhou New District Jiangsu Province, Suzhou 215009 PR China Tel: 86 512 6807 9998



TECHNICAL DATA SHEET

Description: 2.4-2.4835GHz Ceramic SMT antenna, 4x4.25mm keep out area

PART NUMBER: W3008

ELECTRICAL SPECIFICATIONS

Frequency	2400-2483.5MHz
Nominal Impedance	50 Ω
Return Loss	-4dB
Radiation Pattern	Omni
Gain	1.1dBi
Efficiency	66%
Polarization	linear
Power Withstanding	5W

MECHANICAL SPECIFICATIONS

Overall Length 3.2x1.6x1.1mm
Weight 33mg
Antenna Color / Material Ceramic

ENVIRONMENTAL SPECIFICATIONS

Operating Temperature $-40\sim+85^{\circ}$ C Storage Temperature $-40\sim+85^{\circ}$ C RoHS Compliant Yes

(*) All RF parameters measured on 80*37mm PCB with 4*4.25mm clearance in free space. No matching component used.






TECHNICAL DATA SHEET

Description: 2.4-2.4835GHz Ceramic SMT

antenna, 4x4.25mm keep out area

PART NUMBER: W3008

MECHANICAL DRAWING AND TERMINAL CONFIGURATION



No.	Terminal Name	Terminal Dimensions
1	Feed /GND	0.62 x 1.36 mm
2	Feed /GND	0.62 x 1.36 mm
Antenna is symmetrical, either one of pads 1 or 2 can be used as feed terminal		




TECHNICAL DATA SHEET

Description: 2.4-2.4835GHz Ceramic SMT antenna, 4x4.25mm keep out area


PART NUMBER: W3008

MECHANICAL DRAWING AND TERMINAL CONFIGURATION

Ground cleared under antenna, clearance area 4 mm x 4.25mm



Ground Via Hole Ground area should be surround with ground via holes



Feed line 500hm
Any type of 50 Ohm feed line can be used, inner layers on feed line area need to designed to give 50 Ohm characteristics to feed line.





TECHNICAL DATA SHEET

Description: 2.4-2.4835GHz Ceramic SMT


antenna, 4x4.25mm keep out area

PART NUMBER: W3008

Series: Chip Antenna

MECHANICAL DRAWING AND TERMINAL CONFIGURATION

Recommended Antenna Pad Dimensions on PCB Layout (top surface) Ground cleared under antenna, clearance area 4 mm x 4.25 mm



PCB contact pads		
No.	Terminal Name	Terminal Dimensions
1	Feed	0,80 x 0,65 mm
2	GND	0,80 x 0,65 mm
3	GND	0,80 x 1,60 mm





TECHNICAL DATA SHEET


Description: 2.4-2.4835GHz Ceramic SMT antenna, 4x4.25mm keep out area

antenna, 4x4.25mm keep ou

PART NUMBER: W3008

MECHANICAL DRAWING AND TERMINAL CONFIGURATION

Recommended Antenna Pad Dimensions on PCB Layout (bottom surface) Ground cleared under antenna, clearance area 4 mm x 4.25 mm









TECHNICAL DATA SHEET

Description: 2.4-2.4835GHz Ceramic SMT


antenna, 4x4.25mm keep out area


PART NUMBER: W3008

Series: Chip Antenna

MECHANICAL DRAWING AND TERMINAL CONFIGURATION

Recommended test board layout for electrical characteristic measurement, test board outline size 80 x 37mm









TECHNICAL DATA SHEET

Description: 2.4-2.4835GHz Ceramic SMT antenna, 4x4.25mm keep out area

PART NUMBER: W3008

CHARTS Return loss Return Loss 0.0 -2.0-4.0-6.0 -8.0 -10.0 -12.0 2010 Frequency(MHz) Return Loss Spec


(*) All RF parameters measured on 80*37mm PCB with 4*4.25mm clearance in free space. No matching component used.



TECHNICAL DATA SHEET

Description: 2.4-2.4835GHz Ceramic SMT antenna, 4x4.25mm keep out area

PART NUMBER: W3008



(*) All RF parameters measured on 80*37mm PCB with 4*4.25mm clearance in free space. No matching component used.

Issue: 1823

ROHS



TECHNICAL DATA SHEET

Description: 2.4-2.4835GHz Ceramic SMT antenna, 4x4.25mm keep out area

PART NUMBER: W3008

CHARTS Peak Gain(dBi) Peak Gain(dBi) 1.2 0.8 0.6 0.4 0.2

(*) All RF parameters measured on 80*37mm PCB with 4*4.25mm clearance in free space. No matching component used.

Issue: 1823



10




TECHNICAL DATA SHEET

Description: 2.4-2.4835GHz Ceramic SMT antenna, 4x4.25mm keep out area

PART NUMBER: W3008

CHARTS

Free Space Radiation Pattern



(*) All RF parameters measured on 80*37mm PCB with 4*4.25mm clearance in free space. No matching component used.






TECHNICAL DATA SHEET

Description: 2.4-2.4835GHz Ceramic SMT antenna, 4x4.25mm keep out area

PART NUMBER: W3008

CHARTS

Free Space Radiation Pattern



(*) All RF parameters measured on 80*37mm PCB with 4*4.25mm clearance in free space. No matching component used.






TECHNICAL DATA SHEET

Description: 2.4-2.4835GHz Ceramic SMT antenna, 4x4.25mm keep out area

PART NUMBER: W3008

CHARTS

Free Space Radiation Pattern



(*) All RF parameters measured on 80*37mm PCB with 4*4.25mm clearance in free space. No matching component used.





TECHNICAL DATA SHEET

Description: 2.4-2.4835GHz Ceramic SMT antenna, 4x4.25mm keep out area

PART NUMBER: W3008

PACKAGING


3000pcs antennas per 7" reel


5pcs 7" reel per inner package box

2pcs inner box per out box

Total 30000pcs antenna per out box

Out box size: 390mmx215mmx165mm





According to MSL3 packing requirement, MBB-Moisture Barrel Bag, Desiccant, HIC-Humidity Indicator Card, MSID Label, Caution Label are required.