



TAI-SAW TECHNOLOGY CO., LTD.

No. 3, Industrial 2nd Rd., Ping-Chen Industrial District,
Taoyuan, 324, Taiwan, R.O.C.

TEL: 886-3-4690038 FAX: 886-3-4697532

E-mail: tstsales@mail.taisaw.com Web: www.taisaw.com

Product Specifications Approval Sheet

Product Description: SAW Filter 1575.42 MHz 2 MHz BW SMD 2.0X1.6 mm

TST Part No.: TA0664B

Customer Part No.: _____

Customer signature required
Company: _____
Division: _____
Approved by : _____
Date: _____

Checked by: _____ Anne Chen *Anne Chen*

Approved by: _____ Andy Yu *Andy Yu*

Date: _____ 2018/12/10

1. Customer signed back is required before TST can proceed with sample build and receive orders.
2. Orders received without customer signed back will be regarded as agreement on the specifications.
3. Any specifications changes must be approved upon by both parties and a new revision of specifications shall be released to reflect the changes.



TAI-SAW TECHNOLOGY CO., LTD.

No. 3, Industrial 2nd Rd., Ping-Chen Industrial District,
Taoyuan, 324, Taiwan, R.O.C.

TEL: 886-3-4690038 FAX: 886-3-4697532

E-mail: tstsales@mail.taisaw.com Web: www.taisaw.com

SAW Filter 1575.42 MHz 2 MHz BW for GPS

MODEL NO.: TA0664B

REV. NO.:3

A. MAXIMUM RATING:

1. Input Power Level: 10 dB_m (1574.42 ~ 1576.42 MHz)
2. DC voltage: 7.5 V
3. Operating Temperature: -40°C to +85°C
4. Storage Temperature: -40°C to +95°C
5. Moisture Sensitivity Level: Level 1 (**MSL 1**)


RoHS Compliant
Lead free
Lead-free soldering

Electrostatic Sensitive Device (**ESD**)

B. ELECTRICAL CHARACTERISTICS:


Item		Min.	Typ.	Max.
Center frequency	Fc (MHz)	-	1575.42	-
Insertion loss (1574.42~1576.42 MHz)	IL (dB)	-	2.8	3.5
Amplitude ripple (1574.42~1576.42 MHz)	(dB)	-	0.5	1.5
Attenuation (Reference level from 0 dB)				
1475.42	MHz (dB)	35	55	-
1505	MHz (dB)	41	47	-
1535.42	MHz (dB)	30	52	-
1559	MHz (at +25°C only) (dB)	28	33	-
1615.42	MHz (dB)	30	35	-
1675.42	MHz (dB)	40	64	-
VSWR (1574.42~1576.42 MHz)		-	1.5	2.5
Source impedance	Zs (Ω)	-	50	-
Load impedance	ZL (Ω)	-	50	-

C. PCB FOOTPRINT:



TST DCC
please document


D. OUTLINE DRAWING:



□ : Year/Month Code (Follow the table)



Year/Month	1	2	3	4	5	6	7	8	9	10	11	12
2018	A	B	C	D	E	F	G	H	J	K	L	M
2019	N	P	Q	R	S	T	U	V	W	X	Y	Z
2020	a	b	c	d	e	f	g	h	j	k	i	m
2021	n	p	q	r	s	t	u	v	w	x	y	z
2022	A	B	C	D	E	F	G	H	J	K	L	M
2023	N	P	Q	R	S	T	U	V	W	X	Y	Z

E. MEASUREMENT CIRCUIT:





F. FREQUENCY CHARACTERISTICS:

Transfer function





Reflections Functions:

S11 VSWR




S22 VSWR




G. PACKING:

1. REEL DIMENSION

(Reel Count : 7"=3000 typ. Or per the request of customer order)



2. TAPE DIMENSION



H. RECOMMENDED REFLOW PROFILE :

1. Preheating shall be fixed at 150~180°C for 60~90 seconds.
2. Ascending time to preheating temperature 150°C shall be 30 seconds min.
3. Heating shall be fixed at 220°C for 50~80 seconds and at 245~260°C peak (min. 10sec).
4. Time : 2 times.

