



# TAI-SAW TECHNOLOGY CO., LTD.

No. 3, Industrial 2nd Rd., Ping-Chen Industrial District,  
Taoyuan, 324, Taiwan, R.O.C.

TEL: 886-3-4690038 FAX: 886-3-4697532

E-mail: [tstsales@mail.taisaw.com](mailto:tstsales@mail.taisaw.com) Web: [www.taisaw.com](http://www.taisaw.com)

## Product Specifications Approval Sheet

Product Name: SAW Filter 2000 MHz SMD 3.0x3.0 mm (BW=40 MHz)

TST Parts No.:TA0751B

Customer Parts No.: \_\_\_\_\_

Customer signature required
Company: _____
Division: _____
Approved by : _____
Date: _____

Checked by: \_\_\_\_\_ Hayley Chou *Hayley Chou*

Approved by: \_\_\_\_\_ Andy Yu *Andy Yu*

Date: \_\_\_\_\_ 2018/05/08

1. Customer signed back is required before TST can proceed with sample build and receive orders.
2. Orders received without customer signed back will be regarded as agreement on the specifications.
3. Any specifications changes must be approved upon by both parties and a new revision of specifications shall be released to reflect the changes



# TAI-SAW TECHNOLOGY CO., LTD.

No. 3, Industrial 2nd Rd., Ping-Chen Industrial District,  
Taoyuan, 324, Taiwan, R.O.C.

TEL: 886-3-4690038 FAX: 886-3-4697532

E-mail: [tstsales@mail.taisaw.com](mailto:tstsales@mail.taisaw.com) Web: [www.taisaw.com](http://www.taisaw.com)

## SAW Filter 2000 MHz

MODEL NO.: TA0751B

REV. 1.0

### A. MAXIMUM RATING:

1. Input Power Level: 10 dBm
2. DC Voltage : 3 V
3. Operating Temperature: -40 °C to +85 °C (1)
4. Storage Temperature: -40 °C to +85 °C
5. Moisture Sensitive Level: Level 1 (MSL1)

RoHS Compliant  
Lead free  
Lead-free soldering

Electrostatic Sensitive Device (ESD)

### B. ELECTRICAL CHARACTERISTICS:

Terminating source impedance:  $Z_s=50 \Omega$

Terminating load impedance:  $Z_L=50 \Omega$


Parameters Description	Unit	Min.	Type.	Max.	
<b>Center Frequency</b>	<b>Fc</b>	MHz	-	2000	-
<b>Max. Insertion Loss</b> (1980~2020 MHz)	<b>IL</b>	dB	-	2.4	4.0
<b>Amplitude Ripple</b> (1980~2020 MHz)		dB <sub>p-p</sub>	-	0.7	2.0
<b>VSWR</b> (1980~2020 MHz)		-	-	1.7	2.5
<b>Attenuation</b> (Reference level from 0 dB)					
DC ~ 500 MHz		dB	20	32	-
500 ~ 1780 MHz		dB	18	28	-
1780 ~ 1920 MHz		dB	22	33	
2100 ~ 2180 MHz		dB	24	36	-
2180 ~ 4000 MHz		dB	22	34	-

**Notes:** (1) In production, devices will be tested at room temperature to a guard banded specification to ensure electrical compliance over temperature.


(2) Typical values are based on average measurements at room temperature.

### C. MEASUREMENT CIRCUIT:


HP Network analyzer




### D. FREQUENCY CHARACTERISTIC:



**E. OUTLINE DRAWING:**



#B: Input  
 #E: Output  
 #A, C, D, F: Ground  
 Unit: mm



△: Year code (2017→7, 2018→8, .....2022→2)

□: Date code (Follow the table from planner each year)


**Date Code Table:**

WK01	WK02	WK03	WK04	WK05	WK06	WK07	WK08	WK09	WK10	WK11	WK12	WK13
A	B	C	D	E	F	G	H	I	J	K	L	M
WK14	WK15	WK16	WK17	WK18	WK19	WK20	WK21	WK22	WK23	WK24	WK25	WK26
N	O	P	Q	R	S	T	U	V	W	X	Y	Z
WK27	WK28	WK29	WK30	WK31	WK32	WK33	WK34	WK35	WK36	WK37	WK38	WK39
a	b	c	d	e	f	g	h	i	j	k	l	m
WK40	WK41	WK42	WK43	WK44	WK45	WK46	WK47	WK48	WK49	WK50	WK51	WK52
n	o	p	q	r	s	t	u	v	w	x	y	z


**F. PACKING:** (Ref: WI-75M03)

1. REEL DIMENSION

(Please refer to FR-75D10 for packing quantity)



2. TAPE DIMENSION



### G. Recommended Reflow Profile:

1. Preheating shall be fixed at  $150\sim 180^{\circ}\text{C}$  for 60~90 seconds.
2. Ascending time to preheating temperature  $150^{\circ}\text{C}$  shall be 30 seconds min.
3. Heating shall be fixed at  $220^{\circ}\text{C}$  for 50~80 seconds and at  $260^{\circ}\text{C}+0/-5^{\circ}\text{C}$  peak (20~40sec).
4. Time: 2 times.

