



SJV 系列  
SERIES

105°C 3000小时品

Load Life : 105°C 3000 hours


RoHS  
compliance

## ◆尺寸图／DIMENSIONS (mm)



φD	L	A1	B1	C	W1	P
4	6.1	4.3	4.3	1.8	0.5~0.8	1.0
5	6.1	5.3	5.3	2.2	0.5~0.8	1.3
6.3	6.1	6.6	6.6	2.7	0.5~0.8	1.8
6.3	8.0	6.6	6.6	2.7	0.5~0.8	1.8

## ◆标识／MARKING

◆纹波电流补正系数／  
MULTIPLIER FOR RIPPLE CURRENT

频率(Hz) Frequency		60(50)	120	500	1k	10k≤
系数 Coefficient	0.47~1μF	0.50	1.00	1.20	1.30	1.50
	2.2~4.7μF	0.65	1.00	1.20	1.30	1.50
	10~47μF	0.80	1.00	1.20	1.30	1.50
	100~220μF	0.80	1.00	1.10	1.15	1.20

## ◆标准品一览表／STANDARD SIZE Size φD×L(mm), Rated Ripple Current (mA r.m.s./105°C, 120Hz)

Vdc	Cap (μF)	Size (φDxL)	Rated Ripple Current
6.3	22	4×6.1	22
	47	5×6.1	38
	100	6.3×6.1	69
	220	6.3×8	120
10	33	5×6.1	35
16	10	4×6.1	18
	22	5×6.1	30
	47	6.3×6.1	50
	100	6.3×8	81

Vdc	Cap (μF)	Size (φDxL)	Rated Ripple Current
25	33	6.3×6.1	50
	47	6.3×8	63
	4.7	4×6.1	16
	10	5×6.1	27
35	22	6.3×6.1	44
	33	6.3×8	57

Vdc	Cap (μF)	Size (φDxL)	Rated Ripple Current
50	0.47	4×6.1	4
	1	4×6.1	8
	2.2	4×6.1	11
	3.3	4×6.1	14
	4.7	5×6.1	19
	10	6.3×6.1	32
	22	6.3×8	58

## ◆产品型号体系／PART NUMBER

□□□	SJV	□□□□□	M	□□□	D×L
额定电压 Rated Voltage	系列名称 Series	静电容量 Capacitance	静电容量允许差 Capacitance Tolerance	副记号 Option	铝壳尺寸 Case Size