

- Very Low Power Consumption . . . 2 mW Typ at V_{DD} = 5 V
- Capable of Operation in Astable Mode
- CMOS Output Capable of Swinging Rail to Rail
- High Output-Current Capability Sink 100 mA Typ Source 10 mA Typ
- Output Fully Compatible With CMOS, TTL, and MOS
- Low Supply Current Reduces Spikes During Output Transitions
- Single-Supply Operation From 2 V to 15 V

	-
descri	ption

The XDXL/556 series are monolithic timing circuitsfabricated using the TI LinCMOS™ process, which provides full compatibility with CMOS, TTL, and MOS logic and operates at frequencies up to 2 MHz. Accurate time delays and oscillations are possible with smaller, Power consumption is low across the full range of power supply voltages. the XDXL/556 has a trigger levelapproximately one-third of the supply voltage and a threshold level approximately two-thirds of the supply voltage. These levels can be altered by use of the controlvoltage terminal. When the trigger input falls below the trigger level, the flip-flop is set and the output goes high. If the trigger input is above the trigger level and the threshold input is above the threshold level, the flip-flop is reset and the output is low. The reset input can override all other inputs and can be used to initiate a new timingcycle. If the reset input is low, the flip-flop is reset and the output is low. Whenever the output is low, a low-impedance path is provided between the discharge terminal and ground. While the CMOS output is capable of sinking over 100 mA and sourcing over 10 mA, the XDXL/556 exhibits greatly reduced supply-current spikes during output transitions. These devices have internal electrostatic-discharge (ESD) protection circuits that prevent catastrophic failures at voltages up to 2000 V as tested under MIL-STD-883C, Method 3015. However, care should be exercised in handling these devices, as exposure to ESD may result in degradation of the device parametric

performance.All unused inputs should be tied to an appropriate logic level to prevent false triggering.The

XDXL/556 is characterized for operation from 0°C to 70°C.

1 DISCH	1	14	V _{DD}
1 THRES	2	13	2 DISCH
1 CONT	3	12	2 THRES
1 RESET	4	11	2 CONT
1 OUT	5	10	2 RESET
1 TRIG	6	9	2 OUT
GND	7	8	2 TRIG
GND	7	8] 2 TRIG


AVAILABLE OPTIONS									
т.	V		PACKAGE						
T _A RANGE	V _{DD} RANGE	SMALL OUTLINE (D)	CHIP CARRIER (FK)	CERAMIC DIP (J)	PLASTIC DIP (N)				
O°C to 70°C	2 V to 18 V	XL556			XD556				

FUNCTION TABLE

RESET VOLTAGE [†]	TRIGGER VOLTAGE [†]	THRESHOLD VOLTAGE [†]	OUTPUT	DISCHARGE SWITCH
< MIN	Irrelevant	Irrelevant	L	On
> MAX	< MIN	Irrelevant	Н	Off
>MAX	>MAX	>MAX	L	On
> MAX	> MAX	< MIN	As previously	/ established


[†] For conditions shown as MIN or MAX, use the appropriate value specified under electrical characteristics.

functional block diagram (each timer)



RESET can override TRIG and THRES. TRIG can override THRES.

Pin numbers shown are for the D, J, or N packages.



FUNCTIONAL BLOCK DIAGRAM (EACH TIMER)

absolute maximum ratings over operating free-air temperature (unless otherwise noted)

Supply voltage, V _{DD} (see Note 1)		18		
Input voltage range, VI	-0.3 to V _{DD}			
Sink current, discharge or output	ıt			
Source current, output	15			
Continuous total power dissipation		See Dissipation Rating Table		
Operating free-air temperature range		0 to 70		
Storage temperature range		-65 to 150		
Case temperature for 60 seconds	FK package			
Lead temperature 1,6 mm (1/16 inch) from case for 60 seconds	J package			
Lead temperature 1,6 mm (1/16 inch) from case for 10 seconds	D or N package	260		

NOTE 1: All voltage values are with respect to network ground terminal.

DISSIPATION RATING TABLE

PACKAGE	T _A ≤ 25°C POWER RATING	DERATING FACTOR ABOVE T _A = 25°C	T _A = 70°C POWER RATING	T _A = 85°C POWER RATING	T _A = 125°C POWER RATING
D	950 mW	7.6 mW/°C	608 mW	494 mW	N/A
FK	1375 mW	11.0 mW/°C	880 mW	715 mW	275 mW
J	1375 mW	11.0 mW/°C	880 mW	715 mW	275 mW
N	1150 mW	9.2 mW/°C	736 mW	598 mW	N/A

recommended operating conditions

				UNIT
Supply voltage, V _{DD}				V
Operating free-air temperature range, TA	XDXL/556	0	70	°C

electrical characteristics at specified free-air temperature, $V_{DD} = 2 V$ for TLC556C, $V_{DD} = 3 V$ for XDXL/556

		TEST	T . †	Х	XDXL/556	
	PARAMETER	CONDITIONS	ΤA [†]	MIN	TYP	MAX
\/. _	Input throughold voltage		25°C	0.95	1.33	1.65
VIT	Input threshold voltage		Full range	0.85		1.75
	Threshold current		25°C		10	
			MAX		75	
Max X	Trigger veltege		25°C	0.4	0.67	0.95
V(trigger)	Trigger voltage		Full range	0.3		1.05
1	Trigger ourrept		25°C		10	
I(trigger)	Trigger current		MAX		75	
Mr. a	Depart valtage		25°C	0.4	1.1	1.5
V(reset)	Reset voltage		Full range	0.3		1.8
14 A	Reset current		25°C		10	
l(reset)	Reset current		MAX		75	
	Control voltage (open circuit) as a percentage of supply voltage		MAX		66.7%	
	Discharge switch on-state volt-		25°C		0.04	0.2
	age	$I_{OL} = 1 \text{ mA}$	Full range			0.25
	Discharge switch off-state cur-		25°C		0.1	
	rent		MAX		0.5	
Maria		Jan 200 A	25°C	1.5	1.9	
VOH	High-level output voltage	I _{OH} = -300 μA	Full range	1.5		
Val		101 - 1 m	25°C		0.07	0.3
VOL	Low-level output voltage	$I_{OL} = 1 \text{ mA}$	Full range			0.35
		See Note 2	25°C		130	500
DD	Supply current	See Note 2	Full range			800

[†] Full range is 0°C to 70°C for XDXL/556

NOTE 2: These values apply for the expected operating configurations in which THRES is connected directly to DISCH or TRIG.

		TEST		XDXL/556			
	PARAMETER	CONDITIONS	τ _A †	MIN	TYP	MAX	UNIT
	Input threshold		25°C	2.8	3.3	3.8	
VIT	voltage		Full range	2.7		3.9	V
	T I		25°C		10		
	Threshold current		MAX		75		рА
N/	Tringeneration		25°C	1.36	1.66	1.96	
V(trigger)	Trigger voltage		Full range	1.26		2.06	V
	Trianant		25°C		10		- 4
l(trigger)	Trigger current		MAX		75		рА
	Deseturber		25°C	0.4	1.1	1.5	
V(reset)	Reset voltage		Full range	0.3		1.8	V
	D		25°C		10		
I(reset)	Reset current		MAX		75		рA
	Control voltage (open circuit) as a percentage of supply voltage		MAX		66.7%		
	Discharge switch	I _{OL} = 10 mA	25°C		0.15	0.5	V
	on-state voltage	IOL = 10 IIIA	Full range			0.6	v
	Discharge switch		25°C		0.1		nA
	off-state current		MAX		0.5		ΠA
Maria	High-level output	1	25°C	4.1	4.8		V
VOH	voltage	IOH = -1 mA	Full range	4.1			V
		1 0-mA	25°C		0.21	0.4	
		I _{OL} = 8 mA	Full range			0.5	
	Low-level output	1-1 E m A	25°C		0.13	0.3	V
VOL	voltage	I _{OL} = 5 mA	Full range			0.4	V
		1	25°C		0.08	0.3	
		I _{OL} = 3.2 mA	Full range			0.35	
	Supply current	See Note 2	25°C		340	700	
DD	Supply current	See Note 2	Full range			1000	μA

electrical characteristics at specified free-air temperature, $V_{\mbox{\scriptsize DD}}$ = 5 V

[†] Full range is 0°C to 70°C for XDXL/556
 NOTE 2: These values apply for the expected operating configurations in which THRES is connected directly to DISCH or to TRIG.

		TEST	_ +	XDXL/556			
	PARAMETER	CONDITIONS	TA	MIN	TYP	МАХ	UNIT
M			25°C	9.45	10	10.55	V
VIT	Input threshold voltage		Full range	9.35		10.65	v
	Threshold surrent		25°C		10		- 4
	Threshold current		MAX		75		рA
V <i>u</i> · · · ·	Trigger voltage		25°C	4.65	5	5.35	V
V(trigger) Trigger voltage		Full range	4.55		5.45	v	
(();)	Trigger current		25°C		10		pА
(trigger)	nigger ourrent		MAX		75		p/\
V _(reset)	Reset voltage		25°C	0.4	1.1	1.5	V
*(reset)	Treser voltage		Full range	0.3		1.8	•
1(Reset current		25°C		10		pА
I(reset)			MAX		75		рл
	Control voltage (open circuit) as a percent- age of supply voltage		MAX		66.7%		
	Discharge switch on-	let = 100 mA	25°C		0.8	1.7	V
	state voltage	I _{OL} = 100 mA	Full range			1.8	v
	Discharge switch off-		25°C		0.1		nA
	state current		MAX		0.5		ΠA
		I _{OH} = -10 mA	25°C	12.5	14.2		
		OH = -10 MA	Full range	12.5			
VOH	High-level output	I _{OH} = -5 mA	25°C	13.5	14.6		V
VОН	voltage	10H = 3111/1	Full range	13.5			v
		IOH = -1 mA	25°C	14.2	14.9		
			Full range	14.2			
		I _{OL} = 100 mA	25°C		1.28	3.2	
			Full range			3.6	
VOL	Low-level output	I _{OL} = 50 mA	25°C		0.63	1	V
•OL	voltage		Full range			1.3	v
		I _{OL} = 10 mA	25°C		0.12	0.3	
			Full range			0.4	
DD	Supply current	See Note 2	25°C		0.72	1.2	mA
עטי		Jee Note 2	Full range			1.6	1174

electrical characteristics at specified free-air temperature, $V_{DD} = 15 V$

[†] Full range is 0°C to 70°C for XDXL/556.

NOTE 2: These values apply for the expected operating configurations in which THRES is connected directly to DISCH or TRIG.

electrical characteristics, V_{DD} = 5 V, T_A = 25°C

	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
VIT	Input threshold voltage		2.8	3.3	3.8	V
	Threshold current			10		pА
V _(trigger)	Trigger voltage		1.36	1.66	1.96	V
I(trigger)	Trigger current			10		pА
V _(reset)	Reset voltage		0.4	1.1	1.5	V
I(reset)	Reset current			10		pА
	Discharge switch on-state voltage	I _{OL} = 10 mA		0.15	0.5	V
	Discharge switch off-state current			0.1		nA
VOH	High-level output voltage	I _{OH} = -1 mA	4.1	4.8		V
		I _{OL} = 8 mA		0.21	0.4	
VOL	Low-level output voltage	$I_{OL} = 5 \text{ mA}$		0.13	0.3	V
		I _{OL} = 2.1 mA		0.08	0.3	
IDD	Supply current	See Note 2		3.40	700	μA

NOTE 2: These values apply for the expected operating configurations in which THRES is connected directly to DISCH or TRIG.

operating characteristics, V_{DD} = 5 V, T_A = 25°C (unless otherwise noted)

	PARAMETER	TEST CONDITIONS			TYP	MAX	UNIT
	Initial error of timing interval [†]	$V_{DD} = 5 V \text{ to } 15 V,$	$R_A = R_B = 1 \text{ k}\Omega$ to 100 k Ω		1%	3%	
	Supply voltage sensitivity of timing interval	C _T = 0.1 μF,	See Note 3		0.1	0.5	%/V
tr	Output pulse rise time	D. 10 MO	0. 40 = 5		20	75	
t _f	Output pulse fall time	R _L = 10 MΩ,	C _L = 10 pF		15	60	ns
f _{max}	Maximum frequency in astable mode	R _A = 470 Ω, C _T = 200 pF,	R _B = 200 Ω, See Note 3	1.2	2.1		MHz

[†] Timing interval error is defined as the difference between the measured value and the average value of a random sample from each process run.

NOTE 3: R_A , R_B , and C_T are as defined in Figure 3.

TYPICAL CHARACTERISTICS





Figure 1





[‡] The effects of the load resistance on these values must be taken into account separately.

Figure 2

APPLICATION INFORMATION




Figure 3. Astable Operation

Connecting the trigger input to the threshold input, as shown in Figure 3, causes the timer to run as a multivibrator. The capacitor C_T charges through R_A and R_B to the threshold voltage level (approximately 0.67 V_{DD}) and then discharges through R_B only to the value of the trigger voltage level (approximately 0.33 V_{DD}). The output is high during the charging cycle (t_H) and low during the discharge cycle (t_L). The duty cycle is controlled by the values of R_A , and R_B , and C_T , as shown in the equations below.

$$t_{H} \approx C_{T} (R_{A} + R_{B}) \text{ In } 2 \quad (\text{In } 2 = 0.693)$$

$$t_{L} \approx C_{T} R_{B} \text{ In } 2$$
Period = $t_{H} + t_{L} \approx C_{T} (R_{A} + 2R_{B}) \text{ In } 2$
Output driver duty cycle = $\frac{t_{L}}{t_{H} + t_{L}} \approx 1 - \frac{R_{B}}{R_{A} + 2R_{B}}$
Output waveform duty cycle = $\frac{t_{H}}{t_{H} + t_{L}} \approx \frac{R_{B}}{R_{A} + 2R_{B}}$

The 0.1-µF capacitor at CONT in Figure 3 decreases the period by about 10%.

The formulas shown above do not allow for any propagation delay from the trigger and threshold inputs to the discharge output. These delay times add directly to the period and create differences between calculated and actual values that increase with frequency. In addition, the discharge output resistance r_{on} adds to R_B to provide another source of error in the calculation when R_B is very low or r_{on} is very high.

The equations below provide better agreement with measured values.

$$t_{H} = C_{T} (R_{A} + R_{B}) In \left[3 - \exp\left(\frac{-t_{PLH}}{C_{T} (R_{B} + r_{on})}\right) \right] + t_{PHL}$$
$$t_{L} = C_{T} (R_{B} + r_{on}) In \left[3 - \exp\left(\frac{-t_{PHL}}{C_{T} (R_{A} + R_{B})}\right) \right] + t_{PLH}$$

APPLICATION INFORMATION

The preceding equations and those given earlier are similar in that a time constant is multiplied by the logarithm of a number or function. The limit values of the logarithmic terms must be between In 2 at low frequencies and In 3 at extremely high frequencies. For a duty cycle close to 50%, an appropriate constant for the logarithmic

terms can be substituted with good results. Duty cycles less than 50% $\frac{t_H}{t_H + t_L}$ will require that $\frac{t_H}{t_L} < 1$ and


possibly $R_A \leq r_{on}$. These conditions can be difficult to obtain.

In monostable applications, the trip point of the trigger input can be set by a voltage applied to CONT. An input voltage between 10% and 80% of the supply voltage from a resistor divider with at least 500- μ A bias provides good results.

XL556 SOP-14 XD556 DIP-14

D (R-PDSO-G14)

PLASTIC SMALL OUTLINE



NOTES: A. All linear dimensions are in inches (millimeters).

- B. This drawing is subject to change without notice.
- Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0,15) each side.


Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0,43) each side.

E. Reference JEDEC MS-012 variation AB.

XL556 SOP-14 XD556 DIP-14

N (R-PDIP-T**)

PLASTIC DUAL-IN-LINE PACKAGE



- NOTES: A. All linear dimensions are in inches (millimeters).
 - B. This drawing is subject to change without notice.
 - 🖄 Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
 - The 20 pin end lead shoulder width is a vendor option, either half or full width.

以上信息仅供参考.如需帮助联系客服人员。谢谢 XINLUDA