



Features

- 2 pads surface mount package;
- Applications in mobile phone, Notebook and DSC;
- High reliable environmental performance;
- RoHS Compliant / Pb Free.

Crystals specifications

ITEMS (项目)	PARAMETER (规格说明) S21
Norminal Frequency	32.768 KHz
Load Capacitance( CL)	12.5 pF , other spec.
Series Resistance	90KΩ
Frequency Tolerance(at 25 °C)	± 20 ppm , or specify
Frequency-Temperature coefficient	-0.04ppm/°C2
Operation Temperature Range	- 40 ~ + 85 °C
Storage Temperature Range	- 55 ~ +125 °C
Shunt Capacitance (C0)	1.3pF typical
Motional Capacitance (C1)	6.4fF typical
Drive Level (DL)	0.5 μW Max.
Insulation Resistance (IR)	500 MΩ Min.
Aging (at 25 °C)	± 3 ppm at first year
Packing Unit(包装单位)	3,000pcs/Reel

Dimensions

