Surface Mount



- High reliability and high voltage are realized by hybrid electrolyte
- Endurance with ripple current: 4,000 hours at 125°C
- For high temperature and high reliability applications. (Automotive equipment, Base station equipment, etc.)
- RoHS2 Compliant
- Halogen Free

NIPPON CHEMI-CON

• AEC-Q200 compliant : Please contact Chemi-Con for more details, test data, information.

HXA Higher temperature HXB




SPECIFICATIONS

| Items | Characteristics | | | | | | |
|--|---|---------------------------------------|--|------------------|--|--|--|
| Category Temperature Range | -55 to +125℃ | | | | | | |
| Rated Voltage Range | 80V _{dc} | | | | | | |
| Capacitance Tolerance | ±20% (M) | | | (at 20°C, 120Hz) | | | |
| Leakage Current | I=0.01CV or 3μ A, whichever is greater Where, I: Max. leakage current (μ A), C: Nominal capacitance(μ F), V: Rated voltage(V) (at 20°C after 2 minutes) | | | | | | |
| Dissipation Factor | Rated voltage(V _{dc}) | 80V | | | | | |
| (tan δ) | $tan \delta$ (Max.) | 0.08 | | (at 20°C, 120Hz) | | | |
| Low Temperature Characteristics (Max. Impedance Ratio) | $Z(-25^{\circ}C)/Z(+20^{\circ}C)$ ≤1.5 $Z(-55^{\circ}C)/Z(+20^{\circ}C)$ ≤2.0 | | | (at 100kHz) | | | |
| Endurance | The following specifications shall be satisfied when the capacitors are restored to 20°C after subjected to DC voltage with the rated ripple current is applied (the peak voltage shall not exceed the rated voltage) for 4,000 hours at 125°C. | | | | | | |
| | Capacitance change | ≤±30% of the initial value | | | | | |
| | D.F. (tan δ) | ≤ 200% of the initial specified value | | | | | |
| | ESR | ≤ 200% of the initial specified value | | | | | |
| | Leakage current | ≤ The initial specified value | | | | | |
| Shelf Life | The following specifications shall be satisfied when the capacitors are restored to 20℃ after exposing them for 1,000 hours at 125℃ without voltage applied. Before the measurement, the capacitor shall be preconditioned by applying voltage according to item 4.1 of JIS C 5101-4. | | | | | | |
| | Capacitance change | ≦±30% of the initial value | | | | | |
| | D.F. (tan δ) | ≤ 200% of the initial specified value | | | | | |
| | ESR | ≤ 200% of the initial specified value | | | | | |
| | Leakage current | ≦ The initial specified value | | | | | |

◆DIMENSIONS [mm]


• Terminal Code : A

Size code: HA0 and JA0



• Terminal Code: G(Vibration resistant structure)


Size code : HA0 and JA0



| Size Code | φD | L | A | В | С | W | P |
|-----------|----|------|------|------|------|------------|-----|
| HA0 | 8 | 10.0 | 8.3 | 8.3 | 9.0 | 0.7 to 1.1 | 3.1 |
| JA0 | 10 | 10.0 | 10.3 | 10.3 | 11.0 | 0.7 to 1.1 | 4.5 |
| | | | | | | | |

: Dummy terminals

◆PART NUMBERING SYSTEM



Please refer to "Product code guide (conductive polymer hybrid type)"

◆MARKING



■Rated voltage symbol

| Rated voltage (Vdc) | Symbol | | | |
|---------------------|--------|--|--|--|
| 80 | K | | | |





STANDARD RATINGS

| | WV (V _{dc}) | Cap (µF) | Size code | ESR (mΩmax./20°C, 100kHz) | Rated ripple current (mArms/125°C, 100kHz) | Part No. | |
|-----|--------------------------|-------------|-----------|------------------------------|---|--------------------|--|
| ſ | | 22 | HA0 | 45 | 1,100 | HHXA800□RA220MHA0G | |
| - 1 | 80 | 39 | JA0 | 35 | 1,200 | HHXA800□RA390MJA0G | |
| L | | 47 | JA0 | 33 | 1,700 | HHXA800□RA470MJA0G | |

[:] Enter the appropriate terminal code.

♦RATED RIPPLE CURRENT MULTIPLIERS

Frequency Multipliers

| Capacitance(µF) Frequency(Hz) | 120 | 1k | 5k | 10k | 20k | 30k | 100k to 500k |
|-------------------------------|------|------|------|------|------|------|--------------|
| 22 | 0.07 | 0.30 | 0.50 | 0.60 | 0.70 | 0.75 | 1.00 |
| 39 to 47 | 0.10 | 0.40 | 0.60 | 0.70 | 0.80 | 0.80 | 1.00 |