

SL22-B THRU SL220-B

2.0A Low VF Surface Mount Schottky Barrier Rectifiers -20V-200V


Features

- ▶ The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- ▶ For surface mounted applications
- ▶ Metal silicon junction, majority carrier conduction
- ▶ Low power loss, high efficiency
- ▶ Built-in strain relief, ideal for automated placement
- ▶ High forward surge current capability
- ▶ High temperature soldering guaranteed: 250°C/10 seconds at terminals
- ▶ Compliant to RoHS Directive 2011/65/EU
- ▶ Suffix "-H" indicates Halogen-free part, ex. SL24-B-H

Mechanical data

- ▶ **Case:** JEDEC DO-214AA molded plastic body
- ▶ **Terminals:** Solder plated, solderable per MIL-STD-750, Method 2026
- ▶ **Polarity:** Color band denotes cathode end
- ▶ **Mounting Position:** Any
- ▶ **Weight:** 0.003 ounce, 0.093 grams

Package outline



Maximum ratings and Electrical Characteristics (AT T_A=25°C unless otherwise noted)

PARAMETER	CONDITIONS	Symbol	MIN.	TYP.	MAX.	UNIT
Forward rectified current	See Fig.2	I _O			2.0	A
Forward surge current	8.3ms single half sine-wave (JEDEC methode)	I _{FSM}			50	A
Reverse current	V _R = V _{RRM} T _A = 25°C	I _R			1.0	mA
	V _R = V _{RRM} T _A = 100°C				20	
Thermal resistance	Junction to ambient NOTE 1	R _{θJA}		75		°C/W
Diode junction capacitance	f=1MHz and applied 4V DC reverse voltage	C _J		220		pF
Storage temperature		T _{STG}	-65		+150	°C







Note: 1.P.C.B. mounted with 0.2x0.2" (5.0x5.0mm) copper pad areas

SYMBOLS	V _{RRM} ^{*1} (V)	V _{RMS} ^{*2} (V)	V _R ^{*3} (V)	V _F ^{*4} (V)	Operating temperature T _J , (°C)
SL22-B	20	14	20	0.45	-55 to +125
SL23-B	30	21	30		
SL24-B	40	28	40		
SL25-B	50	35	50	0.55	-55 to +150
SL26-B	60	42	60		
SL28-B	80	56	80	0.75	
SL210-B	100	70	100		
SL215-B	150	105	150	0.85	
SL220-B	200	140	200		

- *1 Repetitive peak reverse voltage
- *2 RMS voltage
- *3 Continuous reverse voltage
- *4 Maximum forward voltage@I_F=2.0A

SL22-B THRU SL220-B

Rating and characteristic curves



SL22-B THRU SL220-B


Pinning information

Pin	Simplified outline	Symbol
Pin1 cathode Pin2 anode		

Marking

Type number	Marking code	Example	
SL22-B	SL22	For Halogen Device	For Halogen-free Device
SL23-B	SL23		
SL24-B	SL24		
SL25-B	SL25		
SL26-B	SL26		
SL28-B	SL28		
SL210-B	SL210		
SL215-B	SL215		
SL220-B	SL220		

Suggested solder pad layout



Dimensions in inches and (millimeters)

PACKAGE	A	B	C
SMB	0.078 (2.00)	0.059 (1.50)	0.110 (2.80)