

ES1A THRU ES1J


1.0AMP SURFACE MOUNT GLASS SUPERFAST RECOVERY RECTIFIER


Features

- Low Power Loss, High Efficiency
- Ideally Suited for Automatic Assembly
- Guard Ring Die Construction
- Plastic Case Material has UL Flammability Classification Rating 94V - 0

Mechanical Data

- · Case: Molded plastic SMA
- Terminals: Plated leads solderable per MIL-STD-750, Method 2026 guaranteed
- · Polarity: Color band dentes cathode end
- Mounting Position: Any
- · Making: Type Number





Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified

Single phase, half wave, 60Hz, resistive or inductive load

For capacitive load derate current by 20%

Type Number	SYMBOL	ES1A	ES1B	ES1D	ES1G	ES1J	Unit
Maximum Recurrent Peak Reverse Voltage	VRRM	50	100	200	400	600	V
Maximum RMS Voltage	VRMS	35	70	140	280	420	V
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	V
Average Rectified Output Current @T _L =100 °C	IF(AV)			1.0			А
Peak Forward Surge Current 8.3ms Single half sine-wave superimposed on rated load (JEDEC Method)	İfsm	35					А
Rating for fusing (t<8.3ms)	l ² t	5.08					A ² s
Forward Voltage @IF=1.0A	V _{FM}		0.95		1.3	1.7	V
Peak Reverse Current @T _A =25 °C	I _R 5.0 200						uA
At Rated DC Blocking Voltage @T _A =125 ℃							
Maximum Reverse Recovery Time (Note1)	Trr	35					ns
Typical Junction Capacitance (Note 2)	CJ	20 7				pF	
Typical Thermal Resistance Junction to Ambient(Note 3)	Re JA	34					°C/W
Operating Temperature Range	TJ	-55 to+150					$^{\circ}\!\mathbb{C}$
Storage Temperature Range	Тѕтс	-55 to +150					$^{\circ}\mathbb{C}$

Note: 1.Reverse Recovery Test Conditions:IF=0.5A,IR=1.0A,IRR=0.25A.

- 2. Measured at 1.0 MHz and Applied reverse Voltage of 4.0V D.C
- 3. Device mounted on FR-4 substrate, 1"*1", 2oz, single-sided, PC boards with 0.1"*0.15" copper pad.



ES1A THRU ES1J

INSTANTANEOUS FORWARD CURRENT, (A)

AVERAGE FORWARD RECIFIED CURRENT(A)

I_{FSM}, PEAK FORWARD SURGE CURRENT (A)

INVSTANTANEOUS REVERSE CURRENT, MICROAMPERES

FIG.1MAXIMUM AVERAGE FORWARD CURRENT DERATING




FIG.3MAXIMUM NON-REPEITIVE SURGE CURRENT





FIG.5TYPICAL REVERSE CHRACTERISTICS



PERCENT OF RATED PEAK INVERSE VOLTGE

FIG.2TYPICAL FORWARD CHARACTERISTICS






FIG.4TYPICAL JUNCTION CAPACITANCE



SMA PAD LAYOUT





ES1A THRU ES1J

Important Notice and Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from XINNUO
- XINNUOreserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.
- XINNUOdisclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- XINNUO does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the here in document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications.
 - XINNUO makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown here in are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own ris k andagree to fully indemnifyXINNUOfor any damages resulting from such improper use or sale.
- Since XINNUO uses lot number as the tracking base, please provide the lot number for tracking when complaining.

version:04 3 of 3 www.dyelec.com