

# **DATA SHEET**

**HIGH VOLTAGE CHIP RESISTORS** 

RV series 0.5%, 1%, 5%

sizes 0603/0805/1206/2010/2512

**RoHS** compliant

IEC 62368-1 Safety Certificate issued by UL Demko: sizes 0603/0805/1206



YAGEO Phícomp



# 9

#### SCOPE

This specification describes RV0603/0805/1206/2010/2512 high voltage chip resistors with lead-free terminations made by thick film process.

#### <u>APPLICATIONS</u>

- Converter
- Printer equipment
- Battery charger
- Computer
- Power supply
- Car electronics

# **FEATURES**

- AEC-Q200 qualified for 47ohm
   ≤ R< 5Mohm</li>
- RoHS compliant
- Reducing environmentally hazardous wastes
- High component and equipment reliability
- Non-forbidden materials used in products/production
- Halogen Free Epoxy
- Moisture sensitivity level: MSL I
- IEC 62368-1:2014 safety certificate (G.10.2) issued by UL Demko for the following sizes and resistance ranges:

- 0603:  $100 K\Omega$  to  $10 M\Omega$  - 0805:  $100 K\Omega$  to  $22 M\Omega$ 

1206: 100K $\Omega$  to 27M $\Omega$ 

\*Please refer to UL certification

#### ORDERING INFORMATION - GLOBAL PART NUMBER & 12NC

Both part numbers are identified by the series, size, tolerance, packing type, temperature coefficient, taping reel and resistance value.

#### YAGEO BRAND ordering code

#### **GLOBAL PART NUMBER (PREFERRED)**

#### RV XXXX X X X XX XXXX L

(1) (2) (3) (4) (5) (6) (7

#### (I) SIZE

0603/0805/1206/2010/2512

#### (2) TOLERANCE

 $D = \pm 0.5\%$ 

 $F = \pm 1\%$ 

 $J = \pm 5\%$ 

# (3) PACKAGING TYPE

R = Paper/PE taping reel

K = Embossed taping reel

#### (4) TEMPERATURE COEFFICIENT OF RESISTANCE

- = Base on spec

#### (5) TAPING REEL

07= 7 inch dia, Reel

### (6) RESISTANCE VALUE

There are  $2\sim4$  digits indicated the resistor value. Letter R/K/M is decimal point, no need to mention the last zero after R/K/M, e.g. I K2, not I K20.

Detailed resistance rules show in table of "Resistance rule of global part number".

#### (7) DEFAULT CODE

Letter L is system default code for ordering only (Note)

# Resistance rule of global part number

Resistance code ru	le Example
XXKX	ΙΟΚ = ΙΟ,000 Ω
(10 to 97.6 KΩ)	97K6 = 97,600 Ω
XXXK	$100K = 100,000\Omega$
(100 to 976 K <b>Ω)</b>	$976K = 976,000\Omega$
XMXX	$IM = 1,000,000 \Omega$
(1 to 9.76 M $\Omega$ )	$9M76 = 9,760,000 \Omega$
XXMX	$10M = 10,000,000 \Omega$
(10 to 16 M $\Omega$ )	$27M = 27,000,000 \Omega$

#### **ORDERING EXAMPLE**

The ordering code of a RV1206 chip resistor, value I  $M\Omega$  with  $\pm 5\%$  tolerance, supplied in 7-inch tape reel is: RV1206JR-071ML.

#### NOTE

- All our R-Chip products meet RoHS compliant. "LFP" of the internal 2D reel label mentions "Lead Free Process"
- On customized label, "LFP" or specific symbol printed and the optional "L" at the end of GLOBAL PART NUMBER / 12NC can be added (both are on customer request)



3

9

XXX XXXXX L

# **PHYCOMP BRAND ordering codes**

Both GLOBAL PART NUMBER (preferred) and 12NC (traditional) codes are acceptable to order Phycomp brand products.

# **GLOBAL PART NUMBER (PREFERRED)**

For detailed information of GLOBAL PART NUMBER and ordering example, please refer to page 2.

#### 12NC CODE

2322

	(1)			(2) (3) (4)		
SIZE TYPE START TOL. RESISTANCE IN (1) (%) RANGE		EMBOSSED (2) TAPE ON REEL	PAPER/PE (2) TAPE ON REEL (units)			
		NAINGE	4,000	5,000		
0805	VRCII	2322	±5%	47 to 10M $\Omega$	-	792 61xxx
	VRC12	2322	±1%	47 to 10M $\Omega$	-	793 6xxxx
1206	VRC01	2322	±5%	47 to 27M $\Omega$	-	790 61xxx
	VRC02	2322	±1%	47 to 10M $\Omega$	-	791 6xxxx
2512	VPRC221	2322	±5%	47 to 16M $\Omega$	762 98xxx	-

- (1) The resistors have a 12-digit ordering code starting with 2322.
- (2) The subsequent 4 or 5 digits indicate the resistor tolerance and packaging.
- (3) The remaining 4 or 3 digits represent the resistance value with the last digit indicating the multiplier as shown in the table of "Last digit of I2NC".
- (4) "L" is optional symbol (Note).

#### **ORDERING EXAMPLE**

The ordering code of a VRC01 resistor, value I M $\Omega$  with ±5% tolerance, supplied in tape of 5,000 units per reel is: 232279061105L or RVI206JR-07IML.

Last dia		L a Pris	
Resistance	Last digit		
0.01 to 0.0	976 Ω		0
0.1 to 0.97	<b>'6</b> Ω		7
I to 9.76	Ω		8
10 to 97.6	Ω		9
100 to 976	Ω		1
I to 9.76 k	〈Ω		2
10 to 97.6	ΚΩ		3
100 to 976	S ΚΩ		4
I to 9.76 N	<b>Δ</b> Μ		5
10 to 97.6		6	
Example:	0.02 Ω	=	0200 or 200
	0.3 Ω	=	3007 or 307
	ΙΩ	=	1008 or 108

xample:	0.02 Ω	=	0200 or 200
	0.3 Ω	=	3007 or 307
	ΙΩ	=	1008 or 108
	33 KΩ	=	3303 or 333
	Ι0 ΜΩ	=	1006 or 106

#### **NOTE**

- I. All our R-Chip products are RoHS compliant. "LFP" of the internal 2D reel label mentions "Lead Free Process"
- 2. On customized label, "LFP" or specific symbol printed and the optional "L" at the end of GLOBAL PART NUMBER / I2NC can be added (both are on customer request)



#### MARKING

#### RV0603/0805/1206/2010/2512



E-24 series: 3 digits, ±5%

First two digits for significant figure and 3rd digit for number of zeros

#### **RV0603**



E-24 series: 3 digits, ±0.5% & ±1%

Exception values 10/11/13/15/20/75 of E24 series

One short bar under marking letter



E-96 series: 3 digits, ±0.5% & ±1%

Including values 10/11/13/15/20/75 of E24 series

First two digits for E-96 marking rule and 3rd letter for number of zeros

#### RV0805/1206/2010/2512



Both E-24 and E-96 series: 4 digits, ±0.5% & ±1%

First three digits for significant figure and 4th digit for number of zeros

For further marking information, please refer to data sheet "Chip resistors marking".

# <u>CONSTRUCTION</u>


The resistor is constructed on top of a high-grade ceramic body. Internal metal electrodes are added on each end to make the contacts to the thick film resistive element. The composition of the resistive element is a noble metal imbedded into a glass and covered by a second glass to prevent environment influences. The resistor is laser trimmed to the rated resistance value. The resistor is covered with a protective epoxy coat, finally the two external terminations (matte tin on Nibarrier) are added. See fig.5

#### **DIMENSIONS**

**Table I** For outlines see fig. 5

TYPE	L (mm)	W (mm)	H (mm)	I <sub>I</sub> (mm)	I <sub>2</sub> (mm)
RV0603	1.60 ±0.10	0.80 ±0.10	0.45 ±0.10	0.25 ±0.15	0.25 ±0.15
RV0805	2.00 ±0.10	1.25 ±0.10	0.50 ±0.10	0.35 ±0.20	0.35 ±0.20
RV1206	3.10 ±0.10	1.60 ±0.10	0.55 ±0.10	0.40 ±0.20	0.45 ±0.20
RV2010	5.00±0.10	2.50±0.15	0.55±0.10	0.45±0.15	0.50±0.20
RV2512	6.35 ±0.10	3.10 ±0.15	0.55 ±0.10	0.60 ±0.20	0.50 ±0.20

#### **OUTLINES**



#### **ELECTRICAL CHARACTERISTICS**

Table 2

				CHARA	CTERISTICS		
TYPE	RESISTANCE RANGE	Rated Power	Operating Temperature Range	Max. Working Voltage	Max. Overload Voltage	Dielectric Withstanding Voltage	Temperature Coefficient of Resistance
RV0603	$5\%$ (E-24) $47\Omega$ to $10M\Omega$ 1% (E-24/E-96) $47\Omega$ to $10M\Omega$ 0.5% (E-24/E-96) $47\Omega$ to $10M\Omega$	1/10W	_	350V	500V	500V	
RV0805	$5\%$ (E-24) $47\Omega$ to $22M\Omega$ 1% (E-24/E-96) $47\Omega$ to $22M\Omega$ 0.5% (E-24/E-96) $47\Omega$ to $10M\Omega$	1/8 W	_	400 V	800 V	800 V	
RV1206	$5\%$ (E-24) $47\Omega$ to $27M\Omega$ 1% (E-24/E-96) $47\Omega$ to $27M\Omega$ 0.5% (E-24/E-96) $47\Omega$ to $15M\Omega$	1/4 W	–55 °C to +155 °C	500 V	1,000 V	1,000 ∨	±200 ppm/°C
RV2010	5% (E-24) 47 $\Omega$ to 22M $\Omega$ 1% (E-24/E-96) 47 $\Omega$ to 22M $\Omega$ 0.5% (E-24/E-96) 47 $\Omega$ to 10M $\Omega$	3/4W		500 V	1,000 V	1,000 ∨	
RV2512	$5\%$ (E-24) $47\Omega$ to $16$ M $\Omega$ 1% (E-24/E-96) $47\Omega$ to $16$ M $\Omega$ 0.5% (E-24/E-96) $47\Omega$ to $10$ M $\Omega$	IW		500 V	1,000 V	1,000 ∨	

# FOOTPRINT AND SOLDERING PROFILES

For recommended footprint and soldering profiles, please refer to data sheet "Chip resistors mounting".

# PACKING STYLE AND PACKAGING QUANTITY

Table 3 Packing style and packaging quantity

PACKING STYLE	reel Dimension	RV0603	RV0805	RV1206	RV2010	RV2512
Paper/PE taping reel (R)	7" (178 mm)	5,000	5,000	5,000		
Embossed taping reel (K)	7" (178 mm)				4,000	4,000

#### NOTE

1. For Paper/PE/Embossed tape and reel specification/dimensions, please refer to data sheet "Chip resistors packing".

9

# **FUNCTIONAL DESCRIPTION**

#### **OPERATING TEMPERATURE RANGE**

Range: -55 °C to +155 °C

#### **POWER RATING**

Each type rated power at 70 °C:

RV0603=1/10W; RV0805=1/8W; RV1206=1/4W;

RV2010=3/4W; RV2512=1W

#### **RATED VOLTAGE**

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$V = \sqrt{(P \times R)}$$


or max. working voltage whichever is less

V = Continuous rated DC or AC (rms) working voltage (V)

P = Rated power (W)

 $R = Resistance value (\Omega)$ 

Maximum working voltage can be applicable to resistors only if the resistance value is equal to or higher than the critical resistance value.



# TESTS AND REQUIREMENTS

**Table 4** Test condition, procedure and requirements (AEC-Q200 report available for 47ohm  $\leq$  R < 5Mohm)

TEST METHOD	PROCEDURE	REQUIREMENTS
MIL-STD-202G-method 108A IEC 60115-1 4.25.1 JIS C 5202-7.10	I,000 hours at 70±5 °C applied RCWV I.5 hours on, 0.5 hour off, still air required	±(2%+0.05 Ω)
MIL-STD-202G-method 108A IEC 60115-1 4.25.3 JIS C 5202-7.11	1,000 hours at maximum operating temperature depending on specification, unpowered No direct impingement of forced air to the parts Tolerances: 155±3 °C	±(1%+0.05 Ω)
MIL-STD-202G-method 106F IEC 60115-1 4.24.2	Each temperature / humidity cycle is defined at 8 hours (method 106F), 3 cycles / 24 hours for 10d with 25 °C / 65 °C 95% R.H, without steps 7a & 7b, unpowered  Parts mounted on test-boards, without condensation on parts  Measurement at 24±2 hours after test conclusion	±(2%+0.05 Ω)
MIL-STD-202G-method I07G	-55/+125 °C  Note: Number of cycles required is 300.  Maximum transfer time is 20 seconds. Dwell time is 15 minutes. Air — Air	$\pm$ (0.5%+0.05 $\Omega$ ) for 10 K $\Omega$ to 10 M $\Omega$ $\pm$ (1%+0.05 $\Omega$ ) for others
MIL-R-55342D-para 4.7.5 IEC60115-1 4.13	2.5 times RCWV or maximum overload voltage whichever is less for 5 sec at room temperature	$\pm (2\% + 0.05~\Omega)$ No visible damage
IEC60115-1 4.33	Device mounted on PCB test board as described, only I board bending required Bending for 0603 & 0805: 3mm I 206 & above: 2mm Holding time: minimum 60 seconds Ohmic value checked during bending	±(1%+0.05 Ω) No visible damage
IEC 60115-1 4.24.8	Steady state for 1,000 hours at 40°C / 95% R.H. RCWV applied for 1.5 hours on and 0.5 hour off	±(3.0%+0.05 Ω)
AEC-Q200 Test 7 MIL-STD-202 Method 103	for 47ohm ≤ R< 5Mohm, I,000 hours; 85°C / 85% RH 10% of operating power Measurement at 24 ±4 hours after test conclusion	± (5.0%+0.05 Ω)
	MIL-STD-202G-method 108A IEC 60115-1 4.25.1 JIS C 5202-7.10  MIL-STD-202G-method 108A IEC 60115-1 4.25.3 JIS C 5202-7.11  MIL-STD-202G-method 106F IEC 60115-1 4.24.2  MIL-STD-202G-method 107G  MIL-STD-202G-method 107G  IEC 60115-1 4.13  IEC 60115-1 4.13	MIL-STD-202G-method 108A IEC 60115-1 4.25.1 JIS C 5202-7.10  MIL-STD-202G-method 108A IEC 60115-1 4.25.3 JIS C 5202-7.11  MIL-STD-202G-method 106F IEC 60115-1 4.24.2  MIL-STD-202G-method 107G  MIL-STD-202G-method 108A  MIL-STD-

Chip Resistor Surface Mount RV SERIES 0603/0805/1206/2010/2512 (RoHS Compliant)

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Solderability			
- Wetting	IPC/JEDECJ-STD-002B test B	Electrical Test not required	Well tinned (≥95% covered)
	IEC 60068-2-58	Magnification 50X	No visible damage
		SMD conditions:	
		I <sup>st</sup> step: method B, aging 4 hours at 155 °C dry heat	
		2 <sup>nd</sup> step: leadfree solder bath at 245±3 °C	
		Dipping time: 3±0.5 seconds	
- Leaching	IPC/JEDECJ-STD-002B test D	Leadfree solder, 260 °C, 30 seconds	No visible damage
	IEC 60068-2-58	immersion time	
- Resistance to	MIL-STD-202G-method 210F	Condition B, no pre-heat of samples	±(1%+0.05 Ω)
Soldering Heat	IEC 60068-2-58	Leadfree solder, 260 °C, 10 seconds immersion time	No visible damage
		Procedure 2 for SMD: devices fluxed and cleaned with isopropanol	

# REVISION HISTORY

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 8	Nov .09, 2018	-	- Add AEC-Q200 for 47ohm ≤ R < 5Mohm
Version 7	Jul. 06, 2017	-	- Add IEC62368-1 safety certificate declaration for sizes 0603/0805/1206
Version 6	Dec. 01, 2016	-	- Extend resistor value of RV1206 0.5%
Version 5	Aug. 27, 2015	-	- Extend resistor range and add 0.5%
Version 4	Jan. 27, 2014	-	- RV0603 resistance range extend to $10M\Omega$
			- Add RV2010
Version 3	Aug. 26, 2013	-	- Add RV0603
Version 2	Sep 29, 2011	-	- Type error correction
Version I	Nov 19, 2008	-	- Change to dual brand datasheet that describes RV0805/1206/2512 with RoHS compliant
			- Description of "Halogen Free Epoxy" added
			- Define global part number
Version 0	Feb 14, 2006	-	- New datasheet for high voltage chip resistors sizes of 0805/1206/2512, 5%, 1% tolerance with lead-free terminations
			- Replace the 0805/1206/2512 parts of pdf files: VRC01_02_11_12_51_3.pdf, VPRC221_5_3.pdf, and combine into a document.
			- Test method and procedure updated
			- PE tape added (paper tape will be replaced by PE tape)

<sup>&</sup>quot;Yageo reserves all the rights for revising the content of this datasheet without further notification, as long as the products itself are unchanged. Any product change will be announced by PCN."