







SICR20650WT 650V SIC POWER SCHOTTKY RECTIFIER



Description

SICR20650WT is single SiC Schottky rectifiers packaged in TO-247AD case. The device is a high voltage Schottky rectifier pair that has very low total conduction losses and very stable switching characteristics over temperature extremes. The SICR20650WT are ideal for energy sensitive, high frequency applications in challenging environments.

Circuit Diagram



Applications

- Alternative energy inverters
- Power Factor Correction (PFC)
- Free-Wheeling diodes
- · Switching supply output rectification
- · Reverse polarity protection

Features

- 175°C T_J operation
- Ultra-low switching loss
- · Switching speeds independent of operating temperature
- Low total conduction losses
- High forward surge current capability
- Guard ring for enhanced ruggedness and long term reliability
- Pb Free Device
- All SMC parts are traceable to the wafer lot
- Additional electrical and life testing can be performed upon request

Maximum Ratings:

Characteristics	Symbol	Condition	Max.	Units
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RRM} V _{RWM} V _R	-	650	V
Average Rectified Forward Current	I _{F (AV)}	50% duty cycle @Tc=115°C, rectangular wave form	10(Per Leg) 20(Per Device)	Α
Peak One Cycle Non-Repetitive Surge Current (Per Leg)	I _{FSM}	10ms, Half Sine pulse, T _C = 25 °C	40	А

- China Germany Korea Singapore United States
 - http://www.smc-diodes.com sales@ smc-diodes.com •







Electrical Characteristics:


Characteristics	Symbol	Condition	Тур.	Max.	Units
Forward Voltage Drop(Per Leg)*	V _{F1} @ 10A, Pulse, T _J = 25 °C		1.5	1.7	٧
	V _{F2}	@ 10A, Pulse, T _J = 175 °C	1.6	2.1	V
Reverse Current at DC condition(Per Leg)*	I _{R1}	$@V_R = \text{rated } V_R$ $T_J = 25 ^{\circ}\text{C}$	30	150	μΑ
	I _{R2}	$@V_R = \text{rated } V_R$ $T_J = 175 ^{\circ}\text{C}$	210	1500	μА
Total Capacitive charge(Per Leg)	Qc	V _r = 400 V, I _F = 10A dI _F /dt = -200 A/µs, T _j = 150 °C	12	-	nC
Junction Capacitance(Per Leg)	Ст	@V _R = 0V, T _C = 25 °C, f _{SIG} = 1MHz	650	-	pF
Voltage Rate of Change	dv/dt	-	-	10,000	V/μs

^{*} Pulse width < 300 µs, duty cycle < 2%


Thermal-Mechanical Specifications:

Characteristics	Symbol	Condition	Specification	Units
Junction Temperature	TJ	-	-55 to +175	°C
Storage Temperature	T _{stg}	-	-55 to +175	°C
Typical Thermal Resistance Junction to Case	R _{θJC}	DC operation	0.84	°C/W
Approximate Weight	wt	-	6.28	g
Case Style	TO-247AD			

Tube Specification



Marking Diagram



Where XXXXX is YYWWL

SICR = Device Type 20 = Forward Current (20A) 650 = Reverse Voltage (650V) WT = Configuration

Cautions: Molding resin


Epoxy resin UL:94V-0








Mechanical Dimensions TO-247AD





CVMDOL	Millimeters				
SYMBOL	MIN.	TYP.	MAX.		
Α	4.80	5.00	5.20		
A1	2.20	2.41	2.61		
A2	1.90	2.00	2.10		
b	1.10	1.20	1.40		
b1	1.80	2.00	2.20		
b2	2.80	3.00	3.20		
С	0.50	0.60	0.75		
D	20.30	21.00	21.20		
D1		16.55			
D2		1.20			
D2 E	15.45	15.80	16.00		
E1		13.30			
E2		5.00			
E3		2.50			
е		5.44			
L	19.42	19.92	20.70		
L1		4.13			
Р	3.50	3.60	3.70		
P1	7.1		7.40		
P2		2.50			
		5.80			
Q S T	6.05	6.15	6.25		
Т		10.00			
U		6.20			

Ordering Information

Device	Package	Plating	Weight	Shipping
SICR20650WT	TO-247AD	Pure Sn	6.28g	25pcs / tube

For information on tape and reel specifications, including part orientation and tape sizes, please refer to our tape and reel packaging specification.







DISCLAIMER:

- 1- The information given herein, including the specifications and dimensions, is subject to change without prior notice to improve product characteristics. Before ordering, purchasers are advised to contact the SMC Sangdest Microelectronics (Nanjing) Co., Ltd sales department for the latest version of the datasheet(s).
- 2- In cases where extremely high reliability is required (such as use in nuclear power control, aerospace and aviation, traffic equipment, medical equipment, and safety equipment), safety should be ensured by using semiconductor devices that feature assured safety or by means of users' fail-safe precautions or other arrangement.
- 3- In no event shall SMC Sangdest Microelectronics (Nanjing) Co., Ltd be liable for any damages that may result from an accident or any other cause during operation of the user's units according to the datasheet(s). SMC Sangdest Microelectronics (Nanjing) Co., Ltd assumes no responsibility for any intellectual property claims or any other problems that may result from applications of information, products or circuits described in the datasheets.
- 4- In no event shall SMC Sangdest Microelectronics (Nanjing) Co., Ltd be liable for any failure in a semiconductor device or any secondary damage resulting from use at a value exceeding the absolute maximum rating.
- 5- No license is granted by the datasheet(s) under any patents or other rights of any third party or SMC Sangdest Microelectronics (Nanjing) Co., Ltd.
- 6- The datasheet(s) may not be reproduced or duplicated, in any form, in whole or part, without the expressed written permission of SMC Sangdest Microelectronics (Nanjing) Co., Ltd.
- 7- The products (technologies) described in the datasheet(s) are not to be provided to any party whose purpose in their application will hinder maintenance of international peace and safety nor are they to be applied to that purpose by their direct purchasers or any third party. When exporting these products (technologies), the necessary procedures are to be taken in accordance with related laws and regulations.