

APPROVAL SHEET

Approval Specification	Customer's Approval Certificate
TO:	Checked & Approved by:
Part No.:	Date:
Customer's Part No.:	Please return this copy as a certification of your approval

Shenzhen Huayuan Micro Electronic Technology Co.Ltd.

Tel: +86-0755-29881155-8006

Fax: +86-0755-29881157

E-mail: sfsaw_sales@163.com

QQ: 3037058772

Website: <http://www.sfsaw.com> <http://www.szhywd.net>

Add: No.5 Zhuangcun Road, Xiner Community,
Shajing Street, Baoan District, Shenzhen



Part No.	:	R316A
Pages	:	4
Date	:	2016/8/1
Revision	:	2.0


Features

- 1-port Resonator
- Metal Case for **D11**
- Package size 8.36x3.45x3.00 mm³
- **RoHS** compatible
- **Electrostatic Sensitive Device(ESD)**




Application


Typical Low-Power Transmitter Application



Typical Local Oscillator Application




Package Dimensions (D11)



Pin Configuration

1	Input/Output
3	Output/Input
2	Case Ground



Marking



R	SAW Resonator
316A	Part number

Test Circuit

Equivalent LC Model



Performance

Maximum Rating

Item		Value	Unit
DC Voltage	V_{DC}	± 30	V
Operation Temperature	T	-40 ~ +85	$^{\circ}C$
Storage Temperature	T_{stg}	-40 ~ +85	$^{\circ}C$
RF Power Dissipation	P	25	dBm

Electronic Characteristics

Test Temperature: $25^{\circ}C \pm 2^{\circ}C$

Terminating source impedance: 50Ω

Terminating load impedance: 50Ω

Item			Minimum	Typical	Maximum	Unit
Center Frequency	Absolute Frequency	f_c		316.80		MHz
	Tolerance from 316.80MHz	Δf_c		± 75		KHz
Insertion Loss(min)		IL		1.4	2.0	dB
Quality Factor	Unloaded Q	Q_U		14833		
	50Ω Loaded Q	Q_L		1676		
Frequency Aging	Absolute Value during the First Year	$ f_A $		≤ 10		ppm/yr
DC Insulation Resistance between Any Two Pins			1.0			M Ω
RF Equivalent RLC Model	Motional Resistance	R_M		12.7	18.0	Ω
	Motional Inductance	L_M		94.97		μH
	Motional Capacitance	C_M		2.65		fF
	Static Capacitance	C_0	3.0	3.2	3.4	pF

Frequency Response

