



# TAI-SAW TECHNOLOGY CO., LTD.

No. 3, Industrial 2nd Rd., Ping-Chen Industrial District,  
Taoyuan, 324, Taiwan, R.O.C.

TEL: 886-3-4690038 FAX: 886-3-4697532

E-mail: [tstsales@mail.taisaw.com](mailto:tstsales@mail.taisaw.com) Web: [www.taisaw.com](http://www.taisaw.com)

## Product Specifications Approval Sheet

Product Description: SAW Filter 1191.8 MHz SMD 3.8x3.8 mm (BW=55 MHz)

TST Part No.: TA2388A

Customer Part No.: \_\_\_\_\_

Customer signature required
Company: _____
Division: _____
Approved by : _____
Date: _____

Checked by: \_\_\_\_\_ David Chang *David*

Approved by: \_\_\_\_\_ Andy Yu *Andy Yu*

Date: \_\_\_\_\_ 2018/05/31

1. Customer signed back is required before TST can proceed with sample build and receive orders.
2. Orders received without customer signed back will be regarded as agreement on the specifications.
3. Any specifications changes must be approved upon by both parties and a new revision of specifications shall be released to reflect the changes.



# TAI-SAW TECHNOLOGY CO., LTD.

No. 3, Industrial 2nd Rd., Ping-Chen Industrial District,  
Taoyuan, 324, Taiwan, R.O.C.

TEL: 886-3-4690038 FAX: 886-3-4697532

E-mail: [tstsales@mail.taisaw.com](mailto:tstsales@mail.taisaw.com) Web: [www.taisaw.com](http://www.taisaw.com)

## SAW Filter 1191.8 MHz

MODEL NO.:TA2388A

REV. NO.:1

### A. MAXIMUM RATING:

1. Input Power Level: 10 dBm
2. DC Voltage : 3 V
3. Operating Temperature: -40°C to +85°C
4. Storage Temperature: -40°C to +85°C
5. Moisture Sensivity Level: Level 1 (MSL1)

RoHS Compliant  
Lead free  
Lead-free soldering


Electrostatic Sensitive Device (ESD)

### B. ELECTRICAL CHARACTERISTICS:




Item	Unit	Min.	Typical	Max.
Center frequency <b>Fc</b>	MHz	-	1191.8	-
Insertion loss (1164.3~1219.3 MHz) <b>IL</b>	dB	-	2.5	4.6
Amplitude Ripple (1169.8~1213.8 MHz)	dB	-	0.4	1.2
Group delay ripple (1164.3~1219.3 MHz)	ns	-	18	50
<b>Attenuation</b> (Reference level from 0 dB)				
10 ~ 1040 MHz	dB	35	38	-
1040 ~ 1126 MHz	dB	20	32	-
1256 ~ 1345 MHz	dB	20	31	-
1345 ~ 1650 MHz	dB	24	27	-
1650 ~ 3000 MHz	dB	24	27	-
Temperature coefficient of frequency	ppm/k	-	-36	-

### C. MEASUREMENT CIRCUIT:


HP Network analyzer



## D. Frequency Characteristics:



**E. OUTLINE DRAWING:**




**Product Year Code**

Year	2009	2010	2011	2012
	2013	2014	2015	2016
	2017	2018	2019	2020
Product Code	A	a	A	a

**Date Code Table:**

WK01	WK02	WK03	WK04	WK05	WK06	WK07	WK08	WK09	WK10	WK11	WK12	WK13
A	B	C	D	E	F	G	H	I	J	K	L	M
WK14	WK15	WK16	WK17	WK18	WK19	WK20	WK21	WK22	WK23	WK24	WK25	WK26
N	O	P	Q	R	S	T	U	V	W	X	Y	Z
WK27	WK28	WK29	WK30	WK31	WK32	WK33	WK34	WK35	WK36	WK37	WK38	WK39
a	b	c	d	e	f	g	h	i	j	k	l	m
WK40	WK41	WK42	WK43	WK44	WK45	WK46	WK47	WK48	WK49	WK50	WK51	WK52
n	o	p	q	r	s	t	u	v	w	x	y	z


**F. PCB Footprint:**




**G. PACKING:**

**1. REEL DIMENSION**

(Please refer to FR-75D10 for packing quantity)



**2. TAPE DIMENSION**



## H. RECOMMENDED REFLOW PROFILE:

1. Preheating shall be fixed at  $150\sim 180^{\circ}\text{C}$  for  $60\sim 90$  seconds.
2. Ascending time to preheating temperature  $150^{\circ}\text{C}$  shall be 30 seconds min.
3. Heating shall be fixed at  $220^{\circ}\text{C}$  for  $50\sim 80$  seconds and at  $260^{\circ}\text{C} + 0/-5^{\circ}\text{C}$  peak ( $20\sim 40$ sec).
4. Time: 2 times.

