

■ Features

- Molding Inductor.
- Low Profile,Low Temp.
- Large Current(Over 15A).
- Customize For Different Need.
- Operating temperature:-40℃ ~ +125℃.

■ Applications

- General Electronic.
- Video Device,TV,TFT.
- Power Module for PC.
- NB/Lap Top Computer.
- Server,VGA Card/Module.

■ Product Identification

$\frac{\text{YSPI}}{(1)} \quad \frac{\square\square\square\square}{(2)} - \frac{\square\square\square}{(3)} \quad \frac{\square}{(4)}$


(1) : Type

(2) : Dimensions

(3) : Inductance value

(4) : Inductance Tolerance: N=±30%,M=±20%, K=±10%

■ Shapes and Dimensions (Unit: mm)



TYPE	A	B	C Max.	D	E Ref.	F Ref.	G Ref.	H Ref.
YSPI1350	13.8±0.5	12.6±0.5	5.0	2.5±0.5	3.5±0.5	4.5	14.5	8.0

■ YSPI1350 Series

Part Number	Inductance (uH) @100KHz	DC Resistance (mΩ)		Heat Rating Current (A)	Saturation Current (A)
		Typ.	Max.		
YSPI1350-R36□	0.36	0.72	1.70	35.0	70.0
YSPI1350-R47□	0.47	1.60	2.50	30.0	60.0
YSPI1350-R56□	0.56	2.30	3.50	25.0	45.0
YSPI1350-R68□	0.68	2.50	4.00	24.0	44.0
YSPI1350-R82□	0.82	2.70	4.50	22.0	42.0
YSPI1350-1R0□	1.00	3.10	5.00	22.0	28.0
YSPI1350-1R5□	1.50	3.70	8.00	15.0	24.0
YSPI1350-2R2□	2.20	5.20	11.00	13.0	23.0
YSPI1350-3R3□	3.30	6.90	10.00	12.0	20.0
YSPI1350-4R7□	4.70	10.00	13.00	12.0	18.0
YSPI1350-6R8□	6.80	13.10	17.00	9.0	14.0
YSPI1350-100□	10.0	21.00	28.00	7.0	13.0
YSPI1350-150□	15.0	32.00	41.00	6.0	9.0
YSPI1350-220□	22.0	51.00	66.00	5.0	7.0
YSPI1350-330□	33.0	65.00	84.00	5.0	5.5
YSPI1350-470□	47.0	85.00	110.00	4.0	4.5


- ※ The saturation current value is the DC current value having inductance decrease down to 30%.(at 20°C)
- ※ The temperature rise current value is the DC current value having temperature increase up to 40°C. (at 20°C)
- ※ The rated current is the DC current value that satisfies both of current value saturation current value and temperature rise current value.

■ Taping Dimensions(Unit:mm)



TYPE	W	A	B	C	D	E	P	K Ref	T	MPQ
YSPI1350	24±0.3	12.8±0.1	13.70±0.1	10.75	11.5±0.1	5.8±0.1	20±0.1	5.1	0.50±0.05	500

■ Reel Dimensions(Unit:mm)



TYPE	W	W1	W2	W3	A	B	C	D
YSPI1350	330±2.0	24.4±1.5	30.4MAX	23.9 Min	13.0±0.50	21.0±0.80	2.0±0.50	100 Min

■ Direction of rolling



■ Cover tape peel off condition



Cover tape peel force shall be 0.1N to 1.3N.

Reference peel speed 300±10mm/min.