


1. BASE
2. EMITTER
3. COLLECTOR

FEATURES

- Epitaxial planar die construction.
- Complementary NPN type available (MMBTA42).
- Ideal for medium power amplification and switching.

APPLICATIONS

- High voltage driver applications.



SOT-23		
Dim	Min	Max
A	2.70	3.10
B	1.10	1.50
C	1.0 Typical	
D	0.4 Typical	
E	0.35	0.48
G	1.80	2.00
H	0.02	0.1
J	0.1 Typical	
K	2.20	2.60
All Dimensions in mm		

ORDERING INFORMATION



Type No.	Marking	Package Code
MMBTA92	2D	SOT-23







MAXIMUM RATING @ Ta=25°C unless otherwise specified

Symbol	Parameter	Value	UNIT
V_{CBO}	collector-base voltage	-300	V
V_{CEO}	collector-emitter voltage	-300	V
V_{EBO}	emitter-base voltage	-5	V
I_C	collector current (DC)	-0.5	A
P_C	Collector dissipation	0.35	W
T_J, T_{stg}	junction and storage temperature	-55 to +150	°C

ELECTRICAL CHARACTERISTICS @ Ta=25°C unless otherwise specified

Symbol	Parameter	Test conditions	MIN.	MAX.	UNIT
$V_{(BR)CBO}$	Collector-base breakdown voltage	$I_C = -100\mu A, I_E = 0$	-300		
$V_{(BR)CEO}$	Collector-emitter breakdown voltage	$I_C = -1mA, I_B = 0$	-300		
$V_{(BR)EBO}$	Emitter-base breakdown voltage	$I_E = -100\mu A, I_C = 0$	-5		
I_{CBO}	collector cut-off current	$I_E = 0; V_{CB} = -200V$	-	-0.25	μA
I_{EBO}	emitter cut-off current	$I_C = 0; V_{EB} = -3V$	-	-0.1	μA
h_{FE}	DC current gain	$V_{CE} = -10V; I_C = -1mA$ $V_{CE} = -10V; I_C = -10mA$ $V_{CE} = -10V; I_C = -30mA$	25 40 25		
$V_{CE(sat)}$	collector-emitter saturation voltage	$I_C = -20mA; I_B = -2mA$	-	-0.5	V
$V_{BE(sat)}$	base-emitter saturation voltage	$I_C = -20mA; I_B = -2mA$	-	-0.9	V
C_{ob}	Collector output capacitance	$V_{CB} = -20V, f = 1.0MHz$	-	6.0	pF
f_T	transition frequency	$I_C = -10mA; V_{CE} = -20V;$ $f = 100MHz$	50	-	MHz

TYPICAL CHARACTERISTICS @ Ta=25°C unless otherwise specified




Device	Package	Shipping
MMBTA92	SOT-23	3000/Tape&Reel