

# **Features**

- Halogen Free Available Upon Request By Adding Suffix "-HF"
- High Surge Capability
- Super Low Forward Voltage Drop
- Low-Profile-Package
- Lead Free Finish/RoHS Compliant ("P" Suffix Designates RoHS Compliant. See Ordering Information)
- Epoxy Meets UL 94 V-0 Flammability Rating
- · Moisture Sensitivity Level 1

# **Maximum Ratings**

- Operating Junction Temperature Range: -65°C to +125°C
- Storage Temperature Range: -65°C to +125°C
- Typical Thermal Resistance(Note1):60°C/W Junction to Ambient
- Typical Thermal Resistance(Note2):180°C/W Junction to Ambient

MCC Part Number	Device Marking	Maximum Recurrent Peak Reverse Voltage	Maximum RMS Voltage	Maximum DC Blocking Voltage
MBRX120LF	F02	20V	14V	20V


# Electrical Characteristics @ 25°C Unless Otherwise Specified

Average Forward Current	I <sub>F(AV)</sub>	1A	
Surge Forward Current	I <sub>FSM</sub>	12A	at 8.3ms
Power Dissipation	$P_{D}$	1.67W	Note1
Power Dissipation	$P_D$	556mW	Note2
Forward Voltage	V <sub>F</sub>	0.2V(Typ) 0.3V(Typ) 0.32V(Typ) 0.36V(Max)	I <sub>F</sub> =0.1A I <sub>F</sub> =0.7A I <sub>F</sub> =1A
Leakage Current	I <sub>R</sub>	0.26mA(Typ) 1mA(Max)	V <sub>R</sub> =5V V <sub>R</sub> =20V
Typical Junction Capacitance	C <sub>T</sub>	75pF(Typ)	V <sub>R</sub> =10V, f=1.0MHz

Notes: 1. Part mounted on 50.8mm X 50.8mm GETEK board with 25.4mm X 25.4mm copper pad. $T_A$  = 25°C. 2. Part mounted on FR-4 board with 1.8mm X 2.5mm copper pads.  $T_A$  = 25°C.


# Low Forward Volatge Drop Schottky Barrier Diodes

# SOD-123



DIMENSIONS						
DIM	INCHES		MM		NOTE	
DIIVI	MIN	MAX	MIN	MAX	NOTE	
Α	0.140	0.152	3.55	3.85		
В	0.100	0.112	2.55	2.85		
С	0.055	0.071	1.40	1.80		
D		0.053		1.35		
Е	0.018	0.026	0.45	0.65		
G	0.006		0.15			
Н		0.010		0.25		
J		0.006		0.15		

### Suggested Solder Pad Layout





# **Curve Characteristics**

Fig. 1 - Typical Instantaneous Forward Characteristics





Fig. 2 - Typical Reverse Leakage Characteristics





# **Ordering Information**

Device	Packing	
Part Number-TP	Tape&Reel: 3Kpcs/Reel	

Note: Adding "-HF" Suffix For Halogen Free, eg. Part Number-TP-HF

### \*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp.** reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp**. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp**, and all the companies whose products are represented on our website, harmless against all damages.

### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.