Please visit our website for more information: www.upi-semi.com

QN4103M6N

N-Channel 40V Fast Switching MOSFET

General Description

The QN4103M6N is the highest performance trench N-Channel MOSFET with extreme high cell density , which provide excellent RDSON and gate charge for most of the synchronous buck converter applications .

The QN4103M6N meet the RoHS and Green Product requirement with full function reliability approved.

Product Summary

Green RoHS、HF、Pb

BVDSS	RDSON (VGS=10V)	ID (TC=25℃)
40V	1.4mΩ	255A

Features

- Advanced high cell density Trench technology
- Green Device Available

Applications

- Synchronous rectifier for Consumer/Computing /Industry Power Supply
- Motor
- Load Switch

PRPAK 5X6 Pin Configuration





Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	40	V
V_{GS}	Gate-Source Voltage	±20	V
I_D@T_C=25℃	Continuous Drain Current, V_{GS} @ 10V[1]	255	A
I_D@T_C=100℃	Continuous Drain Current, V_{GS} @ 10V[1]	161	A
I_D@T_A=25℃	Continuous Drain Current, V_{GS} @ 10V[1]	31	A
I_D@T_A=70℃	Continuous Drain Current, V_{GS} @ 10V[1]	24	A
I_{DM}	Pulsed Drain Current[2]	510	A
EAS	Single Pulse Avalanche Energy[3]	1024.0	mJ
I_{AS}	Avalanche Current	64.0	A
P_D@T_C=25℃	Total Power Dissipation[4]	156	W
P_D@T_A=25℃	Total Power Dissipation[4]	2.3	W
T_{STG}	Storage Temperature Range	-55 to 150	℃
T_J	Operating Junction Temperature Range	-55 to 150	℃

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-Ambient[1]	43	54	℃/W
$R_{\theta JC}$	Thermal Resistance Junction-Case	0.6	0.8	℃/W

Electrical Characteristics (T_J=25 ℃, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	V_{GS}=0V , I_D=250uA	40	---	---	V
$\triangle BV_{DSS}/\triangle T_J$	BVDSS Temperature Coefficient	Reference to 25℃ , I_D=1mA	---	0.025	---	V/℃
$R_{DS(ON)}$	Static Drain-Source On-Resistance[2]	V_{GS}=10V , I_D=50A	---	1.1	1.4	mΩ
		V_{GS}=4.5V , I_D=30A	---	1.5	2.0	
$V_{GS(th)}$	Gate Threshold Voltage	V_{GS}=V_{DS} , I_D =250uA	1.2	---	2.5	V
$\triangle V_{GS(th)}$	$V_{GS(th)}$ Temperature Coefficient		---	-5.2	---	mV/℃
I_{DSS}	Drain-Source Leakage Current	V_{DS}=32V , V_{GS}=0V , T_J=25℃	---	---	1	uA
		V_{DS}=32V , V_{GS}=0V , T_J=55℃	---	---	5	
I_{GSS}	Gate-Source Leakage Current	V_{GS}=±20V , V_{DS}=0V	---	---	±100	nA
gfs	Forward Transconductance	V_{DS}=5V , I_D=30A	---	94.2	---	S
R_g	Gate Resistance	V_{DS}=0V , V_{GS}=0V , f=1MHz	---	0.9	---	Ω
Q_g	Total Gate Charge (10V)	V_{DS}=20V , V_{GS}=10V , I_D=30A	---	73.7	---	nC
Q_g	Total Gate Charge (4.5V)	V_{DS}=20V , V_{GS}=4.5V , I_D=30A	---	32.9	---	
Q_{gs}	Gate-Source Charge		---	16.3	---	
Q_{gd}	Gate-Drain Charge		---	7.2	---	
$T_{d(on)}$	Turn-On Delay Time	V_{DD}=20V , V_{GS}=10V , R_G=3.3Ω I_D=30A	---	15.2	---	ns
T_r	Rise Time		---	45.2	---	
$T_{d(off)}$	Turn-Off Delay Time		---	53.0	---	
T_f	Fall Time		---	7.2	---	
C_{iss}	Input Capacitance	V_{DS}=20V , V_{GS}=0V , f=1MHz	---	5450	---	pF
C_{oss}	Output Capacitance		---	996	---	
C_{rss}	Reverse Transfer Capacitance		---	35	---	

Guaranteed Avalanche Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
EAS	Single Pulse Avalanche Energy[5]	V_{DD}=50V , L=0.5mH , I_{AS}= 46A	529	---	---	mJ

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current[1,6]	V_G=V_D=0V , Force Current	---	---	255	A
I_{SM}	Pulsed Source Current[2,6]		---	---	510	A
V_{SD}	Diode Forward Voltage[2]	V_{GS}=0V , I_S=1A , T_J=25℃	---	---	1.2	V
trr	Reverse Recovery Time	IF=30A , di/dt=100A/μs , T_J=25℃	---	44	---	nS
Qrr	Reverse Recovery Charge		---	50	---	nC

Note :
1.The data tested by surface mounted on a 1 inch^2 FR-4 board with 2OZ copper.
2.The data tested by pulsed , pulse width ≦ 300us , duty cycle ≦ 2%
3.The EAS data shows Max. rating . The test condition is V_{DD}=50V,V_{GS}=10V,L=0.5mH
4.The power dissipation is limited by 150℃ junction temperature
5.The Min. value is 100% EAS tested guarantee.
6.The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation.

Typical Characteristics



Fig.1 Typical Output Characteristics



Fig.2 On-Resistance vs. Gate-Source



Fig.3 Forward Characteristics of Reverse



Fig.4 Gate-Charge Characteristics



Fig.5 Normalized $V_{GS(th)}$ vs. T_J



Fig.6 Normalized R_{DSON} vs. T_J



Fig.7 Drain-Source On-State Resistance



Fig.8 Transfer Characteristics



Fig.9 Capacitance



Fig.10 Safe Operating Area



Fig.11 Transient Thermal Impedance

Top Marking



Important Notice

UBIQ and its subsidiaries reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.
UBIQ products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgment. However, no responsibility is assumed by UBIQ or its subsidiaries for its use or application of any product or circuit; nor for any infringements of patents or other rights of third parties which may result from its use or application, including but not limited to any consequential or incidental damages. No UBIQ components are designed, intended or authorized for use in military, aerospace, automotive applications nor in systems for surgical implantation or life-sustaining. No license is granted by implication or otherwise under any patent or patent rights of UBIQ or its subsidiaries.

UBIQ Semiconductor Corp.

Headquarter
9F.,No.5, Taiyuan 1st St. Zhubei City,
Hsinchu Taiwan, R.O.C.
TEL : 886.3.560.1818 FAX : 886.3.560.1919

Sales Branch Office
12F-5, No. 408, Ruiguang Rd. Neihu District,
Taipei Taiwan, R.O.C.
TEL : 886.2.8751.2062 FAX : 886.2.8751.5064