



RECOMMENDED P.C.B LAYOUT

INSPECTION DIMENSION:(A)~(J)

SPECIFICATIONS

ELECTRICAL CHARACTERISTICS:

Contact Current Rating:3 Amperes.
 Dielectric Withstanding Voltage: AC 1000/60sec.r.m.s.
 Insulation Resistance:1000 Megohms Minimum.at DC 500V.
 Contact Resistance:25 Milliohms Maximum.
 Operating Temperature:-55°C to+105°C.

MECHANICAL CHARACTERISTICS:

Contact Insertion Force:341 g.Maximum.
 Contact Separation Force:21 g.Minimum.

MATERIALS:

Contacts:Brass.
 Insulator: PBT Or High Temperature Plastic
 UL 94V-0 Rated.

Shell:Cold Roller Steel.

FINISHES:

Contact:Gold Flash Or Full Gold.
 Shell:Tin Or Nickel Plated.



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: DR9公对DR9公15.88锁螺丝
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYC33-VGA18A-158
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY:	DATE : 2014-02-23	PART NO. HYC33-VGA18A-158
			MOLD NO. / DRAW NO: HYC-VGA16072515
			SHEET NO. 1 OF 1