



Fast Recovery Rectifier



Features

- High efficiency
- High current capability
- High reliability
- High surge current capability
- Low power loss
- Glass passivated chip junction
- Solder dip 275 °C max. 7 s, per JESD 22-B106

Mechanical Data

- **Package:** DO-201AD(DO-27)
Molding compound meets UL 94 V-0 flammability rating, RoHS-compliant
- **Terminals:** Tin plated leads, solderable per J-STD-002 and JESD22-B102
- **Polarity:** Color band denotes cathode end

■Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	FR301	FR302	FR303	FR304	FR305	FR306	FR307
Device marking code			FR301	FR302	FR303	FR304	FR305	FR306	FR307
Repetitive Peak Reverse Voltage	VRRM	V	50	100	200	400	600	800	1000
Average Forward Current @60Hz sine wave, Resistance load, Ta=50°C	IF(AV)	A	3.0						
Forward Surge Current(Non-repetitive) @60Hz Half-sine wave, 1 cycle, Ta=25°C	IFSM	A	125						
Storage Temperature	Tstg	°C	-55 ~+150						
Junction Temperature	Tj	°C	-55~+150						

■Electrical Characteristics (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	TEST CONDITIONS	FR301	FR302	FR303	FR304	FR305	FR306	FR307
Maximum instantaneous forward voltage drop per diode	V _{FM}	V	IFM=3.0A	1.3						
Maximum DC reverse current at rated DC blocking voltage per diode	I _{RRM1}	μA	Ta=25°C	2.5						
	I _{RRM2}		Ta=100°C	100						
Reverse Recovery time	t _r	ns	I _F =0.5A I _R =1A I _{RR} =0.25A			150		250		500
Typical junction capacitance	C _j	pF	Measured at 1MHZ and Applied Reverse Voltage of 4.0 V.D.C.	35						

■Thermal Characteristics (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	FR301	FR302	FR303	FR304	FR305	FR306	FR307
Thermal Resistance(Typical)	R _{θJA}	°C/W	30						



FR301 THRU FR307

Ordering Information (Example)

PREFERRED P/N	PACKAGE CODE	UNIT WEIGHT(g)	MINIMUM PACKAGE(pcs)	INNER BOX QUANTITY(pcs)	OUTER CARTON QUANTITY(pcs)	DELIVERY MODE
FR301~FR307	D1	Approximate 1.05	1250	1250	12500	Tape

Characteristics (Typical)

FIG.1: I_o-T_a Curve




FIG.2: Forward Surge Current Capability




FIG.3: Forward Voltage




FIG.4: Typical Reverse Characteristics






FIG.5: Diagram of circuit and Testing wave form of reverse recovery time



■ Outline Dimensions



DO-201AD(DO-27)		
Dim	Min	Max
A	8.50	9.50
B	5.00	5.60
C	25.4	/
D	1.20	1.30



FR301 THRU FR307

Disclaimer

The information presented in this document is for reference only. Yangzhou Yangjie Electronic Technology Co., Ltd. reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), Yangjie or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale.

This publication supersedes & replaces all information previously supplied. For additional information, please visit our website [http:// www.21yangjie.com](http://www.21yangjie.com) , or consult your nearest Yangjie's sales office for further assistance.