# FFPF30UA60S

## Ultrafast II Diode 30 A, 600 V

#### Description

The FFPF30UA60S is a ultrafast II diode with low forward voltage drop. This device is intended for use as freewheeling and clamping diodes in a variety of switching power supplies and other power switching applications. It is specially suited for use in switching power supplies and industrial application.

#### Features

- Ultrafast Recovery,  $t_{RR} = 90$  ns (@  $I_F = 30$  A)
- Max Forward Voltage,  $V_F = 2.2 V (@ T_C = 25^{\circ}C)$
- 600 V Reverse Voltage and High Reliability
- Avalanche Energy Rated
- This Device is Pb-Free and is RoHS Compliant

#### Applications

- Boost Diode in PFC and SMPS
- Welder, UPS and Motor Control Application

### **ABSOLUTE MAXIMUM RATINGS**

 $T_C = 25^{\circ}C$  unless otherwise noted


Symbol	Parameter	Rating	Unit
VRRM	Peak Repetitive Reverse Voltage	600	V
VRWM	Working Peak Reverse Voltage	600	V
lf(AV)	Average Rectified Forward Current @ $T_c = 43^{\circ}C$	30	A
IFSM	Non-repetitive Peak Surge Current 60Hz Single Half-Sine Wave	180	A
Тј, Тѕтс	IJ, TSTG Operating Junction and Storage Temperature		°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.



## **ON Semiconductor®**


www.onsemi.com





TO-220, 2-Lead CASE 221AS

### MARKING DIAGRAM



#### **ORDERING INFORMATION**

See detailed ordering and shipping information on page 2 of this data sheet.

## FFPF30UA60S

#### THERMAL CHARACTERISTICS $T_C$ = 25°C unless otherwise noted

Symbol	Parameter	Max.	Unit
Rejc	Maximum Thermal Resistance, Junction to Case	2.5	°C/W

#### PACKAGE MARKING AND ORDERING INFORMATION

Part Number	Top Mark	Package	Packing Method	Reel Size	Tape Width	Quantity
FFPF30UA60S	F30UA60S	TO-220F-2L	Tube	N/A	N/A	50


#### **ELECTRICAL CHARACTERISTICS** $T_C = 25^{\circ}C$ unless otherwise noted

Parameter	Conditions		Min.	Тур.	Max.	Unit
V <sub>F</sub> (Note 1)	I <sub>F</sub> = 30 A I <sub>F</sub> = 30 A	$T_{C} = 25^{\circ}C$ $T_{C} = 125^{\circ}C$	-		2.2 2.0	V
I <sub>R</sub> (Note 1)	V <sub>R</sub> = 600 V V <sub>R</sub> = 600 V	$T_{C} = 25^{\circ}C$ $T_{C} = 125^{\circ}C$	-	-	100 150	μΑ
t <sub>RR</sub> I <sub>RR</sub> Q <sub>RR</sub>	I <sub>F</sub> = 30 A, di <sub>F</sub> /dt = 200 A/μs	T <sub>C</sub> = 25°C		- - -	90 8 360	ns A nC
W <sub>AVL</sub>	Avalanche Energy ( L = 40 mH)		20	-	-	mJ

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

1. Pulse: Test Pulse Width = 300  $\mu$ s, Duty Cycle = 2%

#### **Test Circuit and Waveforms**



#### Figure 1. Diode Reverse Recovery Test Circuit & Waveform





Figure 2. Unclamped Inductive Switching Test Circuit & Waveform

### FFPF30UA60S

#### **TYPICAL PERFORMANCE CHARACTERISTICS**









Figure 5. Typical Junction Capacitance






Figure 4. Typical Reverse Current vs. Reverse Voltage






Figure 6. Typical Reverse Recovery Time vs. di<sub>F</sub>/dt









TO-220 Fullpack, 2-Lead / TO-220F-2FS

DATE 29 FEB 2012

DOCUMENT NUMBER:	98AON67438E	Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.				
DESCRIPTION:	RIPTION: TO-220 FULLPACK, 2-LEAD / TO-220F-2FS PAGE 1 O					
ON Semiconductor and (III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the						

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor date sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use a a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor houteds for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

#### TECHNICAL SUPPORT

ON Semiconductor Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910 Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative