KP-2012CGCK

2.0 x 1.25 mm SMD Chip LED Lamp



DESCRIPTIONS

- The Green source color devices are made with AlGaInP on GaAs substrate Light Emitting Diode
- · Electrostatic discharge and power surge could damage the LEDs
- · It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs
- · All devices, equipments and machineries must be electrically grounded

FEATURES

- 2.0 mm x 1.25 mm SMD LED, 1.1 mm thickness
- Low power consumption
- Wide viewing angle
- · Ideal for backlight and indicator
- Package: 2000 pcs / reel
- Moisture sensitivity level: 3
- · Halogen-free
- RoHS compliant


APPLICATIONS

- Backlight
- · Status indicator
- · Home and smart appliances
- Wearable and portable devices
- · Healthcare applications

ATTENTION

Observe precautions for handling electrostatic discharge sensitive devices

PACKAGE DIMENSIONS



(units : mm; tolerance : ± 0.1)



Notes

All dimensions are in millimeters (inches).
 Tolerance is ±0.1(0.004") unless otherwise noted.

3. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.

The device has a single mounting surface. The device must be mounted according to the specifications.

SELECTION GUIDE

Part Number	Emitting Color	Lens Type	lv (mcd) @ 20mA ^[2]		Viewing Angle ^[1]	
r art Number	(Material)	Lens Type	Min.	Тур.	201/2	
KP-2012CGCK	Green (AlGalnP)	Water Clear	20	50	140°	

Notes

1. 61/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
 2. Luminous intensity / luminous flux: +/-15%.
 3. Luminous intensity value is traceable to CIE127-2007 standards.

KP-2012CGCK

ELECTRICAL / OPTICAL CHARACTERISTICS at T_A=25°C

Parameter	Symbol	Emitting Color	Value		Unit
Farameter		Emitting Color	Тур.	Max.	Unit
Wavelength at Peak Emission I_F = 20mA	λ_{peak}	Green	574	-	nm
Dominant Wavelength I _F = 20mA	λ_{dom} ^[1]	Green	570	-	nm
Spectral Bandwidth at 50% Φ REL MAX I _F = 20mA	Δλ	Green	20	-	nm
Capacitance	С	Green	15	-	pF
Forward Voltage I _F = 20mA	V _F ^[2]	Green	2.1	2.5	V
Reverse Current (V _R = 5V)	I _R	Green	-	10	μA

Notes.

The dominant wavelength (λd) above is the setup value of the sorting machine. (Tolerance λd : ±1nm.)
 Forward voltage: ±0.1V.
 Wavelength value is traceable to CIE127-2007 standards.
 Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.


ABSOLUTE MAXIMUM RATINGS at $T_A=25^{\circ}C$

Parameter	Symbol	Value	Unit
Power Dissipation	P _D	75	mW
Reverse Voltage	V _R	5	V
Junction Temperature	Tj	115	°C
Operating Temperature	T _{op}	-40 to +85	°C
Storage Temperature	T _{stg}	-40 to +85	°C
DC Forward Current	l _F	30	mA
Peak Forward Current	I _{FM} ^[1]	150	mA
Electrostatic Discharge Threshold (HBM)	-	3000	V


Notes: 1. 1/10 Duty Cycle, 0.1ms Pulse Width. 2. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.

TECHNICAL DATA

RELATIVE INTENSITY vs. WAVELENGTH



SPATIAL DISTRIBUTION




GREEN

30 40 50

Forward Current vs. Forward Voltage Luminous Intensity vs. Forward Current 50 2.5 Luminous intensity normalised at 20 mA T_a = 25 °C T_a = 25 °C 2.0 Forward current (mA) 40 30 1.5 1.0 20 10 0.5 0 0.0 1.9 2.1 23 25 10 20 1.5 1.7 0 Forward voltage (V) Forward current (mA)

REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS




Notes

50 at Permissible forward current (mA) Luminous intensity normalised 40 30 20 10 0 -40 -20 0 20 40 60 80 100 Ambient temperature (°C)


Forward Current Derating Curve

Luminous Intensity vs. Ambient Temperature


KP-2012CGCK



TAPE SPECIFICATIONS (units : mm)




REEL DIMENSION (units : mm)



Notes: 1. Don't cause stress to the LEDs while it is exposed to high temperature. 2. The maximum number of reflow soldering passes is 2 times. 3. Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product.

KP-2012CGCK

Outside _____Label



PRECAUTIONARY NOTES

- The information included in this document reflects representative usage scenarios and is intended for technical reference only.
- The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications. 2.
- the latest datasheet for the updated specifications.
 When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.
 The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.
 The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
 All design applications should refer to Kingbright application notes available at https://www.Kingbright.com/application_notes