KPBD-3224SURKCGKC

3.2 x 2.4 mm SMD Chip LED Lamp



DESCRIPTIONS

- The Hyper Red source color devices are made with AlGaInP on GaAs substrate Light Emitting Diode
- · The Green source color devices are made with AlGaInP on GaAs substrate Light Emitting Diode
- · Electrostatic discharge and power surge could damage the LEDs
- · It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs
- All devices, equipments and machineries must be electrically grounded

FEATURES

- 3.2 x 2.4 mm SMD LED, 2.4 mm thickness
- Low power consumption
- Ideal for backlight and indicator
- Package: 1500 pcs / reel
- Moisture sensitivity level: 3
- Halogen-free
- RoHS compliant

APPLICATIONS


- Backlight
- Status indicator
- · Home and smart appliances
- · Wearable and portable devices
- · Healthcare applications

ATTENTION


Observe precautions for handling electrostatic discharge sensitive devices



PACKAGE DIMENSIONS



RECOMMENDED SOLDERING PATTERN



Notes

All dimensions are in millimeters (inches).
 Tolerance is ±0.1(0.004") unless otherwise noted.

3. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.

The device has a single mounting surface. The device must be mounted according to the specifications.

SELECTION GUIDE

Part Number	Emitting Color (Material)	Lens Type	lv (mcd) @ 20mA ^[2]		Viewing Angle ^[1]	
			Min.	Тур.	201/2	
KPBD-3224SURKCGKC	Hyper Red (AlGaInP)	- Water Clear	700	1300		
			*120	*400	20°	
	Green (AlGaInP)		80	280	20	
			*80	*280		

Notes

Holes.
 Holes.

KPBD-3224SURKCGKC

ELECTRICAL / OPTICAL CHARACTERISTICS at T_A=25°C

Parameter	Symbol	Emitting Color	Value		Unit
			Тур.	Max.	
Wavelength at Peak Emission I_F = 20mA	λ_{peak}	Hyper Red Green	645 574	-	nm
Dominant Wavelength I _F = 20mA	λ_{dom} ^[1]	Hyper Red Green	630 570	-	nm
Spectral Bandwidth at 50% Φ REL MAX I _F = 20mA	Δλ	Hyper Red Green	28 20	-	nm
Capacitance	С	Hyper Red Green	35 15	-	pF
Forward Voltage I _F = 20mA	V _F ^[2]	Hyper Red Green	1.95 2.1	2.5 2.5	V
Reverse Current ($V_R = 5V$)	I _R	Hyper Red Green	-	10 10	μΑ

Notes.

The dominant wavelength (λd) above is the setup value of the sorting machine. (Tolerance λd : ±1nm.)
 Forward voltage: ±0.1V.
 Wavelength value is traceable to CIE127-2007 standards.
 Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.


ABSOLUTE MAXIMUM RATINGS at $T_A=25^{\circ}C$

Parameter	Symbol	Value	Unit	
		Hyper Red	Green	
Power Dissipation	P _D	75	75	mW
Reverse Voltage	V _R	5	5	V
Junction Temperature	TJ	115	115	°C
Operating Temperature	T _{op}	-40 To +8	°C	
Storage Temperature	T _{stg}	-40 To +85		°C
DC Forward Current	I _F	30	30	mA
Peak Forward Current	I _{FM} ^[1]	185	150	mA
Electrostatic Discharge Threshold (HBM)	-	3000	3000	V


Notes: 1. 1/10 Duty Cycle, 0.1ms Pulse Width. 2. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.

TECHNICAL DATA

RELATIVE INTENSITY vs. WAVELENGTH




KPBD-3224SURKCGKC



SPATIAL DISTRIBUTION

HYPER RED




Forward Current vs. Forward Current Derating Curve Luminous Intensity vs. Luminous Intensity vs. Forward Voltage Ambient Temperature Forward Current 50 2.5 2.5 50 Luminous intensity normalised at 20 mA Luminous intensity normalised at $T_a = 25 \ ^\circ C$ Permissible forward current (mA) T_a = 25 °C T_a = 25 °C 40 2.0 2.0 40 Forward current (mA) 30 1.5 30 1.5 20 1.0 20 1.0 10 10 0.5 0.5 0 0.0 0 0.0 1.5 1.7 1.9 2.1 2.3 2.5 0 10 20 30 40 50 -40 -20 0 20 40 60 80 100 -40 -20 0 20 40 60 80 100 Forward voltage (V) Forward current (mA) Ambient temperature (°C) Ambient temperature (°C)

GREEN


Spec No: DSAD3553 / 1203000875 Rev No: V.21A Date: 05/19/2020

KPBD-3224SURKCGKC


REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS



TAPE SPECIFICATIONS (units : mm)




REEL DIMENSION (units : mm)



Notes

Don't cause stress to the LEDs while it is exposed to high temperature
 The maximum number of reflow soldering passes is 2 times.

3. Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product.



PACKING & LABEL SPECIFICATIONS

PRECAUTIONARY NOTES

(SP)XXXXXXXXXXX

- The information included in this document reflects representative usage scenarios and is intended for technical reference only. The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications. 2.
- When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If 3.
- Customer usage exceeds the specified limits. Kingbright will not be responsible for any subsequent issues. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright. All design applications should refer to Kingbright application notes available at <u>https://www.Kingbright.com/application_notes</u> 4.
- 5. 6.

RoHS Cor